

## PERFORMANCE

### Processor

Intel® N100 (4C / 4T, 0.8 / 3.4GHz, 6MB)

### Graphics

Integrated Intel UHD Graphics

### Chipset

Intel SoC Platform

### Memory

4GB Soldered LPDDR5-4800

### Memory Slots

Memory soldered to systemboard, no slots

### Max Memory

4GB soldered memory, not upgradable

### Storage

64GB eMMC 5.1

### Storage Support

64GB eMMC 5.1 on systemboard

### Storage Slot

eMMC on systemboard, no slots

### Card Reader

None

### Optical

None

### Audio Chip

High Definition (HD) Audio

### Speakers

Stereo speakers, 2W x2, optimized with Waves MaxxAudio®

### Camera

HD 720p with Privacy Shutter

### Microphone

2x, Array

### Battery

Integrated 57Wh

### Power Adapter

45W USB-C® (2-pin)

## DESIGN

### Display

14" HD (1366x768) TN 250nits Anti-glare, 45% NTSC

### Touchscreen

None

### Keyboard

Non-backlit, English

### Case Color

Storm Grey

### Surface Treatment

Aluminium Stamping (Anodized)

### Case Material

Aluminium (Top), PC-ABS (Bottom)

### Dimensions (WxDxH)<sup>[1]</sup>

324.4 x 216.2 x 19.3 mm (12.77 x 8.51 x 0.76 inches)

### Weight<sup>[2]</sup>

Around 1.45 kg (3.2 lb)

## SOFTWARE

### Operating System

ChromeOS

### Bundled Software

No ChromeOS Zero Touch Enablement

## CONNECTIVITY

### Ethernet

No Onboard Ethernet

### WLAN + Bluetooth<sup>[3][4]</sup>

Intel Wi-Fi® 6E AX211, 11ax 2x2 + BT5.1

### Standard Ports

- 1x HDMI® 1.4b
- 1x Headphone / microphone combo jack (3.5mm)
- 1x USB-C 3.2 Gen 2 (support data transfer, Power Delivery and DisplayPort™)
- 2x USB 3.2 Gen 1

## SECURITY & PRIVACY

### Security Chip

Google Security Chip H1

### Fingerprint Reader

None

### Physical Locks

Kensington® NanoSaver® lock Slot

### Other Security

Camera privacy shutter

## SERVICE

### Base Warranty

1-year, Courier or Carry-in

### Included Upgrade

None

## CERTIFICATIONS

### Green Certifications<sup>[5]</sup>

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered
- ErP Lot 6
- ErP Lot 26
- TCO Certified 9.0
- RoHS compliant

## MODEL

TopSeller : No

Announce Date : 2023-06-13

EAN / UPC / JAN : 196804080802

End of Support : 2029-04-17



intel

Product image is a sample, it may not match the real color of this model  
Note:

[1] The system dimensions may vary depending on configurations.

[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.

[3] Bluetooth 5.2 is hardware ready but may run at a lower version due to OS limitations.

[4] Wi-Fi 6E full features might be limited by country-level restrictions.

6GHz Wi-Fi 6E operation is dependent on the support of the operating system, routers/APs/Gateways that support Wi-Fi 6E, and the regional regulatory certifications & spectrum allocation.

[5] EPEAT is registered where applicable, please see <https://www.epeat.net> for registration status by country.

· Lenovo reserves the right to change specifications without notice.

· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

To see more note information, please link to

<https://psref.lenovo.com/Detail/2263?M=83BN0001US>

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo 65W USB-C DC Travel Adapter

40AK0065WW

Power up and stay productive on the road with this DC Travel adapter. Lenovo 65W USB-C DC Travel Adapter is the universal DC adapter, providing 65W power via USB-C for outdoor use.

## Recommended Services

GOOD

3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0K75663)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>

Lenovo

PSREF  
Product Specifications  
Reference