



## Thunderbolt™ 4 Triple Alt Mode Display Docking Station

### DOCKTB4PT

SKU: 10QT54

This DOCKTB4PT Thunderbolt 4 Triple Alt Mode Display Docking Station from V7 adds up to 3 displays, 3 USB ports, 2 Thunderbolt 4 ports, a USB-C port with up to 96 Watts Power Delivery, Audio, SD/Micro SD Memory Cards and up to 2.5 Gigabit Ethernet network connectivity to your Thunderbolt 4 enabled computer while charging at the same time with up to 96W power delivery. It features two HDMI ports and two DisplayPort outputs that can be used to extend or mirror your device for multitasking productivity. It supports single 8K 30Hz display (HDMI or DP) or up to three 4K (4K/60Hz + 4K/60Hz + 4K/30Hz) displays. It is Thunderbolt 4 certified and compatible with DisplayPort Alt mode and USB4 enabled computers and mobile devices. It includes both K-Lock and N-Lock interface for security. This solution provides high performance connectivity to extend and enhance your workstation productivity with a 2 year warranty.

- Connect your displays and devices while charging your computer with one cable
- Supports single 8K 30Hz display (HDMI or DP) or up to three 4K (4K/60Hz + 4K/60Hz + 4K/30Hz) displays
- 2 x Thunderbolt 4, 2 x USB A 3.2 Gen2, 1 x USB A 3.2 Gen 1 and 1 x USB-C 3.2 Gen2
- Charge your device with Thunderbolt 4 Power Delivery up to 96 Watts
- Up to 2.5 Gigabit ethernet, SD/Micro SD 4.0, and 3.5mm Audio
- K-Lock and N-Lock interface for security
- 2 year warranty

#### General

Sku: 10QT54  
 Model: DOCKTB4PT  
 EAN: 0662919116199  
 Warranty: 2 years  
 Compliance: CE, FCC, RoHS  
 Country Of Origin: Vietnam  
 Package Type: 4 Color Box  
 ASIN: B0BX4SMJ9B  
 SAP: 5644881  
 Package Includes: 1 x TB4 Docking Station, 1 x TB4 Cable, 1 x 0.8 Meter Quick Start Guide, 1 x DC 20V/7.5A 150W Power Adapter with US, Schuko and UK AC cables

#### Color

Color: Silver  
 Accent Color: Black

#### Design

Docking Type: Alt Mode  
 Number of Ports: 1 x RJ45 Ethernet, 2 x DisplayPort, 2 x HDMI, 2 x Thunderbolt 4, 2 x USB A 3.2 Gen2, 1 x 3.5 mm Audio/Microphone, 1 x MicroSD Card Reader, 1 x SD Card Reader, 1 x USB A 3.2 Gen1, 1 x USB-C 3.2 Gen2, 1 x Thunderbolt 4 Input  
 Material: ABS

#### Package Dimensions

Package Dimensions (L/W/H): 10.63 x 6.3 x 2.36 in (270 x 160 x 60 mm)  
 Shipping Weight: 2.31 lbs (1.05 kg)

#### Product Dimensions

Product Dim (L/W/H): 8.86 x 3.35 x 0.87 in (225 x 85 x 22 mm)  
 Product Weight: 1.1 lbs (0.5 kg)

#### Technical

Connectivity: USB-C  
 Power Delivery: 96 Watts  
 USB Display Type: Alt-Mode  
 Connectors: 3.5mm Audio, DisplayPort, HDMI, Thunderbolt™ 4, USB A, USB-C / USB 3.2  
 Storage Temperature : 0° to +70°  
 Input Voltage: 100-240V AC  
 Security: K-Lock & N-Lock  
 Operating Temperature : 0° to +45°  
 Output Voltage: 20V/7.5A DC  
 Audio Channel: 384KHz sampling rate  
 Data Transfer Rate: 2.5Gbps



### Specifications

Displays	HDMI	DP
1	Max 4K UHD 30/60Hz	Max 8K/30Hz
	2K WQHD 60/120/144/240Hz	4K UHD 60/120/144Hz
	1080P 60/120/144/240Hz	2K WQHD 60/120/144/240Hz
		1080P 60/120/144/240Hz
2	Max 4K UHD 30/60Hz	Max 4K UHD 30/60Hz
	2K WQHD 60/120/144/240Hz	2K WQHD 60/120/144/240Hz
	1080P 60/120/144/240Hz	1080P 60/120/144/240Hz
3	Max 4K UHD 30/60Hz *	Max 4K UHD 30/60Hz *
	2K WQHD 60/120/144/240Hz	2K WQHD 60/120/144/240Hz
	1080P 60/120/144/240Hz	1080P 60/120/144/240Hz

\* second display is max 30Hz