

Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

www.tripplite.com

# 750VA 600W 120V Line-Interactive UPS - 4 NEMA 5-15R Outlets, Network Card Option, USB, DB9, 1U Rack/Tower

MODEL NUMBER: SMART750RT1U











Provides complete battery backup and power protection for servers, switches and other in-rack IT equipment in small-to-mid-size networks.

# **Features**

750VA/600W/120V Battery Backup for PC Networks, Security Systems or Digital Signage

This SmartPro® line-interactive UPS system with AVR provides reliable battery backup and AC power protection against blackouts, brownouts, surges and line noise that can damage valuable electronics or destroy data. The SMART750RT1U is ideal protection for point-of-sale and kiosk applications, a small-business VoIP network or rack-mount equipment, such as servers and switches, in your server room or network closet.

# Reliable Battery Backup Keeps You Operational Through Power Outages

The field-replaceable, hot-swappable internal battery provides ten minutes of support at half load (300W) and three minutes at full load (600W), allowing you to work through short power failures and giving you enough time to safely save files and shut down your system in case of a prolonged blackout. Automatically Turns Back On After Power Is RestoredBattery-independent restart ensures automatic UPS power-up without user interaction after lengthy power outages, even when batteries are expired and require replacement.

Optional WEBCARDLX Network Interface Offers 24/7 Remote Access for Monitoring and Control The optional WEBCARDLX (sold separately) with the latest version of PowerAlert Device Manager firmware (PADM20) provides enhanced remote management capabilities, including customizable dashboard graphs to fit user preferences. The PADM20 upgrade and Tripp Lite's PowerAlert Element Manager (PAEM) software form a powerful tool for expanding maintenance functions in large installations, including firmware update checks and backup and restoration of device configurations.

# **NEMA 5-15R Outlets Protect Your Connected Components**

Four 5-15R outlets in two separate load banks provide connected equipment with pure sine wave AC output during blackouts, overvoltages and severe brownout conditions. Power provided by these outlets is filtered to protect connected equipment against damaging surges and line noise.

# Automatic Voltage Regulation (AVR) Corrects Low- and High-Voltage Conditions

AVR protects your equipment from incremental hardware damage, data loss and performance problems caused by brownouts. The SMART750RT1U maintains regulated 120V nominal output during brownouts as low as 90V, while keeping the battery fully charged and ready to take over in case of power failure.

# **Highlights**

- Protects equipment against blackouts, brownouts, transient surges and line noise
- Keeps AC power running during outages to allow time for file saves and safe shutdown
- Maintains continuous 120V nominal output during brownouts as low as 90V
- 4 outlets (5-15R) power and protect networking, telecom and other sensitive equipment
- Optional WEBCARDLX with latest version of PADM20 for enhanced remote management

# Package Includes

- 750VA 600W 120V Line-Interactive UPS with 4 Outlets
- USB cable
- DB9 cable
- EPO/ROO connector
- Rack-mounting hardware
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

#### Premium Protection from EMI/RFI Line Noise Helps Your Equipment Perform Better

This UPS system filters out disruptive electromagnetic and radio frequency interference that can inflict hardware damage or data loss. This EMI/RFI filtering also helps your connected components perform better and last longer.

# Designed for High Efficiency to Help You Save Money and Protect the Environment

A 97% efficiency rating reduces BTU emissions, energy consumption and, ultimately, your energy costs.

# Intuitive Front-Panel Interface for Convenient UPS Operation and Monitoring

The front-panel LCD features detailed UPS and site power status and operating data (including load, voltage and battery data) and multiple screens of configuration and setup options. LEDs indicate AC output availability and fault status. On-screen operational diagram offers an easy-to-grasp visual representation of line and battery modes.

## **Advanced Communications Ports Allow for Automatic Saves and Shutdowns**

RS-232 and HID-compliant USB ports connect to a computer running Tripp Lite's free downloadable PowerAlert® software to enable safe unattended shutdown in case of a prolonged power failure. The EPO/ROO port supports emergency shutdown in large facilities or Remote ON/OFF capability. USB and RS-232 cables are included.

# **Versatile Installation Options**

Hardware is included for mounting the UPS in just 1U of space in an EIA-standard 19-inch 4-post or 2-post rack. You can also adapt it for tower mounting using the included hardware. The six-foot power cord with NEMA 5-15P plug connects to a compatible AC outlet.

# **Specifications**

| _                                  |  |  |
|------------------------------------|--|--|
| OVERVIEW                           |  |  |
| UPC Code                           | 037332239297                             |  |
| UPS Type                           | Line-Interactive                         |  |
| INPUT                              |  |  |
| Rated input current (Maximum Load) | 6.44A (100V); 6.44A (120V); 6.09A (127V) |  |
| Nominal Input Voltage(s) Supported | 100V AC; 120V AC; 127V AC                |  |
| UPS Input Connection Type          | 5-15P                                    |  |
| Input Circuit Breakers             | (1) 10A                                  |  |
| UPS Input Cord Length (ft.)        | 6  |  |
| UPS Input Cord Length (m)          | 1.8                                      |  |
| Recommended Electrical Service     | 15A 120V                                 |  |
| Input Phase                        | Single-Phase                             |  |
| оитрит                             |  |  |
| Output Volt Amp Capacity (VA)      | 750                                      |  |
| Output Capacity (kVA)              | 0.75                                     |  |
| Output Watt Capacity (Watts)       | 600                                      |  |
| Output kW Capacity (kW)            | 0.6                                      |  |



| Output Capacity Details                    | 120VAC and 127VAC: 600W; 100VAC: 500W   |
|--|---|
| Power Factor                               | 0.8   |
| Nominal Voltage Details                    | 120V sinusoidal in line mode and 120V sinusoidal in battery mode  |
| Frequency Compatibility                    | 50 / 60 Hz  |
| Frequency Compatibility Details            | Output is regulated to +/-0.05Hz when input frequency exceeds +/-5Hz of nominal.  |
| Output Voltage Regulation (Line Mode)      | For 100V: 90VAC +/-5% -115VAC +/- 5% (78VAC +/- 5% -115VAC +/- 5%(@70VAC Input)) For 120V: 102VAC +/- 5% -139VAC +/- 5%, (78VAC +/- 5% -139VAC +/- 5%(@70VAC Input)), For 127V: 108VAC +/- 5% -145VAC +/- 5% (@70VAC Input))                |
| Output Voltage Regulation (Battery Mode)   | -10%, +6%   |
| Load Management Receptacles                | LOAD 1 (BANK OF 2 OUTLETS), LOAD 2 (BANK OF 2 OUTLETS)  |
| Output AC Waveform (AC Mode)               | Pure Sine wave  |
| Output AC Waveform (Battery<br>Mode)       | Pure Sine wave  |
| Nominal Output Voltage(s)<br>Supported     | 120V  |
| Output Receptacles                         | (4) 5-15R   |
| Individually Controllable Load Banks       | Yes   |
| BATTERY                                    |   |
| Battery Type                               | Valve Regulated Lead Acid (VRLA)  |
| Full Load Runtime (min.)                   | 3   |
| Half Load Runtime (min.)                   | 10  |
| Expandable Runtime                         | No  |
| DC System Voltage (VDC)                    | 24  |
| Battery Recharge Rate (Included Batteries) | 6 Hours to 90%  |
| Battery Access                             | Battery access door   |
| Internal UPS Replacement Battery Cartridge | RBC247-1U   |
| Battery Replacement Description            | Hot-swappable, user replaceable batteries   |
| VOLTAGE REGULATION                         |   |
| Voltage Regulation Description             | Automatic voltage regulation (AVR) maintains line power operation with input voltage as low as 90 (±5%). Input voltage range of 90 to 139   |
| USER INTERFACE, ALERTS & CON               | TROLS   |
| Front Panel LCD Display                    | Front panel LCD information and configuration screen offers detailed UPS and site power status and operating data plus configuration of voltage, frequency, operating mode, alarm function and a variety of additional options (see manual) |
| Switches                                   | ON button controls UPS ON, Cold-start, Self-test, and menu functions. OFF button controls unit off, fault clearance, and menu functions. Alarm/Enter button control audible alarm state and menu confirmation.                              |



| Alarm Cancel Operation  | Power-fail alarm can be silenced using alarm-cancel button   |  |
|---|--|--|
| Audible Alarm   | Audible alarm indicates power-failure, overload and low-battery conditions   |  |
| LED Indicators  | 2 LEDs indicate AC output status (Green); UPS fault (Solid Red)/ UPS abnormal conditions (Flashing Red).           |  |
|   |  |  |
| SURGE / NOISE SUPPRESSION                                     |  |  |
| AC Suppression Joule Rating                                   | 540  |  |
| AC Suppression Response Time                                  | Instantaneous  |  |
| PHYSICAL  |  |  |
| Primary Form Factor   | Rackmount; Tower   |  |
| Rack Height   | 1U   |  |
| Included Mounting Accessory<br>Description                    | Included mounting brackets provide front-rail installation in 2 or 4 post racks, plus upright tower configurations |  |
| Installation Form Factors Supported with Included Accessories | 2 post 19 inch rackmount; 2 post front mount; 4 post 19 inch rackmount; Tower                                      |  |
| Maximum Device Depth (cm)                                     | 28.60  |  |
| Maximum Device Depth (in.)                                    | 11.26  |  |
| Maximum Device Depth (mm)                                     | 286  |  |
| Minimum Required Rack Depth (cm)                              | 36.22  |  |
| Minimum Required Rack Depth (inches)                          | 14.26  |  |
| Primary UPS Depth (mm)  | 286  |  |
| Primary UPS Height (mm)                                       | 44   |  |
| Primary UPS Width (mm)  | 440  |  |
| UPS Housing Material  | Steel  |  |
| UPS Power Module Weight (kg)                                  | 13.50  |  |
| UPS Power Module Weight (lbs.)                                | 29.76  |  |
| ENVIRONMENTAL   |  |  |
| Operating Temperature Range                                   | +32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius  |  |
| Storage Temperature Range                                     | +5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius   |  |
| Relative Humidity   | 0 to 95%, non-condensing   |  |
| AC Mode BTU / Hr. (Full Load)                                 | 48   |  |
| AC Mode Efficiency Rating (100% Load)                         | 97%  |  |
| Operating Elevation (ft.)                                     | 3280 ft. (1000 m) above sea level  |  |
| Audible Noise   | 40 dBA maximum, front side 1m  |  |
| COMMUNICATIONS  |  |  |
| COMMUNICATIONS  |  |  |



| Connected Equipment Insurance (U.S., Canada & Puerto Rico)     | \$250,000 <a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>   |
|--|--|
| Extended Warranties  | 1-year 2-year, and 3-year extensions available   |
| Product Warranty Period<br>(Worldwide)                         | 2-year warranty, 3 year with registration. Note: <a class="insuranceLink" href="//www.tripplite.com/support/product-warranty-registration">Registration is required</a> for 3-year warranty.                 |
| WARRANTY   |  |
| Product Compliance   | ENERGY STAR Qualified; FCC Part 15 Class B (USA); RoHS   |
| Product Certifications   | CSA (Canada); NOM (Mexico); UL 1778  |
| STANDARDS & COMPLIANCE   |  |
| Grounding Lug  | Back panel grounding lug   |
| High Availability UPS Features                                 | Auto Probe Monitoring (requires WEBCARDLX); Automatic Voltage Regulation (AVR); Hot swappable batteries; Remote management; Surge/noise protection   |
| Cold Start (Startup in Battery Mode<br>During a Power Failure) | Cold-start operation supported   |
| FEATURES & SPECIFICATIONS                                      |  |
| High Voltage Transfer to Battery Power (Setpoint)              | 162 VAC (120VAC/127VAC INPUT), 139 VAC (100VAC INPUT) +/- 5%   |
| Low Voltage Transfer to Battery Power (Setpoint)               | 100V: 80VAC +/- 5% (HI sensitivity), 70VAC +/- 5%, (LO sensitivity), @120V: 89VAC +/- 5% (HI sensitivity), 70VAC+/- 5% (LO sensitivity), @127V: 93VAC+/- 5%, (HI sensitivity), 70VAC+/- 5%, (LO sensitivity) |
| Transfer Time  | 6-8 ms typical ( < 10 ms max)  |
| LINE / BATTERY TRANSFER  |  |
| Emergency Power Off/Remote On-<br>Off Details                  | Phoenix-style connection supports Emergency Power Off and Remote ON/OFF functions.   |
| Emergency Power Off<br>(EPO)/Remote On-Off (ROO)               | Yes  |
| Communications Interface                                       | (1) EPO (emergency power off); (1) RS-232; (1) USB (HID enabled)   |
| Network Management Card<br>Description                         | Network management card optional   |
| WatchDog Compatibility   | Supports Watchdog application, OS and hard-reboot restart options for remote applications  |
| Communications Cable   | USB and DB9 cabling included   |
| PowerAlert Software  | For local monitoring via the UPS's built-in communication ports, download PowerAlert Local software at https://www.tripplite.com/poweralert  |
| Network Monitoring Port Description                            | Supports detailed monitoring of UPS and site power conditions  |
| Network Management Cards                                       | (1) <a class="productLink" href="//www.tripplite.com/Web-Management-Accessory-Card~WEBCARDLX">WEBCARDLX</a>  |

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <a href="https://www.tripplite.com/products/product-certification-agencies">https://www.tripplite.com/products/product-certification-agencies</a>