

**PERFORMANCE****Processor**

Intel® Core™ i7-1255U, 10C (2P + 8E) / 12T, P-core 1.7 / 4.7GHz, E-core 1.2 / 3.5GHz, 12MB

**Graphics**

Integrated Intel Iris® Xe Graphics

**Chipset**

Intel SoC Platform

**Memory**

16GB Soldered DDR4-3200

**Memory Slots**

Memory soldered to systemboard, no slots, dual-channel (Intel i5 / i7 models)

**Max Memory**

16GB soldered memory, not upgradable

**Storage**

1TB SSD M.2 2280 PCIe® 4.0x4 NVMe®

**Storage Support**

Models with 57Wh battery: up to two drives, 1x 2.5" HDD + 1x M.2 SSD

- 2.5" HDD up to 1TB
- M.2 2242 SSD up to 512GB
- M.2 2280 SSD up to 1TB

**Storage Slot**

Models with 57Wh battery: one 2.5" drive slot + one M.2 slot

- One 2.5" SATA HDD slot
- One M.2 2280 PCIe 4.0 x4 slot

**Card Reader**

4-in-1 Card Reader

**Optical**

None

**Audio Chip**

High Definition (HD) Audio, Realtek® ALC3287 codec

**Speakers**

Stereo speakers, 2W x2, optimized with Dolby® Audio™

**Camera**

FHD 1080p with Privacy Shutter

**Microphone**

2x, Array

**Battery**

Integrated 57Wh

**Max Battery Life**

Models with 57Wh integrated graphics:

MobileMark® 2018@200nits: 8.5 hr

Local video (1080p) playback@150nits: 12.8 hr

**Power Adapter**

65W USB-C® (3-pin)

**DESIGN****Display**

15.6" FHD (1920x1080) IPS 300nits Anti-glare

**Touchscreen**

None

**Keyboard**

Backlit, English (US)

**Case Color**

Abyss Blue

**Surface Treatment**

Aluminium Stamping (Anodized)

**Case Material**

Aluminium (Top), Aluminium (Bottom)

**Dimensions (WxDxH)**

356.67 x 233.13 x 16.9 mm (14.04 x 9.18 x 0.67 inches)

**Weight**

Starting at 1.85 kg (4.08 lbs)

**SOFTWARE****Operating System**

Windows® 11 Home, English

**Bundled Software**

Office Trial

**CONNECTIVITY****Ethernet**

No Onboard Ethernet

**WLAN + Bluetooth®**

Wi-Fi® 6, 11ax 2x2 + BT5.1

**Standard Ports**

- 1x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 2x USB-C 3.2 Gen 1 (support data transfer, Power Delivery 3.0 and DisplayPort™ 1.2)
- 1x HDMI® 1.4b
- 1x Card reader
- 1x Headphone / microphone combo jack (3.5mm)

**SECURITY & PRIVACY****Security Chip**

Firmware TPM 2.0

**Fingerprint Reader**

Touch Style, Integrated in Power Button

**Other Security**

Camera privacy shutter

**SERVICE****Base Warranty**

1-year, Courier or Carry-in

**Included Upgrade**

None

**CERTIFICATIONS****Green Certifications**

- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

**Other Certifications**

TÜV Rheinland® Low Blue Light (Software Solution)

**Mil-Spec Test**

MIL-STD-810H military test passed

**MODEL**

TopSeller : No

EAN / UPC / JAN : 196379855515

Announce Date : 2022-05-06

End of Support : 2028-05-29



intel

· Lenovo reserves the right to change specifications or other product information without notice.

· Battery life is an estimated maximum. Actual battery life may vary by hardware or system settings, active applications, battery conditioning, etc.

· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

## Premium Care - Advanced Support from Real People. Real Fast.



### REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



### REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



### PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.



### HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

## Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

## Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

## Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

## Recommended Accessories



### Lenovo USB-C Mini Dock\_US

40AU0065US

Expand Your Potential with An Universal Mini Dock; Lenovo understands that modern business depends on a wide variety of PC's and even brands to meet their business needs. To make this easier Lenovo USB-C Mini dock is ...

## Recommended Services

BEST	3Y Premium Care Plus upgrade from 1Y Courier/Carry-in (5WS1J38674)
BETTER	3Y Onsite upgrade from 1Y Courier/Carry-in (5WS0K75721)
GOOD	3Y Courier/Carry-in upgrade from 1Y Courier/Carry-in (5WS0K75704)

For a full list of accessories and services, please visit:  
<https://smartfind.Lenovo.com>



**PSREF**  
Product Specifications  
Reference