

PERFORMANCE**Processor**

Intel® Core™ i7-12700H, 14C (6P + 8E) / 20T, P-core 2.3 / 4.7GHz, E-core 1.7 / 3.5GHz, 24MB

Graphics

NVIDIA® GeForce RTX™ 3060 6GB GDDR6, Boost Clock 1702MHz, TGP 140W

Chipset

Intel SoC Platform

Memory

2x 8GB SO-DIMM DDR5-4800

Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

Max Memory

Up to 32GB DDR5-4800 offering

Storage

2x 1TB SSD M.2 2280 PCIe® 4.0x4 NVMe®

Storage Support

Up to two drives, 2x M.2 SSD

- M.2 2242 SSD up to 512GB
- M.2 2280 SSD up to 1TB

RAID Preset

RAID 0

Card Reader

None

Optical

None

Audio Chip

High Definition (HD) Audio, Realtek® ALC3287 codec

Speakers

Stereo speakers, 2W x2, Nahimic Audio

Camera

HD 720p with E-camera Shutter

Microphone

2x, Array

Battery

Integrated 80Wh

Max Battery Life

Model with 80Wh battery:

MobileMark® 2018: 4.05 hr (discrete mode) or 6.68 hr (hybrid mode)

Power Adapter

300W Slim Tip (3-pin)

DESIGN**Display**

15.6" FHD (1920x1080) IPS 300nits Anti-glare, 165Hz, 100% sRGB, Dolby® Vision™, G-Sync, DC dimmer

Touchscreen

None

Keyboard

4-Zone RGB Backlit, English (US)

Case Color

Storm Grey

Surface Treatment

Anodizing

Case Material

Aluminium (Top), PC + ABS (Bottom)

Dimensions (WxDxH)

358.8 x 262.35 x 19.99 mm (14.13 x 10.33 x 0.79 inches)

Weight

Around 2.4 kg (5.3 lbs)

SOFTWARE**Operating System**

Windows® 11 Pro 64, English

Bundled Software

Office Trial

CONNECTIVITY**Ethernet**

100/1000M

WLAN + Bluetooth®

Wi-Fi® 6E 11ax, 2x2 + BT5.1

Standard Ports

- 2x USB 3.2 Gen 1
- 1x USB 3.2 Gen 1 (Always On)
- 1x USB-C® 3.2 Gen 2 (support data transfer and DisplayPort™ 1.4)
- 1x USB-C 3.2 Gen 2 (support data transfer, Power Delivery 135W and DisplayPort 1.4)
- 1x Thunderbolt™ 4 / USB4® 40Gbps (support data transfer and DisplayPort 1.4)
- 1x HDMI®, up to 8K/60Hz
- 1x Ethernet (RJ-45)
- 1x Headphone / microphone combo jack (3.5mm)
- 1x Power connector

SECURITY & PRIVACY**Security Chip**

Firmware TPM 2.0

Fingerprint Reader

None

Other Security

E-Camera shutter

SERVICE**Base Warranty**

1-year, Depot

Included Upgrade

1Y Legion Ultimate Support IdeaPad® 5 embedded (5WS0Y99554)

ACCESSORIES**Bundled Accessories**

None

CERTIFICATIONS**Green Certifications**

- ErP Lot 3
- RoHS compliant

MODEL

TopSeller : Yes

EAN / UPC / JAN : 196379335857

Announce Date : 2022-02-14

End of Support : 2028-02-29



intel

· Lenovo reserves the right to change specifications or other product information without notice.

· Battery life is an estimated maximum. Actual battery life may vary by hardware or system settings, active applications, battery conditioning, etc.

· California Electronic Waste Recycling Fee In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo 500 FHD Webcam

4XCOV13599

A USB Video Class (UVC) compliant video camera designed for teleconferencing applications on desktop or laptop. It's a reliable digital video device to transfer video data with HD quality through a high-speed USB interface.



Lenovo Powered USB-C Travel Hub

4X90S92381

Travel-Ready Productivity Powerhouse; One-stop travel docking is finally here. Connect and charge new and legacy devices wherever you happen to be. Sleek and compact, the Lenovo Powered USB-C Travel Hub fits unlimited...

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference