

Vertical Stacking Dual Monitor Arm

Part Number: K53802WW | UPC Code: 0 85896 53802 8

Mount your monitors vertically.

Whether you're trying to maximize your desk space, a security professional, gamer or simply want to expand top-to-bottom web browsing, the Vertical Stacking Dual Monitor Arm offers stable and secure vertical positioning of two monitors, each up to 32" (19.8lbs/9kg). Easy to install and adjust, the full-motion design offers monitor positioning in any direction, while the integrated cable management reduces clutter.

Features include:

- Dual vertical mounting holds two screens, each up to 32" (19.8lbs/9kg) in landscape orientation, 29" in portrait orientation
- Stacked monitors maximize desk space
- Quick-release handle for smooth and effortless monitor height adjustment
- Full-motion design
- Detachable ±180° rotatable VESA® 75/100 plates
- Pre-installed C-clamp (optional grommet mount included)
- Integrated cable management

Kensington

Vertical Stacking Dual Monitor Arm

Part Number: K53802WW | UPC Code: 0 85896 53802 8



Dual Vertical Mounting

Ideal for top-to-bottom web browsing, control rooms, gaming, or anywhere desk space is limited.



Maximizes Desk Space Stacked monitor arrangement allows two monitors in a single footprint.



Quick-Release Height Adjustment Handle

Offers smooth and effortless monitor height adjustment.



Full-Motion Design Allows flexible monitor positioning.



Detachable VESA® 75/100 Plates

Rotate ±180° for landscape or portrait orientation of each monitor. Holds two screens, each up to 32" (19.8lbs/9kg) in landscape orientation, 29" in portrait orientation.



Pre-Installed C-Clamp Makes installation easy

and provides a stable and secure base (optional grommet mount included).



Integrated Cable Management

Reduces clutter and keeps workspace tidy.



Warranty and Support

Backed by a two-year warranty and outstanding customer support, you can rest assured Kensington has you covered.

Kensington

Vertical Stacking Dual Monitor Arm

Part Number: K53802WW | UPC Code: 0 85896 53802 8

	Base	Steel with Powder Coating
	Pole	Steel with Powder Coating
	Joint	Steel with Powder Coating
	Base: C-clamp / Grommet	Steel with Powder Coating
Other Features		
	Compatibility	Compatible with Monitors with 75x75 or 100x100 VESA® Plates
Product Dimensions		
	Unit Dimensions with Peripherals (like cap)	114 x 148 x 988mm (4.5 x 5.8 x 38.9in)
	Unit Weight	4.22kg (9.30lbs)
	Unit Dimensions without Peripherals	114 x 148 x 988mm (4.5 x 5.8 x 38.9in)
	Enclosure Color & Material	Black
	Desktop Footprint	114 x 148cm (4.5 x 5.8in)
	Weight Capacity	Supports up to 19.8lbs (9kg) per monitor
	Screen Size Support	13"-32" (up to 29" for portrait mode)
Packaging Dimensions		
	Packaging Style	Brown Box
	Packaging Dimensions	600 x 142 x 147mm (23.6 x 5.59 x 5.79in)
	Packaging Weight	4.36kg (9.61lbs)
	Packaging Content	1 x Vertical Stacking Dual Monitor Arm (Including Installation Kit), 1 x User Manual, 1 x Warranty Card
Angle Adjustments		
	Tilt	+45° to -45°
	Swivel	+45° to -45°
	Screen Rotation	+180° to -180°
	Pole height	883mm (34.8")
	Upper Swivel Joint	+180° to -180°



All specifications are subject to change without notice. Products may not be available in all markets. Kensington and the ACCO name and design are registered trademarks of ACCO Brands. Kensington The Professionals' Choice is a trademark of ACCO Brands. All other registered and unregistered trademarks are the property of their respective owners. © 2022 Kensington Computer Products Group, a division of ACCO Brands. All rights reserved. k21-20027p

Kensington The Professionals' Choice

Kensington

Vertical Stacking Dual Monitor Arm

Part Number: K53802WW | UPC Code: 0 85896 53802 8

Installation (Clamp / Grommet)

	Desktop Thickness for C-clamp	10 - 88mm (0.39 - 3.46")	
	Desktop Thickness for Grommet	10 - 88mm (0.39 - 2.95")	
	Diameter for grommet mount	10 - 70mm (0.39 - 2.76")	
Country of Origin	n, Regulatory, and Warranty		
	Country of Origin	China	
	Certifications & Compliance	REACH, RoHS, Prop 65	
	Warranty	2-Year Limited	



All specifications are subject to change without notice. Products may not be available in all markets. Kensington and the ACCO name and design are registered trademarks of ACCO Brands. Kensington The Professionals' Choice is a trademark of ACCO Brands. All other registered and unregistered trademarks are the property of their respective owners. © 2022 Kensington Computer Products Group, a division of ACCO Brands. All rights reserved. k21-20027p

Kensington The Professionals' Choice