



# Poly Savi 7320-M Office Microsoft Teams Certified DECT 1920-1930 MHz Headset TAA (7E2L3AA)



## Overview

### Ensure secure conversations

Keep conversations private. With up to 2x better density, this secure DECT™ wireless headset is an ideal choice for financial, medical, government, and contact centers or anywhere sensitive conversations happen.

### DECT™ security

Savi 7300 headsets don't just meet security expectations, they exceed them with secure pairing, 128-bit authentication, and military-grade features, such as 256-bit AFS encryption. Conversations stay private and secure.

### Keep conversations private

Make sure nearby conversations are not overheard. The noise-canceling microphone enhanced with Poly Acoustic Fence technology, that meets the Microsoft Teams Open Office specification, private conversations stay private[1].

### Interference-free audio

With 2x better density than other DECT™ headsets, more people in shared spaces benefit from wireless headsets with clear, interference-free audio. IT can deploy more Savi 7300 Office Series compared to other DECT™ headsets without concern.

# Features

## DECT™ security standards

Designed to meet the highest-level DECT™ Security Step C enhanced with military-grade FIPS 140-2 listed features, such as 256-bit AES encryption.<sup>[2]</sup>

## Meet enterprise security needs

Ideal for use in financial, medical, and government environments, where Bluetooth® technology is typically banned.

## Remote management

Stay in control with remote device management for settings, firmware, and security updates.

## Roaming range

Give users more freedom to move with a line-of-sight wireless range of up to 580 ft/180 m.

## Works with you

Lasts through out the day with up to 13 hours of talk time. And a choice of wearing style accommodates all your users with monaural or stereo over-the-head (OTH) models.

## Communications platforms

An IT manager's dream, this headset was created for communication and is optimized and certified to work with top virtual meeting providers.<sup>[3]</sup>

---

*[1] Make sure nearby conversations are not overheard. The noise-canceling microphone enhanced with Poly Acoustic Fence technology, that meets the Microsoft Teams Open Office specification, private conversations stay private.*

*[2] DECT security standards can be found on <https://etsi.org>*

*[3] Visit <https://www.poly.com/savi-7300> for more detail*

## Additional specifications

<b>Acoustic protection technology</b>	SoundGuard Digital <sup>[1,2]</sup>
<b>Audio</b>	Noise and echo reduction
<b>Base controls</b>	Desk phone configuration; Softphone selector; Microsoft Teams button
<b>Base ringer</b>	Incoming calls (when not wearing the headset)
<b>Battery life</b>	Up to 13 hours (talk time); Up to 52 hours (standby time)
<b>Battery type</b>	Rechargeable Li-ion polymer
<b>Button user controls</b>	Call answer/end; Mute; Volume +/-; Power on/off; Microsoft Teams
<b>Certified collaboration software</b>	Microsoft Teams
<b>Charge time</b>	2 hours
<b>Color</b>	Black
<b>Connection type</b>	DECT™
<b>Connects to</b>	Desk phone; PC
<b>Ear cushions</b>	Artificial leather (surface material)
<b>Headphone type</b>	On-ear (stereo)
<b>Indicator light</b>	On call
<b>Management Software</b>	Plantronics Hub (desktop); Plantronics Manager Pro suites (Asset Management and Adoption, Call Quality and Analytics, Health and Safety)
<b>Manufacturer Warranty</b>	Poly standard two-year limited warranty
<b>Speaker size</b>	14.2 mm
<b>Special features</b>	Adjustable headband
<b>UNSPSC code</b>	52161514
<b>UPC number</b>	197192156407
<b>Voice alerts</b>	Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low
<b>Weight</b>	0.35 lb
<b>Weight</b>	160 g
<b>What's in the box</b>	Wireless headset; Office base; Micro USB to Type-A cable; Micro USB to Type-C® cable; USB Type-C® to USB Type-A cable; Telephone cable; Quick start guide
<b>Wireless range</b>	Up to 180 m in open area; Up to 55 m in typical office environment
<b>Wireless range (imperial)</b>	Up to 590 ft in open area; Up to 180 ft in typical office environment

---

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and

*controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).*

*[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.*

---

## Disclaimer — Copyright

© Copyright 2023 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Nov 15, 2023 6:58 AM UTC+0000