

PERFORMANCE

Processor

Intel® Core™ i5-12500, 6C (6P + 0E) / 12T, P-core 3.0 / 4.6GHz, 18MB

Graphics

Integrated Intel UHD Graphics 770

Chipset

Intel Q670 Chipset

Memory

16GB UDIMM DDR5-4400

Memory Slots

Four DDR5 UDIMM slots, dual-channel capable

Max Memory

Up to 128GB DDR5

Storage

256GB SSD M.2 2280 PCIe® 4.0x4 Value NVMe® Opal

Storage Support

Up to five drives, 2x 2.5"/3.5" HDD + 1x 2.5" HDD + 2x M.2 SSD

- 2.5" HDD up to 1TB each
- 3.5" HDD up to 2TB
- M.2 SSD up to 2TB

Optical

DVD±RW

Audio Chip

High Definition (HD) Audio, Realtek® ALC897Q-CG codec

Speakers

2Wx1

Power Supply

300W 90%

DESIGN

Keyboard

USB Traditional Keyboard, Black, English

Mouse

USB Calliope Mouse, Black

Expansion Slots

- One PCIe 4.0 x16, full-height, length ≤ 268.5mm, height ≤ 114.55mm
- One PCIe 4.0 x16 (x4 signal), full-height, length ≤ 205mm, height ≤ 114.55mm
- Two PCIe 3.0 x1, full-height, length ≤ 205mm, height ≤ 114.55mm
- Three M.2 slots (one for WLAN, two for SSD)

Case Color

Black

Stand

No stand

Form Factor

Tower (17L)

Dimensions (WxDxH)

170 x 298 x 376 mm (6.7 x 11.7 x 14.8 inches)

Weight

Around 6.5 kg (14.3 lbs)

CONNECTIVITY

Ethernet

Integrated 100/1000M

WLAN + Bluetooth®

Intel AX201 11ax, 2x2 + BT5.1

Front Ports

- 1x USB-C® 3.2 Gen 2 (support data transfer and 15W charging)
- 2x USB 3.2 Gen 1
- 2x USB 3.2 Gen 2
- 1x headphone / microphone combo jack (3.5mm)
- 1x microphone (3.5mm)

Rear Ports

- 4x USB 3.2 Gen 1
- 1x HDMI® 2.1 TMDS
- 2x DisplayPort™ 1.4
- 1x Ethernet (RJ-45)
- 1x line-out (3.5mm)

Optional Rear Ports (configured)

1x DP 1.2 (Flex IO)

SECURITY & PRIVACY

Security Chip

Discrete TPM 2.0, TCG certified

Fingerprint Reader

No fingerprint reader

Physical Locks

- Kensington® Security Slot™, 3 x 7 mm
- Padlock Loop

MANAGEABILITY

System Management

Non-vPro®

SERVICE

Base Warranty

3-year, Onsite

Included Upgrade

3Y Premier Support Upgrade from 3Y Onsite (5WSOV07841)

CERTIFICATIONS

Green Certifications

- EPEAT™ Silver
- ENERGY STAR® 8.0
- ErP Lot 3
- TCO Certified 9.0
- RoHS compliant

Mil-Spec Test

MIL-STD-810H military test passed (Low Pressure [Altitude], High Temperature, Low Temperature, Temperature Shock, Humidity, Sand and Dust, Vibration, Shock, Fungus, Solar Radiation, Contamination by Fluids, Salt Fog)

SOFTWARE

Operating System

Windows® 11 DG Windows 10 Pro 64, English

MODEL

TopSeller : Yes

Announce Date : 2022-08-30

EAN / UPC / JAN : 196802766234

End of Support : 2028-10-29



intel

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Kensington MicroSaver 2.0 Cable Lock from Lenovo

4XEON80914

Protect your device. Lenovo offers the latest standard in device security - the MicroSaver 2.0 Cable Lock From Lenovo. Engineered to be the smallest, strongest lock for laptops and other devices, the MicroSaver 2.0 re...

Recommended Services

| | |
|--------|--|
| BEST | 5Y Lenovo Protect (Premier Support + ADP + KYD + International Upg) (5PS1D67032) |
| BETTER | 5Y Lenovo Support (Premier Support + KYD + International Upg) (5PS1D67028) |
| GOOD | 4Y Lenovo Support (Premier Support + KYD + International Upg) (5PS1D67027) |

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>



PSREF
Product Specifications
Reference