



## ExpertBook B5 | B5402C

### Portable power for business on the go

ASUS ExpertBook B5 is built for business success in style, with a precision-crafted chassis that's as light as 1.25 kg. Powered by cutting-edge 11th Gen Intel® Core™ processor. ExpertBook B5 is your perfect portable, powerful partner for the corporate world.



Up to 11<sup>th</sup> Gen CPU



Ultra light



All-day battery life



Dual SSDs  
Support RAID 0, 1



US military grade



AI noise-canceling technology

### Ultimate portability

- Lightweight from 1.25 kg
- Aluminum and Mg-Al alloy chassis
- Up to **12hrs** of long battery life, support fast charging

### Exceptional performance for Business

- Up to 11th Gen Intel Core™ i7 processor with **Iris Xe** graphic
- Dual SSD up to **2TB** support Raid 0, Raid 1\*
- Up to **48 GB** DDR4 3200MHz Memory
- Full I/O ports with Thunderbolt™ 4, HDMI, USB type-A, RJ45 and micro SD card Reader
- **Two-way AI noise-canceling** technology with hot key

### Business Focus Design

- Up to WiFi 6E\* & ASUS WiFi Master provides seamless connection
- User-status indicator on the top cover
- ASUS exclusive NumberPad\*
- ErgoLift hinge for better cooling effect and typing experience

### Enterprise-grade durability and security

- **US Military Grade** durability to cope with business rigors on the road
- IR Camera\* for facial log in and webcam shield
- TPM 2.0 chip\*, Kensington lock slot, fingerprint sensor

\* Optional specification

### Warranty and Support



**3-Year global warranty**  
100% free of charge, with no hidden costs.



**Pick Up & Return service**  
Enjoy a door-to-door service including pick up, repair, and return.



**MyASUS App**  
Contact customer service, view repair status, read product guides and more.

# SPECIFICATION



Model	B5402C
Operating system	Windows 11 Pro(ASUS recommends Windows 11 Pro) Windows 11 Home
CPU	Intel® Core™ i7-1195G7 processor 2.9 GHz (12MB cache, up to 5.0 GHz, 4 cores) Intel® Core™ i5-1155G7 processor 2.5 GHz (8MB cache, up to 4.5 GHz, 4 cores)
GPU	Intel® Iris Xe graphics
Memory	1 x onboard, 1 x SO-DIMM, up to 48 GB DDR4 3200 MHz Onboard: 4 GB/8 GB/16 GB DDR4 3200 MHz SO-DIMM: 4 GB/8 GB/16 GB/32 GB DDR4 3200 MHz
Storage	2 x M.2 SSD, up to 2 TB PCIe® 3.0 SSD 256 GB/512 GB/1 TB M.2 PCIe®3.0 Value SSD 1 TB M.2 PCIe®3.0 Performance SSD
Display	14.0" FHD (1920 x 1080), value IPS, 16:9, wide view, anti-glare, 250 nits, 45% NTSC 14.0" FHD (1920 x 1080), IPS, 16:9, wide view, anti-glare, 400 nits, 100% sRGB 14.0" FHD (1920 x 1080), IPS, 16:9, wide view, anti-glare, 400 nits, low power, 72% NTSC
Stylus	Not available
I/O ports	2 x Thunderbolt™4 Type-C (supports 4K display, USB PD3.0 ), 1 x USB3.2 Gen2 Type-A 1 x USB2.0 Type-A, 1 x HDMI 1.4b, 1 x microSD card reader 1 x 3.5 mm combo audio jack, 1 x RJ45, 1 x Kensington Nano Security Slot
Video camera	1.0 MP camera with 720 P HD video, Webcam Shield IR camera with 720 P HD video, Webcam Shield
Wireless	Dual-band 2x2 WiFi 6E + Bluetooth® 5.2 Dual-band 2x2 WiFi 6 (802.11ax) + Bluetooth® 5.2
Audio	2 x speaker 2 x multi-array microphone ASUS two-way AI Noise-Canceling Technology Cortana voice-recognition support
Weight	Starting at 1.25kg
Dimensions (WxDxH)	32.34 x 22.31 x 1.79 cm
Battery	63 Wh, 3-cell, Li-polymer
Security	Fingerprint sensor(combo power button), TPM 2.0 (optional), IR Camera (optional), Webcam Shield , Kensington lock slot
Keyboard and touchpad	Full-size keyboard with 1.5 mm key travel; backlit (optional); spill-resistant to 66cc* *Quantity used during testing, with duration of 3 minutes
NumberPad	Optional
Featured software	ASUS Control Center (sold separately), ASUS Business Manager, MyASUS
AC adapter	USB Type-C®, 65 W; Output: 20 V DC, 3.25 A; Input: 100~240 V AC 50/60 Hz universal
Energy efficiency compliance	Energy star, EPEAT

Disclaimer :  
ASUS Expert Series Service Package may differ from country to country. We recommend that you check with your local dealers for the specifications of the products available in your country.


## Recommended Accessories



ASUS SimPro dock 2



ZenScreen MB165B



65W USB-C Ultra Mini  
Universal Adapter