



SPECIFICATIONS

Model Name	GeForce RTX™ 4070 Ti VENTUS 3X E 12G
Graphics Processing Unit	NVIDIA® GeForce RTX™ 4070 Ti
Interface	PCI Express® Gen 4
Core Clocks	Extreme Performance: 2625 MHz (MSI Center) Boost: 2610 MHz
CUDA® CORES	7680 Units
Memory Speed	21 Gbps
Memory	12GB GDDR6X
Memory Bus	192-bit
Output	DisplayPort x 3 (v1.4a) HDMI™ x 1 (Supports 4K@120Hz HDR, 8K@60Hz HDR, and Variable Refresh Rate as specified in HDMI™ 2.1a)
HDCP Support	Y
Power consumption	285W
Power connectors	16pin x 1
Recommended PSU	700W
Card Dimension (mm)	308 x 120 x 52mm
Weight (Card / Package)	1073g / 1667g
DirectX Version Support	12 Ultimate
OpenGL Version Support	4.6
Maximum Displays	4
G-SYNC® technology	Y
Digital Maximum Resolution	7680 x 4320

CONNECTIONS



1. DisplayPort
2. HDMI™

FEATURES



Triple Fan

Three fans and a huge heatsink ensure a cool and quiet experience for you.



TORX FAN 4.0

A masterpiece of teamwork, fan blades work in pairs to create unprecedented levels of focused air pressure.



Copper Baseplate

A solid nickel-plated copper baseplate transfers heat from the GPU to all heat pipes for better cooling.



Core Pipe

Precision-machined heat pipes ensure max contact to the GPU and spread heat along the full length of the heatsink.



Airflow Control

Don't sweat it, Airflow Control guides the air to exactly where it needs to be for maximum cooling.



Reinforcing Backplate

The reinforcing backplate features a flow-through design that provides additional ventilation.



MSI Center

The exclusive MSI Center software lets you monitor, tweak and optimize MSI products in real-time.



Afterburner

Take full control with the most recognized and widely used graphics card overclocking software in the world.