Legion T7 34IRZ8 90V60009US

Lenovo PSREF Product Specifications Reference

PERFORMANCE

Processor

Intel® Core™ i7-13700KF, 16C (8P + 8E) / 24T, P-core 3.4 / 5.3GHz. E-core 2.5 / 4.2GHz. 30MB

Graphics

NVIDIA® GeForce RTX™ 4080 16GB GDDR6X

Chipset

Intel Z790 Chipset

Memory

2x 16GB UDIMM DDR5-5600

Memory Slots

Four DDR5 UDIMM slots, dual-channel capable

Max Memory

Up to 64GB DDR5-5600

Storage

1TB SSD M.2 2280 PCIe® 4.0x4 NVMe®

Storage Support

Up to seven drives, 2x 3.5" HDD + 2x 2.5" HDD + 3x M.2 SSD

- 3.5" HDD up to 2TB
- 2.5" HDD up to 2TB
- M.2 SSD up to 2TB

Card Reader

None

Optical None

NOHE

Audio Chip

High Definition (HD) Audio, Realtek® ALC897 codec

Speakers

No speakers

Power Supply

850W 90%

DESIGN

Keyboard

USB Calliope Keyboard, Black, English

Mouse

USB Calliope Mouse, Black

Optional Bay

2.5" HDD bay

Expansion Slots

- One PCle 3.0 x1
- One PCIe 5.0 x16
- One PCle 4.0 x16 (x4 signal)
- Four M.2 slots (one for WLAN, three for SSD)

Case Color

Storm Grev

System Lighting

Legion Lighting + Internal Ambient Lighting

Chassis

None

Cooler

3x M.2 SSD Heatsink + 250W 360MM with RGB Light

System Fan

1x Rear + 2x Top with ARGB

Form Factor

Tower (34L)

Dimensions (WxDxH)

211 x 464 x 494 mm (8.3 x 18.26 x 19.44 inches)

Weight

17 kg (37.47 lbs)

CONNECTIVITY

Ethernet

2.5GbE RTL8125BG

WLAN + Bluetooth®

Wi-Fi® 6E, 11ax 2x2 + BT5.1

Top Ports

- 2x USB 2.0
- 2x USB 3.2 Gen 1
- 1x headphone (3.5mm)
- 1x microphone (3.5mm)

Rear Ports

- 1x USB-C® 3.2 Gen 2x2
- 2x USB 2.0
- 4x USB 3.2 Gen 1
- 1x USB 3.2 Gen 2
- 6x audio connectors (with SPDIF)
- 1x Lighting switch
- 1x Ethernet (RJ-45)

SECURITY & PRIVACY

Security Chip

Firmware TPM 2.0 integrated in chipset

MANAGEABILITY

SERVICE

Base Warranty

1-year, Mail-in

Included Upgrade

3Y Legion Ultimate Support with Onsite (5WS0V25263)

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 8.0
- ErP Lot 3
- RoHS compliant

SOFTWARE

Operating System

Windows® 11 Pro, English

Bundled Software

None

ACCESSORIES

MODEL

 TopSeller
 : Yes
 Announce Date
 : 2023-03-31

 EAN / UPC / JAN
 : 196804172514
 End of Support
 : 2028-12-07



intel

 $[\]cdot$ Lenovo reserves the right to change specifications or other product information without notice.

[·] Product image on this page is a sample, it may not match the real color of this model

Premium Care - Advanced Support from Real People. Real Fast.



REAL PERSON

Choose how you want to reach us through the phone, chat or email - our expert technicians will take care of you.



REAL FAST

Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.



HASSLE FREE

'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.



PC HEALTH CHECK

Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.



Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades – Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support

- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



intel



intel.



