

 **Poly Savi 8220 Top and Charging Cradle (85T31AA)**



Specifications

Audio	Active noise cancellation (ANC)
Package dimensions (W x D x H)	190 x 210 x 55 mm
Package weight	300 g
Battery life	>13 hours (talk time, over-the-head); >50 hours (standby time)
Special features	Adjustable headband
UPC number	(ABA) 197497580044; (ABB) 197497580068; (UUF) 197497580075
Manufacturer Warranty	Poly standard two-year limited warranty
What's in the box	Headset (top only)

Additional specifications

Acoustic protection technology	SoundGuard Digital ^[1,2]
Battery type	Rechargeable Li-ion polymer
Button user controls	Power on/off; Call answer/end; Mute; Volume +/-
Cartons per layer	6
Cartons per pallet	36
Certified collaboration software	Zoom
Charge time	3 hours
Color	Black
Connection type	USB Type-A
Connection type	Bluetooth®; USB Type-A
Connectivity	3-way base
Country of origin	Made in Mexico
ECCN	EAR99
Ear cushions	PC (polycarbonate) (surface material)
HTS code	8517620090
Headphone type	On-ear (stereo)
Impedance	32 ohms
Indicator light	On call
Management Software	Plantronics Hub (desktop)
Microphone bandwidth	35 Hz to 21 kHz
Microphone type	Omnidirectional
Multiple order quantity	12
Package dimensions (W x D x H)	7.48 x 8.26 x 2.16 in
Package weight	0.66 lb
Paired devices	Up to 2
Pallet (layers)	6
Pallet dimensions	40 x 48 x 58.66 in
Pallet dimensions (W x D x H)	101.6 x 121.9 x 149 cm
Pallet weight	787.05 lb
Pallet weight	357 kg
Products per pallet	432
Products per pallet layer	72
Sensitivity (microphone)	-40 +/-3 dB

Signal-to-noise ratio	>53 dB
Speaker bandwidth	20 Hz to 20 kHz (media mode)
Speaker size	32 mm
Supported bluetooth profiles	A2DP; AVRCP; HFP; HSP
UC compatibility	Standard
UNSPSC code	43191638
Voice alerts	Volume maximum; Volume minimum; Mute on; Mute off; Muted; Connection status; Talk time; Battery low
Wearing style	Stereo
Wireless range	Up to 180 m in open area; Up to 55 m in typical office environment
Wireless range (imperial)	Up to 590 ft in open area; Up to 180 ft in typical office environment

[1] SoundGuard Digital Plantronics owns sophisticated algorithms including: Protects against Acoustic Shock by limiting sounds to below 118 dBA; G616 anti-startle protection that limits the noise level to below 102 dB SPL and is therefore compliant to the Australian Communications Industry Forum (ACIF) G616 recommendation; Average daily noise exposure measures and controls sound to prevent the average daily sounds exposure from exceeding 80 dBA or 85 dBA time-weighted average (TWA).

[2] Requires Poly Lens Desktop App to enable SoundGuard Digital features.

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Oct 15, 2024 9:47 AM UTC+0000