

ESG620



Gateway6 8mG 2SFP+

Cloud SD-WAN Gateway with 8x 2.5-Gigabit (4 PoE+) Ethernet ports and two SFP+ slots

Overview

EnGenius ESG620 SD-WAN gateway provides a high-performance network solution with advanced features, including load balancing, dual-WAN, and site-to-site VPN. The product offers unified management through EnGenius Cloud, allowing for easy configuration and management from anywhere. It offers a comprehensive end-to-end solutionfor businesses seeking to enhance their network performance and security.



Features & Benefits

- Simple, unified cloud management for any size business
- Intuitive and centralized device visibility from anywhere
- Dual WAN ports with 1x SFP+ and 1x 2.5GbE
- Quad-core 2.2 GHz processor for greater speed and power
- Built-in load balancing and safeguards with dual-WAN and cellular failover
- 4 x 2.5 GbE PoE+ to power up multiple Wi-Fi 6E AP, IP camera or IP phone

- Stateful firewall with high-efficiency filtering and inspection to enhance security
- High-speed and secure site-to-site VPN and client VPN
- Quick self-healing VPN and VLAN setup for faster and easier deployments
- Touchless system maintenance and automatic updates
- Multiple passthrough and routing options
- Captive portal with external radius capabilities

1

Technical Specifications

CPU Processor	
Quad Core	
Operating Frequency	
2.2GHz	
Memory	
8GB	
Flash Storage	
16GB	
RJ-45 Interface	
8x2.5G	
SFP interface	
2 x SFP+	
PoE ports	
4	
PoE Standard	
802.3 af/at	
I/O Interfaces	
1 x RJ-45 console/1 x USB 3.0	
Mounting Method	
Rack mount	
Security	
TPM	

Perfomance & Capacity	
Firewall (SPI throughput)	

7.7G

VPN throughput

1.5G

1.56

Max. Concurrent VPN Tunnels

300

Max. Concurrent VPN Users

380

Max. TCP Concurrent Sessions

1,250,000

Max VLAN

160

Firewall

Firewall Features

Stateful Packet Inspection

Policy Rules

Port Forwarding

1:1 NAT

Allow Inbound Services

Site-to-Site VPN	
Mesh VPN/ Hub-and-Spoke	
Encryption	
3DES, AES (256/192/128-bit)	
Authentication	
MD5, SHA1, SHA2 (256-bit)	
Key Managment	
IKEv1 (x-auth, mode-config)	
IKEv2 (EAP, configuration payload)	
VPN Features	
Site-to-Site VPN	
Client VPN(IPsec/SecuPoint SSL)	
Policy-based VPN	
IPSec NAT traversal (NAT-T)	
Dead Peer Detection (DPD)	
Auto-VPN Connection	
Auto NAT traversal	

Networking	
Operation mode	
Routed / Passthrough	
Multiple WANs	
Dual	

Bandwidth Limit
Per client/ Per Interface

Traffic Load Balancing
WAN load balancing with WRR

Networking Features

Static Route
Multiple WANs

USB Cellular

User Authentication

PPPoE

VPN

VLAN Tagging

Captive Portal

Custom Splash Page

Bandwidth Limit

Traffic Load Balancing


DHCP client/server/relay

Dynamic DNS support

Technical Specifications

Environmental & Physical	
Power	
intermal 300w power	
Operation Temperature	
0°C to 40°C	
Humidity (non-condensing)	
5 to 95% non-condensing	
Dimensions & Weight	
Dimensions	
Width: 330mm	
Length: 230mm	
Height: 44mm	
Package Contents	
Power cord	
RJ-45 Console Cable	
Rack Mount Kit	
Product Card	
Compliance	
Regulatory Compliance	
FCC Part 15 (Class B)	
IC	
CE EMC	
CB	
UL	

Hardware Overviews



EnGenius Technologies | Costa Mesa, California, USA

Emaill: support@engeniustech.com
Website: www.engeniustech.com
Local contact: (+1) 714 432 8668

EnGenius Networks Singapore Pte Ltd. | Singapore

Emaill: techsupport@engeniustech.com.sg
Website: www.engeniustech.com.sg
Local contact: (+65) 6227 1088

EnGenius Technologies Canada | Ontario, Canada

Email: support@engeniustech.com
Website: www.engeniustech.com
Local contact: (+1) 905 940 8181

EnGenius Networks Dubai | Dubai, UAE

Emaill: support@engenius-me.com
Website: www.engenius-me.com
Local contact: (+971) 4 339 1227

EnGenius Networks Europe B.V. | Eindhoven, Netherlands

Email: support@engeniusnetworks.eu Website: www.engeniusnetworks.eu Local contact: (+31) 40 8200 887

恩碩科技股份有限公司 | Taiwan, R.O.C.

Email: sales@engeniustech.com.tw
Website: www.engeniustech.com.tw
Local contact: (+886) 933 250 628

Features and specifications subject to change without notice. Trademarks and registered trademarks are the property of their respective owners. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses, and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. Operation of this equipment in a residential area is likely to cause harmful interference in which case the user will be required to correct the interference at his/her own expense. Prior to installing any surveillance equipment, it is your responsibility to ensure the installation is in compliance with local, state and federal video and audio surveillance and privacy laws.

