



## SPECIFICATIONS

Panel Size	26.5"(67.31cm)
Active Display Area (mm)	590.42(H) x 333.72(V)
Curvature	Flat
Panel Type	QD-OLED
Panel Resolution	2560x1440 (WQHD)
Pixel Pitch (H x V)	0.2292(H) x 0.2292(V)
Aspect Ratio	16:9
Brightness (nits)	250 (Typ.)
Contrast Ratio	1500000:1 (Typ.)
DCR	N/A
Signal Frequency	30~585 KHz(H) / 48~360 Hz(V)
ACTIVATED RANGE	48~360Hz
Refresh Rate	360Hz
Response time	0.03ms (GtG)
DYNAMIC REFRESH RATE TECHNOLOGY	Adaptive-Sync
HDR Support	DisplayHDR True Black 400
Video ports	1 x DisplayPort (1.4a) 2 x HDMI™ (2.1) 1 x Type-C (DP alt.) w/PD 15W
USB ports	N/A
Audio ports	1 x Headphone-out
Viewing Angle	178°(H) / 178°(V)
Adobe RGB / DCI-P3 / sRGB	98% / 99.1% / 138.4%
Surface Treatment	Anti-Reflection
Display Colors	1.07B, 10 bits
Power Type	Power Cable
Power Input	100~240V, 50/60Hz
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	30° ~ 30°
Adjustment (Pivot)	-90° ~ 90°
Adjustment (Height)	0 ~ 110mm
Kensington Lock	Yes
Dimension (W x D x H)	609 x 242 x 416mm 609 x 72 x 362mm (without stand)
Carton Dimension (W X D X H)	WW carton: 800 x 185 x 500mm Outer: 818 x 200 525 mm
Frameless Design	Yes

## FEATURES



### QD-OLED Display

MSI's renowned QD tech, combined with the latest OLED panel technology, these displays exhibit the best picture quality and incredible high contrast when gaming



### 360Hz High Refresh Rate

Experience smooth gaming with a blazing fast refresh rate, that gives you the upper hand in fast-moving games.




### Fastest 0.03 Response time

Response time is much faster and smoother than conventional LCD displays. The response time is up to 0.03 ms GtG exceeds the most mainstream refresh rates requirements.



### OLED Care 2.0

MSI has developed a more advanced version to provide several care services and significantly reduce the chances of OLED screen aging.



### Graphene film with Custom Heatsink

Graphene film and customized heatsink designs, the synergy between these two elements enables monitor to operate without an active cooling fan, achieving a fanless design. This ensures efficient and silent heat dispersion, further extending the panel's lifespan.

VESA CERTIFIED




### VESA DisplayHDR True Black 400

It has passed the VESA DisplayHDR True Black 400 Certification, meaning it can provide a display with the most realistic colors.

<b>PIP / PBP Function</b>	Yes
<b>VESA Mounting</b>	100 x 100 mm
<b>Weight (NW / GW)</b>	8 kg / 10.3 kg
<b>Note</b>	Display Port: 2560 x 1440 (Up to 360Hz) HDMI 2.1: 2560 x 1440 (Up to 360Hz) Type C(DP alt.): 2560 x 1440 (Up to 360Hz) and 15W PD charging *sRGB and DCI-P3 follow CIE1976 standard

## CONNECTIONS



1. AC Power Jack
2. 5-way Joystick Navigator
3. 2 x HDMI™ (2.1)
4. Display Port (1.4a)
5. USB Type-C (PD 15W)
6. Earphone out
7. Kensington lock