

# Product datasheet

Specifications



APC Easy UPS On-Line,  
2000VA/1600W, Rackmount 2U,  
230V, 4x IEC C13 outlets, Intelligent  
Card Slot, LCD, Extended runtime,  
No Battery, W/O rail kit

SRVPM2KRIL

## Overview

Presentation	High quality, Double-conversion On-line UPS designed for essential power protection needs even in the most unstable power conditions.
Lead time	Usually in Stock

## Main

Main Input Voltage	230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated power in W	1600 W
Rated power in VA	2000 VA
Input Connection Type	IEC 60320 C14
Output connection type	4 IEC 60320 C13
Number of rack unit	2U
Number of cables	1
Provided equipment	1 IEC 60320 C13 to Schuko power cable 1 IEC 60320 C13 to C14 power cable 1 USB cable 1 RS-232 configuration cable user manual

## General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No

## Physical

Colour	Black (RAL 7010)
Height	8.6 cm
Width	43.8 cm

Depth	46.2 cm
Net weight	9.2 kg
Mounting location	Front
Mounting preference	Lower
Mounting mode	Rack-mounted with kit
USB compatible	No
Mounting position	Horizontal

## Input

Input voltage limits	110...285 V half load 160...280 V full load
Network frequency	40...70 Hz auto sensing

## Output

Maximum configurable power in VA	2000 VA
Maximum configurable power in W	1600 W
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Harmonic distortion	3 %
UPS type	Double conversion online
Wave type	Sine wave
Efficiency	88 % (full load)
Additional information	Configurable for 220 : 230 or 240 nominal output voltage
Bypass type	Internal bypass (automatic and manual)
Crest factor	3 : 1

## Conformance

Product certifications	CE UKCA EAC TISI
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3000 m
Ambient air temperature for storage	-20...50 °C
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0...15000 m
Acoustic level	50 dBA
IP degree of protection	IP20

## Batteries & Runtime

Battery type	External battery system
Battery voltage	72 V
Number of battery filled slots	0
Number of battery free slots	0
Battery charger power	350 W rated

## Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Control panel	Multifunction LCD status and control console

## Surge Protection and Filtering

Surge energy rate	600 J
-------------------	-------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	24 cm
Package 1 Width	54.5 cm
Package 1 Length	70 cm
Package 1 Weight	13.4 kg

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

## Recommended replacement(s)