

# LG gram SuperSlim

## Unbelievably Thin, Uncompromisingly Light

## LG gram SuperSlim with OLED Display

15Z90RT



- Windows 11 Pro Operating System
- 15.6-inch Large OLED Display with Anti-glare Low Reflection Panel
- True Black with 1M:1 Contrast Ratio
- 13th Gen Intel<sup>®</sup> Core<sup>™</sup> Processor
- Dolby Atmos & Smart Amp
- 60 Wh Long-lasting Battery



### Practical Design Optimized for Portability

#### 0.5-inch Slim Body & 2.18 lb. Ultra-lightweight | 60Wh High-capacity Battery | Mini Adapter

Solid, sturdy, and backed by military-grade durability testing<sup>1</sup>, LG gram SuperSlim is a powerhouse for demanding tasks. Its ultra slim 0.4-inch body weighs a mere 2.18 pounds, making it ultra-thin and compact enough to fit on your lap on a train or plane for those consulting with clients or creating projects on the move. What's more, its ultra-lightweight casing features a high capacity 60W battery, so users can work virtually anywhere without having to constantly worry about charging. It also comes with a portable Mini Adapter that packs up easily to minimize disruption on those long business trips.

gram

### Vivid Viewing with Extraordinary Detail

#### OLED Display with Anti-glare Low Reflection Panel | 1M:1 Contrast Ratio | DCI-P3 100% | 0.2ms Response Time

Featuring an OLED Display with Anti-glare Low Reflection, LG gram SuperSlim delivers captivating image quality with remarkable detail in brightly lit or darkened environments, making it ideal for editing media-rich documents and rendering video content. In addition, its astonishing 1M:1 contrast ratio brings out perfect blacks as they were meant to be seen, while its 100% DCI-P3 color range ensures optimal expression when showcasing creative content for true-to-life viewing. And with ultra-fast 0.2ms response times, users are granted fluid viewing when web conferencing, scrolling, or simply streaming content.

### **Multitasking Powerhouse**

#### 13th Gen Intel<sup>®</sup> Core<sup>™</sup> Processor | LPDDR5 6000 MHz RAM | Gen 4 NVMe Dual SSD | Dolby Atmos & Smart Amp

Bundled with the 13th Gen Intel<sup>®</sup> Core<sup>™</sup> processor, LG gram SuperSlim is robust enough to accelerate performance in the most intensive work environments, whether documenting intensive demands of any workstation, from documenting to content creation and streaming. Add to this both LPDDR5 memory and the 4th generation NVME SSD, which allow users to handle more sizeable workloads and manage multiple tasks with supreme efficiency. Lastly, its built-in Dolby Atmos speaker system and Smart Amp provide rich, full three-dimensional sound during video conferencing or streaming.

\*Images shown are for illustration purposes only.

1) MIL-STD 810H certification based on a series of seven tests (low pressure, high and low temperatures, salt fog, dust, vibration, and shock) conducted by an independent laboratory that conforms to strict US military standards.

## Specifications

| Model      |                           | 15Z90RT-N.APB7U1 and 15Z90RT-N.APB4U1  |
|------------|---------------------------|--|
|            |                           |  |
| System     | Operating System          | Windows 11 Pro   |
|            | CPU                       | 13 <sup>th</sup> Gen Intel <sup>®</sup> Core™ i7-1360P (15Z90RT-N.APB7U1)<br>13 <sup>th</sup> Gen Intel <sup>®</sup> Core™ i5-1340P (15Z90RT-N.APB4U1) |
|            | Memory                    | 16 GB LPDDR5 (Dual Channel, 6,000 MHz)   |
|            | GPU                       | Intel <sup>®</sup> Iris <sup>®</sup> Xe graphics   |
| Display    | Size                      | 15.6-inch  |
|            | Aspect Ratio              | 16:9   |
|            | Panel Type                | Anti Glare Low Reflection, OLED  |
|            | Resolution                | FHD (1920x1080)  |
|            | Brightness                | Normal 400 nits Brightness, HDR Peak Brightness 500 nits   |
|            | Color Gamut (Typ. / Min.) | DCI-P3 100% / 90%  |
|            | Refresh Rate              | 60 Hz  |
|            | Response Time             | 0.2 ms   |
| Signal     | Storage                   | 1 TB NVMe Gen4 (15Z90RT-N.APB7U1)<br>512 GB NVMe Gen4 (15Z90RT-N.APB4U1)   |
|            | Connectivity              | Headphone Out (4Pole Headset, 3.5 mm), USB 4 Gen 3x2 Type C (x2, with Thunderbolt™ 4,  |
|            |                           | Power Delivery, DisplayPort), USB 3.2 Gen 2x1 (x1, with Power Delivery, DisplayPort)   |
| Webcam     |                           | Full HD IR Webcam with Dual Mic (Facial Recognition System)  |
| Speakers   |                           | Stereo Speakers 2.0W x2 with Smart Amp, Dolby Atmos  |
| Battery    |                           | 60 Wh  |
| Mechanical | Dimensions                | 14.0 x 9.0 x 0.5 in.<br>356 x 227.45 x 12.55 mm  |
|            | Weight                    | 2.18 lbs / 990 g   |
| Color      |                           | Neptune Blue   |
| SW         |                           | Intel® Unison™, LG Smart Assistant (Including OLED Panel Care, Lively Theme, Display Extension),   |
|            |                           | Sync On Mobile, PCmover Professional   |
| Security   |                           | LG Security Guard, LG Glance by Mirametrix®  |
| Warranty   |                           | 3 Year Limited   |

\*Specifications are subject to change without notice, so please reach LG sales team to ensure before ordering.

https://www.facebook.com/LGcommercialdisplays
https://www.linkedin.com/company/lg-commercial-displays-usa
https://www.youtube.com/lgcommercialdisplayusa

Copyright 2023 <sup>®</sup>LG Electronics USA, Inc., 2000 Millbrook Drive Lincolnshire, IL 60069, USA. All rights reserved. LG and the LG logo are registered trademarks of LG Corp. All other products and brand names are trademarks or registered trademarks of their respective companies. Designs, features, and specifications are subject to change without notice. All screen images are simulated. SPEC\_15290RT gram SuperSlim\_072351\_LR1

