

Product datasheet

Specifications



APC Back-UPS Pro for Gaming, 2200VA/1320W, Tower, 230V, 6x Australian outlets, RGB Lights, Pure Sine Wave, Arctic (White)

BGM2200-AZ

Overview

Lead time Usually in Stock

Main

Main Input Voltage 230 V AC 1 phase

Other Input Voltage 230 V

Main Output Voltage 230 V 1 phase

Rated power in W 1320 W

Rated power in VA 2200 VA

product or component type Uninterruptible power supply (UPS)

Input Connection Type Australian

output connection type 3 Australian
3 Australian surge

Cable length 1.5 m

Number of cables 1

Battery type Lead-acid battery

Batteries & Runtime

Run Time [View Runtime Graph](#)

Efficiency [View Efficiency Graph](#)

Number of battery filled slots 1

Number of battery free slots 0

Battery recharge time 16 h

Number of battery replacement quantity 1

Battery voltage 24 V

Overcurrent protection 15 A

Battery charger power 12 W rated

Battery life 3...5 year(s)

General

Provided equipment safety guide
USB cable
power cable

product web sub-family Gaming performance

| | |
|-----------------------------------|----|
| Number preinstalled power module | 0 |
| Number of power module free slots | 0 |
| Redundant | No |

Physical

| | |
|---------------------|--------------------|
| Colour | White |
| Height | 292.1 mm |
| Width | 104.1 mm |
| Depth | 408.9 mm |
| net weight | 12.56 kg |
| mounting support | Floor |
| Mounting preference | No preference |
| mounting mode | Not rack-mountable |
| Two post mountable | 0 |
| USB compatible | Yes |
| Mounting position | Vertical |

Input

| | |
|----------------------------|-----------------------------|
| Network frequency | 50/60 Hz +/- 3 Hz |
| plug standard | Australian |
| Input voltage limits | 168...302 V |
| Maximum input current | 12 A |
| Switching current capacity | 15 A |
| Input harmonic distortion | Less than 3 % for full load |
| Input protection type | Circuit breaker |

Output

| | |
|----------------------------------|---------------------------------|
| Maximum configurable power in W | 1320 W |
| Output frequency | 50/60 Hz +/- 3 Hz sync to mains |
| UPS type | Line interactive |
| Wave type | Sine wave |
| Full load runtime | 00:30:00 |
| Half load runtime | 00:05:30 |
| Maximum configurable power in VA | 2200 VA |
| Transfer time | 8 ms typical : 10 ms maximum |

Conformance

| | |
|-----------------------------|---------------------|
| Product certifications | CE CB |
| Equipment protection policy | Lifetime : \$150000 |

Environmental

| | |
|---------------------------------------|----------------------------------|
| Ambient air temperature for operation | 0...40 °C |
| Relative humidity | 0...95 % |
| Operating altitude | 0...10000 ft |
| Ambient air temperature for storage | -15...40 °C |
| Storage Relative Humidity | 0...95 % |
| Storage altitude | 0.0000000000...3048.0000000000 m |
| Acoustic level | 45 dBA |
| IP degree of protection | IP20 |

Communications & Management

| | |
|---------------|--|
| Free slots | 0 |
| control panel | Multifunction LCD status and control console |
| Alarm | Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm |

Surge Protection and Filtering

| | |
|-------------------|--|
| Surge energy rate | 1080 J |
| Noise suppression | Full time multi-pole noise filtering : 5% of IEEE surge let-through : zero clamping response time: instantaneous |

Packing Units

| | |
|------------------------------|----------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 15.5 cm |
| Package 1 Width | 35.5 cm |
| Package 1 Length | 48 cm |
| Package 1 Weight | 14.38 kg |

Contractual warranty

| | |
|----------|---|
| Warranty | 2 years repair or replace, 3 years repair or replace for European Union countries |
|----------|---|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

RoHS Exemption Information Yes

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |