# 27BR530Y-B IPS Multi-tasking Monitor



## **FEATURES**

#### FLICKER SAFE

• Flicker Safe reduces on-screen flickers, which gives viewers a clearer view. By combining Flicker Safe with the proven picture quality of IPS technology, users can comfortably work throughout the day.

#### **READER MODE**

• With the touch of a button, Reader Mode reduces blue light emissions for a more comfortable viewing experience.

#### SMART ENERGY SAVING

• LG's Smart Energy Saving Mode reduces power consumption without lowering the brightness of the monitor.

## COLOR CALIBRATED

• Experts have conducted color calibration tests at the production line so that colors reproduced just as content creators intended.

## **SPECIFICATIONS**

Native Display Resolution: 1920 x 1080

Contrast Ratio: 1000:1

5 ms (G to G) Response Time

Vesa™ Compliant Wall Mountable

3-Year Limited Warranty: Parts/Labor/Backlight

TAA Compliant

www.LG.com/us/commercial



## FULL HD IPS DISPLAY

Designed for professionals, this Full HD display with IPS technology minimizes color shifts and provides outstanding picture quality from virtually any viewing angle.

### INTEGRATED POWER MODULE FOR ORGANIZED WORKSPACES

The power module is integrated with the monitor, helping to reduce the amount of power modules in your workspace.





#### PERSONALIZED VIEWING ANGLES AND EASY ASSEMBLY

The monitors provide comfortable viewing with versatile screen height/tilt/pivot/swivel adjustments. You can customize the display condition to create a more personal, comfortable workstation. The monitor can be easily assembled without any tools, and is also able to be wall-mounted\*.

\* Wall mount sold separately



## **27BR530Y-B** IPS Multi-tasking Monitor

	MODEL	27BR530Y-B		MODEL	27BR530Y-B
DISPLAY	Diagonal	27685501-В 27"	SOUND	Speaker	YES
	5				2W
	Resolution	1920 x 1080		Speaker_Output (unit)	
	Panel Type	IPS		Speaker_Channel	2ch
	Backlight Technology	LED		Speaker_Direction	Down Firing
	Backlight Type	Edge		Output_Frequency	150Hz - 20KHz
	Backlight Array	H1B	ELECTRICAL	Туре	Built-in Power
	Backlight Dimming Technology	Global Dimming		AC Input DC Output	100-240 Vac, 50/60Hz N/A (PSU)
	Aspect Ratio	16:9			
	Pixel Pitch	0.3114 x 0.3114 mm		Power Consumption	27W
	Brightness (Min.)	200 nits		(Тур.)	
	Brightness (Typ.)	250 nits		Power Consumption (Max.)	39W
	Color Gamut (Min.)	NTSC 72% (CIE1931)			
	Color Gamut (Typ.)	NTSC 72% (CIE1931)		Power Consumption	
	Color Depth (Number of Colors)	16.7M		(Energy Star)	14.3W
	Color Bit	8bit (6bit+FRC)		Power Consumption	
	Contrast Ratio (Min.)	700:1		(Sleep Mode) Power Consumption (DC Off)	Less than 0.3W Less than 0.3W
	Contrast Ratio (Typ.)	1000:1			
	Contrast Ratio with DFC	Mega			
	Response Time	5ms (GtG at Faster)			
	Viewing Angle (CR≥10)	178° (R/L), 178° (U/D)		Borderless Design	3-Side Virtually Borderless Design
	Surface Treatment	Anti-Glare treatment of the front polarizer (Haze25%, 3H)		Color (Front Cabinet)	Black Texture
FEATURES	Color Calibrated	YES		Color (Middle Cabinet)	Black Texture
	Flicker safe	YES		Color (Back Cover)	Black Texture
	Picture Mode	Custom, Reader, Photo, Cinema, Color Weakness, Game		Color (Stand Body)	Black Texture
	Reader Mode	YES		Color (Stand Base)	Black Texture
	Color Weakness	YES		Display Position	
	Super Resolution+	YES		Adjustments	Tilt/Height/Swivel/Pivot
	Black Stabilizer	YES		-	
	Dynamic Action Sync	YES	MECHANICAL	Tilt	-5° to +35°
	Crosshair	YES		Swivel	0° to 355° (🛛 5°)
	Smart Energy Saving	YES		Height Range	130mm
	5,5 5	18 countries English, Germanic, French, Spanish, Italian, Swedish, Finnish, Portuguese, Polish, Russian, Greek, Chinese, Japanese, Korean, Ukrainian, Portuguese(brazil), Hindi, Tranditional Chinese		Down Height	50mm
	OSD Language			Pivot	Bi-Directional
				Wall Mountable	100 x 100 mm
				Base Detchable	YES
	Dual Controller	YES		Assembly Step	Three-Step
	OnScreen Control /			OneClick Stand	YES
	Switch	YES		Dimensions with Stand	TBD
CONNECTIVITY	DVI	YES (1ea)		(W x H x D)	
	DVI (V Frequency)	56-60Hz		Dimensions without	24.1 x 14.3 x 2.0 in.
	DVI (Max Resolution at Hz)	1920 x 1080 @ 60Hz		Stand (W x H x D)	611.7 x 364.1 x 50.3 mm
	HDMI	YES		Shipping Dimensions	TBD
	HDMI Version	1.4		$(W \times H \times D)$	
	HDMI (HDCP Version)	1.4		Weight with Stand	TBD
	HDMI (V Frequency)	48-75Hz		Weight without Stand	11.5 lbs. / 5.2kg
				Shipping Weight	TBD
	HDMI (FreeSync Supported Frequency)	48-75Hz	CERTIFICATIONS & STANDARDS WARRANTY & OTHER	EPA 8.0	YES
				TUV-GS	YES
	HDMI (Maxy Decelution at LI=)	1920 x 1080 @ 75Hz		TUV-Ergo	YES
	(Max. Resolution at Hz)	-		СВ	YES
	DisplayPort	YES(1ea)		UL (cUL)	YES
	DP Version	1.2		FCC-B	YES
	DP (HDCP Version)	1.4		EPEAT (USA)	YES
	DP (V Frequency)	48-75Hz		CE	YES
	DP (FreeSync Supported Frequency)	48-75Hz		Warranty	3 Year Limited
	DP (Max. Resolution at			UPC Code	1 95174 06561 7
	Hz)	1920 x 1080 @ 75Hz			135174003017
	USB Upstream Port	YES (1ea), Ver 3.0		Power Cord (Color/Length)	Black / 1.8m
	USB Downstream Port	YES (2ea), Ver 3.0			
	Audio In	YES		Display Port Cable	Plack / 1.0-
	Headphone out	YES		(Color/Length)	Black / 1.8m
		-			





https://www.lg.com/us/business/commercial-display

https://www.twitter.com/LGCommDisplays

f https://www.facebook.com/LGcommercialdisplays

https://www.linkedin.com/company/lg-commercial-displays-usa

https://www.youtube.com/lgcommercialdisplayusa

LG Electronics U.S.A., Inc. HE B2B Division 2000 Millbrook Drive Lincolnshire, IL 60069

Customer Service: 888.865.3026 www.LG.com/us/commercial/display-support

Contact your LG Regional Sales Representative: Channel: 800.897.8871 Hospitality: 800.228.1236 E-mail: info@LGsolutions.com © Copyright 2023 ©LG Electronics USA, Inc. All rights reserved. LG and the LG logo are registered trademarks of LG Corp. All other trademarks are the property of their respective owners. Prices, promotions, and availability may vary by dealer. The information contained herein is subject to change without notice. All screen images are simulated.

SPEC\_27BR530Y-C\_082347\_LR