

4XEM In Car Mobile Device Charging Kit – Dual USB Adapter and 3FT USB-C to USB-C Cable

4XEM Part- 4XCARCHARGEKITB



Introducing the 4XEM In Car Mobile Device Charging Kit – the ultimate solution for keeping your mobile devices powered up on the go. With a sleek black design, this kit includes a Dual USB Adapter and a 3FT USB-C to USB-C Cable, providing you with efficient and reliable charging options for your devices.

Equipped with industry-standard USB-PD 3.0 and USB 3.2 Gen 2, this charging kit ensures fast and stable charging speeds, with a data rate of 10Gbps. The USB Type-C Female and USB Type-A Female ports allow you to charge multiple devices simultaneously, making it perfect for long road trips or daily commutes. Its power budget of 20W and Power Delivery capability of 20W Max ensures efficient charging performance.

The included 3FT USB-C to USB-C Cable boasts a bidirectional charging cable direction and a passive operating mode. With a length of 3 feet, it offers flexibility and convenience for connecting your devices. The cable supports E-Marker technology, providing a power output of 100W, along with video support. Its black color complements the charger's design perfectly.

4XEM Products Are Available At Your Favorite Online Retailers

WWW.4XEM.COM

**Contact Todd Schaus 4XEM sales Rep
1-866-999-4936 Ext.104 tschaus@4xem.com**



Features

Dual USB Car Charger Adapter:


- 12V Vehicle Accessory Port connector – Power Source
- 1x USB Type-C Female Port
- 1x USB Type-A Female Port
- 20W Power Budget with 20W Max Power Delivery
- Meets USB-PD 3.0 Standards
- Color: Black

USB-C to USB-C Charging Cable:

- Connector 1: USB 3.1 Gen 2 Type-C
- Connector 2: USB 3.1 Gen 2 Type-C
- Passive Operating mode
- Bidirectional – no input or output connector, interchangeable
- 10 Gbps Data Transfer Rate
- E-marked for 100 Watts (20V,5A) charging
- Supports video (through DisplayPort Alt mode, must be supported by source and display)
- Color: Black



Reversible USB Type C Connectors



4XEM Products Are Available At Your Favorite Online Retailers



Warranty Information	Warranty	1 year
Connector(s)	Charging Port	1x USB Type-C Female 1x USB Type-A Female
	Power	12V Vehicle Accessory Port
	Charging Cable Connector A	USB Type-C Male
	Charging Cable Connector B	USB Type-C Male
	Charging Cable Operating Mode	Passive
	Charging Cable Direction	Bidirectional
Performance	Industry Standards	USB-PD 3.0 USB 3.2 Gen 2
	Cable Data Rate	10Gbps
	E-Marker	20V, 5A (100W)
	Cable Video Support	Yes
	Certifications	CE TUV-MARK ROHS
Physical Characteristics	Charger Color	Black
	Display	No
	LED Indicator(s)	Power: White
	Charger Width	1.04 in [26.3 mm]
	Charger Height	1.04 in [26.3 mm]
	Charger Length	2.25 in [57.1 mm]
	Charger Weight	0.56 oz [16 g]
	Charging Cable Color	Black
	Charging Cable Length	3.28 ft [1.00 m]
	Charging Cable OD	0.18 in [4.50 mm]
	Charging Cable Weight	1.13 oz [32 g]
Power	Total Power Budget	20W
	Power Delivery	20W Max
	Input Voltage	12V-24V DC @ 2A
	Output Voltage (C1)	20W: 5V 3A, 9V 2.22, 12V 1.67A
	Output Voltage (A1)	18W: 5V 3A, 9V 2A, 12 1.5A
	Output Voltage (C1) + (A1)	17W MAX - 17W: 5V 3.4A (Shared)
Environmental	Operating Temperature	32°F to 104°F [0°C to 40°C]
	Storage Temperature	-4°F to 176°F [-20°C to 80°C]
	Humidity	5% to 90% (non-condensing)
Packaging Information	Package Type	Poly Bag
	Package Height	7.09 in [180 mm]
	Package Width	4.72 in [120 mm]
	Package Length	0.54 in [13.7 mm]
	Shipping (Package) Weight	1.69 oz [48 g]
What's in the Box	Included in Package	1x 20W USB-C + USB-A Car Charger 1x 3ft/1m USB-C/USB-C Cable
Notes	Notes	"Connected video source equipment and display must both support DisplayPort Alt-Mode for functional A/V transmission. Charger made with PC V0 flame retardant plastics"

* Product appearance and specifications are subject to change without notice.

* Weights and measurements are approximate.

