


IN-WALL SPEAKERS

CLEAR SOUND ANYWHERE

Turn the entire home into a living theater with Phoenix Gold's affordable solutions. Speaker selectors deliver flexibility, and with our in-ceiling, in-wall and indoor/outdoor speakers, there's a speaker solution for every need.



WITH GRILL

IN-WALL 2-WAY LCR AT1515

FEATURES

- Dual 5.25" Polypropylene Woofers
- 25mm Pivoting Parachute Silk Dome Tweeter
- Mid, Tweeter, Mid Configuration (MTM)
- Butyl Rubber Surround
- Robust Dog-Leg Mounting System
- Spray-Paintable Frame and Grill
- Integrated Rear Dust Shield
- Left, Center, Right Application
- Magnetically Shielded
- Sold Individually

SPECIFICATIONS

- Power Handling: 15 - 150 Watts
- Impedance: 8 Ω
- Frequency Response: 60Hz - 20kHz
- Sensitivity 2.83V/1m: 92dB
- Cut-Out Dimension: 13 ¹⁵/₁₆ x 6 ⁷/₈" (354 x 175mm)
- Mounting Depth: 3 ¹/₂" (89mm)

IN-WALL SPEAKERS

IN-WALL 2-WAY AT18

FEATURES

8" Polypropylene Woofer
25mm Pivoting Parachute Silk Dome Tweeter
Butyl Rubber Surround
Robust Dog-Leg Mounting System
Spray-Paintable Frame and Grill
Textured Woofer for Reduced Resonance
Sold as a Pair

SPECIFICATIONS

Power Handling: 15 - 200 Watts
Impedance: 8 Ω
Frequency Response: 38Hz - 20kHz
Sensitivity 2.83V/1m: 90dB
Cut-Out Dimension: 8 $\frac{3}{4}$ " x 12 $\frac{3}{4}$ " (222 x 324mm)
Mounting Depth: 3 $\frac{3}{8}$ " (85mm)



IN-WALL 2-WAY AT16

FEATURES

6.5" Polypropylene Woofer
25mm Pivoting Parachute Silk Dome Tweeter
Butyl Rubber Surround
Robust Dog-Leg Mounting System
Spray-Paintable Frame and Grill
Textured Woofer for Reduced Resonance
Sold as a Pair

SPECIFICATIONS

Power Handling: 15 - 200 Watts
Impedance: 8 Ω
Frequency Response: 40Hz - 20kHz
Sensitivity 2.83V/1m: 90dB
Cut-Out Dimension: 7 $\frac{9}{16}$ " x 10 $\frac{13}{16}$ " (186 x 276mm)
Mounting Depth: 3 $\frac{3}{8}$ " (85mm)



IN-WALL 2-WAY AT15

FEATURES

5.25" Polypropylene Woofer
25mm Pivoting Parachute Silk Dome Tweeter
Butyl Rubber Surround
Robust Dog-Leg Mounting System
Spray-Paintable Frame and Grill
Textured Woofer for Reduced Resonance
Sold as a Pair

SPECIFICATIONS

Power Handling: 15 - 150 Watts
Impedance: 8 Ω
Frequency Response: 60Hz - 20kHz
Sensitivity 2.83V/1m: 90dB
Cut-Out Dimension: 6 $\frac{1}{8}$ " x 9 $\frac{5}{8}$ " (155 x 243mm)
Mounting Depth: 2 $\frac{3}{4}$ " (69mm)



IN-CEILING SPEAKERS



IN-CEILING 2-WAY ATC8

FEATURES

- 8" Polypropylene Woofer
- 25mm Pivoting Parachute Silk Dome Tweeter
- Butyl Rubber Surround
- Robust Dog-Leg Mounting System
- Spray-Paintable Frame and Grill
- Textured Woofer for Reduced Resonance
- Sold as a Pair

SPECIFICATIONS

- Power Handling: 15 - 150 Watts
- Impedance: 8 Ω
- Frequency Response: 38Hz - 22kHz
- Sensitivity 2.83V/1m: 90dB
- Cut-Out Diameter: 9 $\frac{5}{16}$ " (236mm)
- Mounting Depth: 3 $\frac{3}{8}$ " (85mm)



IN-CEILING 2-WAY ATC6

FEATURES

- 6.5" Polypropylene Woofer
- 25mm Pivoting Parachute Silk Dome Tweeter
- Butyl Rubber Surround
- Robust Dog-Leg Mounting System
- Spray-Paintable Frame and Grill
- Textured Woofer for Reduced Resonance
- Sold as a Pair

SPECIFICATIONS

- Power Handling: 15 - 150 Watts
- Impedance: 8 Ω
- Frequency Response: 40Hz - 20kHz
- Sensitivity 2.83V/1m: 90dB
- Cut-Out Diameter: 7 $\frac{5}{16}$ " (193mm)
- Mounting Depth: 3 $\frac{3}{8}$ " (85mm)



IN-CEILING 2-WAY ATC5

FEATURES

- 5.25" Polypropylene Woofer
- 19mm Pivoting Parachute Silk Dome Tweeter
- Butyl Rubber Surround
- Robust Dog-Leg Mounting System
- Spray-Paintable Frame and Grill
- Textured Woofer for Reduced Resonance
- Sold as a Pair

SPECIFICATIONS

- Power Handling: 15 - 150 Watts
- Impedance: 8 Ω
- Frequency Response: 60Hz - 20kHz
- Sensitivity 2.83V/1m: 90dB
- Cut-Out Diameter: 6 $\frac{5}{16}$ " (166mm)
- Mounting Depth: 2 $\frac{3}{4}$ " (69mm)

IN-CEILING SPEAKERS

IN-CEILING 2-WAY LCR ATCLCR6

FEATURES

6.5" Polypropylene Woofer
25mm Pivoting Parachute Silk Dome Tweeter
15 Degree Speaker Inclination
Butyl Rubber Surround
Robust Dog-Leg Mounting System
Spray-Paintable Frame & Grill
Left, Center, Right Application
Textured Woofer for Reduced Resonance
Sold Individually

SPECIFICATIONS

Power Handling: 15 - 150 Watts
Impedance: 8 Ω
Frequency Response: 55Hz - 18kHz
Sensitivity 2.83V/1m: 92dB
Cut-Out Diameter: 8 $\frac{1}{8}$ " (206mm)
Mounting Depth: 5" (127mm)



WITH GRILL

IN-CEILING SUMMED STEREO ATC8DM

FEATURES

8" Polypropylene Woofer
Dual 19mm Parachute Silk Dome Tweeters
Dual Voice Coils
Summed Stereo or Single Channel Operation
Butyl Rubber Surround
Robust Dog-Leg Mounting System
Spray-Paintable Frame and Grill
Textured Woofer for Reduced Resonance
Sold Individually

SPECIFICATIONS

Power Handling: 15 - 150 Watts
Impedance: 8 Ω
Frequency Response: 38Hz - 22kHz
Sensitivity 2.83V/1m: 86/89dB
Cut-Out Diameter: 9 $\frac{5}{16}$ " (236mm)
Mounting Depth: 3 $\frac{3}{8}$ " (85mm)



WITH GRILL

IN-CEILING SUMMED STEREO ATC6DM

FEATURES

6.5" Polypropylene Woofer
Dual 19mm Parachute Silk Dome Tweeters
Dual Voice Coils
Summed Stereo or Single Channel Operation
Butyl Rubber Surround
Robust Dog-Leg Mounting System
Spray-Paintable Frame and Grill
Textured Woofer for Reduced Resonance
Sold Individually

SPECIFICATIONS

Power Handling: 15 - 150 Watts
Impedance: 8 Ω
Frequency Response: 50Hz - 20kHz
Sensitivity 2.83V/1m: 86/89dB
Cut-Out Diameter: 7 $\frac{5}{8}$ " (193mm)
Mounting Depth: 3 $\frac{3}{8}$ " (85mm)




WITH GRILL

INDOOR/OUTDOOR SPEAKER PLACEMENT

Like all speakers, Indoor/Outdoor Speakers sound best when placed in the line of sight of the listener, with no obstructions. They can be mounted vertically or horizontally and will pivot 180 degrees.

Indoor/Outdoor Speakers are manufactured to resist a variety of weather conditions. However, they are not waterproof, so if you decide to place your speakers outdoors, position them so they are not directly exposed to the elements. The undersides of most eaves and overhangs provide the best protection.



INDOOR/OUTDOOR SPEAKERS

INDOOR/OUTDOOR 2-WAY IHS6B

FEATURES

6.5" Polypropylene Woofer
25mm Parachute Silk Dome Tweeter
Butyl Rubber Surround
CAD/CAE Designed, Audiophile Phase Compensated Crossover
Magnetically Shielded
Weather and UV Resistant Design
Aluminum Grill and Mounting Brackets
Pivoting Bracket Design with 15 Degree Marked Increments
Corner Mounting Holes in Brackets
Sold as a Pair

SPECIFICATIONS

Power Handling: 25 - 100 Watts
Impedance: 8 Ω
Sensitivity 2.83V/1m: 90dB
Frequency Response: 65Hz - 20kHz
Dimensions: 8 $\frac{3}{4}$ x 12 $\frac{61}{64}$ x 7 $\frac{5}{8}$ "
(223 x 328 x 195mm)
Weight: 7.5 lbs (3.4 kg)



Also available in white - IHS6W

INDOOR/OUTDOOR 2-WAY IHS5B

FEATURES

5.25" Polypropylene Woofer
25mm Parachute Silk Dome Tweeter
Butyl Rubber Surround
CAD/CAE Designed, Audiophile Phase Compensated Crossover
Magnetically Shielded
Weather and UV Resistant Design
Aluminum Grill and Mounting Brackets
Pivoting Bracket Design with 15 Degree Marked Increments
Corner Mounting Holes in Brackets
Sold as a Pair

SPECIFICATIONS

Power Handling: 25 - 100 Watts
Impedance: 8 Ω
Sensitivity 2.83V/1m: 89dB
Frequency Response: 85Hz - 20kHz
Dimensions: 7 $\frac{1}{2}$ x 11 x 6 $\frac{1}{2}$ "
(190 x 280 x 166mm)
Weight: 5.75 lbs (2.6 kg)



Also available in white - IHS5W

INDOOR/OUTDOOR 2-WAY IHS4B

FEATURES

4" Polypropylene Woofer
19mm Parachute Silk Dome Tweeter
Butyl Rubber Surround
CAD/CAE Designed, Audiophile Phase Compensated Crossover
Magnetically Shielded
Weather and UV Resistant Design
Aluminum Grill and Mounting Brackets
Pivoting Bracket Design with 15 Degree Marked Increments
Corner Mounting Holes in Brackets
Sold as a Pair

SPECIFICATIONS

Power Handling: 25 - 100 Watts
Impedance: 8 Ω
Sensitivity 2.83V/1m: 88dB
Frequency Response: 100Hz - 20kHz
Dimensions: 6 $\frac{7}{16}$ x 9 $\frac{1}{2}$ x 5 $\frac{3}{8}$ "
(163 x 241 x 143mm)
Weight: 4 lbs (1.8 kg)



Also available in white - IHS4W

INDOOR/OUTDOOR SPEAKERS



Also available in black - ATO62B

INDOOR/OUTDOOR 2-WAY ATO62W

FEATURES

- 6.5" Polypropylene Woofer
- CAD/CAE Designed, Phase Compensated Crossover
- 25mm Aluminum Dome Tweeter
- Weather and UV Resistant Design
- Mounting Brackets and Hardware Included
- Spray-Paintable Grill and Housing
- Butyl Rubber Surround
- 5-Way Color Coded Binding Posts
- Sold as a Pair

SPECIFICATIONS

- Power Handling: 25 - 100 Watts
- Impedance: 8 Ω
- Sensitivity 2.83V/1m: 87.5dB
- Frequency Response: 65Hz - 20kHz
- Dimensions: 8 x 11 x 7 1/4"
(203 x 280 x 184mm)
- Weight: 5.5 lbs (2.3 kg)



Also available in black - ATO52B

INDOOR/OUTDOOR 2-WAY ATO52W

FEATURES

- 5.25" Polypropylene Woofer
- CAD/CAE Designed, Phase Compensated Crossover
- 25mm Aluminum Dome Tweeter
- Weather and UV Resistant Design
- Mounting Brackets and Hardware Included
- Spray-Paintable Grill and Housing
- Butyl Rubber Surround
- 5-Way Color Coded Binding Posts
- Sold as a Pair

SPECIFICATIONS

- Power Handling: 25 - 100 Watts
- Impedance: 8 Ω
- Sensitivity 2.83V/1m: 89dB
- Frequency Response: 85Hz - 20kHz
- Dimensions: 6 3/4 x 9 1/2 x 6 3/8"
(170 x 240 x 160mm)
- Weight: 4.2 lbs (1.9 kg)



Also available in black - ATO42B

INDOOR/OUTDOOR 2-WAY ATO42W

FEATURES

- 4" Polypropylene Woofer
- CAD/CAE Designed, Phase Compensated Crossover
- 25mm Aluminum Dome Tweeter
- Weather and UV Resistant Design
- Mounting Brackets and Hardware Included
- Spray-Paintable Grill and Housing
- Butyl Rubber Surround
- 5-Way Color Coded Binding Posts
- Sold as a Pair

SPECIFICATIONS

- Power Handling: 25 - 100 Watts
- Impedance: 8 Ω
- Sensitivity 2.83V/1m: 85dB
- Frequency Response: 100Hz - 20kHz
- Dimensions: 5 1/16 x 8 x 5"
(145 x 203 x 127mm)
- Weight: 2.2 lbs (1 kg)

INDOOR/OUTDOOR SPEAKERS

INDOOR/OUTDOOR 2-WAY ATO5

FEATURES

5.25" Polypropylene Woofer
19mm Polycarbonate Tweeter
Weather Resistant Speaker System
White Housing with White Powder Coated Microperf Grill
Mounting Brackets and Hardware Included
Spray-Paintable Grill and Housing
Butyl Rubber Surround
Sold as a Pair

SPECIFICATIONS

Power Handling: 25 - 100 Watts
Impedance: 8 Ω
Sensitivity 2.83V/1m: 89dB
Frequency Response: 60Hz - 20kHz
Dimensions: 9 1/2" x 7" x 6 5/8"
(241 x 178 x 169mm)
Weight: 4.6 lbs (2.1 kg)



OUTDOOR ROCK ATR5G (GRANITE)

FEATURES

5.25" Woofer
19mm Balanced Drive Tweeter
Rugged Fiberglass Enclosure
Sold as a Pair

SPECIFICATIONS

Power Handling: 25 - 100 Watts
Impedance: 8 Ω
Sensitivity 2.83V/1m: 90dB
Frequency Response: 120Hz - 21kHz
Dimensions: 9 1/4" x 10 3/8" x 7 5/8"
(235 x 264 x 194mm)
Weight: 6.9 lbs (3.1 kg)



OUTDOOR ROCK ATR5S (SANDSTONE)

FEATURES

5.25" Woofer
19mm Balanced Drive Tweeter
Rugged Fiberglass Enclosure
Sold as a Pair

SPECIFICATIONS

Power Handling: 25 - 100 Watts
Impedance: 8 Ω
Sensitivity 2.83V/1m: 90dB
Frequency Response: 120Hz - 21kHz
Dimensions: 9 1/4" x 10 3/8" x 7 5/8"
(235 x 264 x 194mm)
Weight: 6.9 lbs (3.1 kg)

