

ThinkVision T27i-30 Monitor

Big on comfort. Big on productivity.

Amplify productivity with complete connectivity.

The ThinkVision T27i-30 Monitor is carefully configured with features that deliver better connectivity, enhance your productivity, and ensure your comfort. This large screen 27-inch FHD monitor offers a resolution of 1920 x 1080 pixels with a wide viewing angle for clear, crisp on-screen content. Expect rich, vibrant colors with 99% sRGB that sharpens the display and is great for video producers and film animators. Long hours at the screen can cause eye fatigue but not with the ThinkVision T27i-30 Monitor which has Natural Low Blue Light technology that cuts down harmful blue light to give your eyes a comfortable, strain-free experience. The monitor hosts a range of versatile connectors for extended usage with VGA, HDMI 1.4, DP 1.2 ports and a USB Hub. Say hello to great video conferencing¹ capabilities as with this monitor's expandable functions. A full-function ergonomic stand allows for greater flexibility, with a wider adjustment range and low head position so you can set up the monitor to suit your comfort. What's more, you'll be delighted to know that the ThinkVision T27i-30 Monitor comes in an eco-friendly paper-pulp packaging that's great for the environment.



KEY FEATURES OF THINKVISION T27i-30 MONITOR



A treat for your eyes

The ThinkVision T27i-30 Monitor's IPS display is a treat for your eyes with an ultra-wide viewing angle that delivers high color accuracy and image quality. This large 27-inch monitor feels even bigger with 3-side NearEdgeless bezels. Rich display quality is enhanced with 99% sRGB color for an impressive viewing experience. Comfort is key with the ThinkVision T27i-30 Monitor with Natural Low Blue Light technology which helps to minimize visual fatigue and strain, so your eyes are protected.



Plug in to productivity

You won't miss a beat with the ThinkVision T27i-30 Monitor. A range of connectivity options from VGA and HDMI 1.4 ports to DP 1.2 ports ensure you're always ready to plug in and perform. Take advantage of the monitor's four USB 3.2 Gen 1² ports for easy extension of USB devices. A dedicated USB port for modular VoIP solution - ThinkVision MC30 Monitor Soundbar and ThinkVision MC60 Monitor Webcam¹ enables incredible video conferencing experiences. Enjoy easy and effortless access to configuration settings with the updated ThinkColour software³. The ThinkVision T27i-30 is geared to ensure incredible connectivity that amplifies your productivity.

USB Type-A



User-friendly and eco-friendly

Enjoy an upgraded user experience that makes comfort and ease a priority with the ThinkVision T27i-30 Monitor. Save space and reduce clutter with cleaner cable management. Joystick control puts easy control at your fingertips. A full-function ergonomic stand with wider adjustable ranges including lift range and tilt ensure that you can position the monitor perfectly for your comfort. ThinkVision T27i-30 Monitor also supports cableless modular VoIP solution¹ and a phone holder for enhanced flexibility. It is also eco-friendly with sustainable paper pulp packaging that's great for the environment!

¹ Modular VoIP solution (ThinkVision MC30 Monitor Soundbar and ThinkVision MC60 Monitor Webcam) is sold separately.

² Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: 5 Gbit/s for USB 3.2 Gen 1; 10 Gbit/s for USB 3.2 Gen 2 & 20 Gbit/s for USB 3.2 Gen2x2.

³ This software can only be used with Windows 10 & Windows 11.

ThinkVision T27i-30 Monitor

DISPLAY

Panel Size
27-inch

Screen Dimensions
607.1 mm x 354.1 mm

Panel Type
3-side NearEdgeless In-Plane Switching

Active Area
597.9 mm x 336.3 mm

Backlight
WLED

Aspect Ratio
16:9

Resolution
1920 x 1080

Pixel Pitch
0.311 mm x 0.311 mm

Dot/Pixel Per Inch (DPI/PPI)
81

Viewing Angle (H x V @ CR 10:1)
178° / 178°

Response Time
4ms (Extreme Mode),
6ms (Normal Mode)

Refresh Rate
60 Hz

Brightness (Typical)
300 cd/m²

Contrast Ratio (Typical)
1000:1

Dynamic Contrast Ratio (Typical)
3M:1

Color Gamut (Coverage Ratio)
99% sRGB (CIE 1931)

Color Support (Typical)
16.7 Million

Color Depth
8-bit (6+FRC)

Anti-Glare
Yes

CONNECTIVITY

Video Signal
1 x HDMI 1.4
1 x DP 1.2
1 x VGA

Audio Signal
1 x Audio Out (3.5 mm)

USB Hub
Yes

USB Upstream
1 x USB 3.2 Gen 1¹ (by USB Type-B)

USB Downstream
4 x USB 3.2 Gen1¹ (1 x BC 1.2)

MULTIMEDIA

Modular Camera/Speaker Support
Yes (Optional Support²)

SPECIAL FEATURES

Software
Lenovo ThinkColour
(Lenovo Display Control Center)³

Natural Low Blue Light
Yes

POWER

Power Consumption (Typ. / Max.)
24W / 65W

Power Consumption Sleep/Off Mode
< 0.5W

Power Consumption Switch-Off Mode
< 0.3W

ENERGY STAR Power Consumption (Pon/E_{rec})
15W / 50kWh

Power Supply
Internal

Voltage Required
AC 100 to 240 V (50-60 Hz)

MECHANICAL

Tilt Angle (Front / Back)
-5° / 23.5°

Swivel Angle (Left / Right)
+45° / -45°

Lift Range
155 mm

Pivot
-90° / 90°

VESA Mount Capability
Yes (100 x 100 mm)

ThinkCentre M Series Tiny Support
Yes, by Tiny Clamp Bracket
Mounting Kit III (PN: 4XF1K72399)⁴

Kensington Lock Slot
Yes

Cable Management
Yes

Bezel Color
Raven Black

Bezel Width (Side)
2.0 mm

Bezel Width (Top / Bottom)
2.0 / 17.6 mm

DIMENSION

Size Packed (D x H x W) (mm/inch)
525.0 x 148.0 x 690.0 mm
20.67 x 5.83 x 21.17 inches

Size Unpacked w/ Stand (Lowest Position) (D x H x W) (mm/inch)
204.5 x 389.3 x 611.9 mm
8.05 x 15.33 x 24.09 inches

Size Unpacked w/ Stand (Highest Position) (D x H x W) (mm/inch)
204.5 x 544.3 x 611.9 mm
8.05 x 21.43 x 24.09 inches

Size Unpacked w/o Stand (Head Only) (D x H x W) (mm/inch)
50.0 x 362.5 x 611.9 mm
1.97 x 14.27 x 24.09 inches

Weight Packed (kg / lb)
10.1 kg / 22.3 lbs.

Weight Unpacked (kg / lb)
6.9 kg / 15.2 lbs.

Weight (Monitor Head Only) (kg / lb)
4.9 kg / 10.8 lbs.

WHAT'S IN THE BOX

Monitor with Stand
Yes

Power Cable (Cable Length)
1 x Power Cable (1.8m)

DP Cable (Cable Length)
1 x DP Cable (1.8m)

USB Cable (Cable Length)
1 x USB Type-A to Type-B Cable (1.8m)

Quick Setup Guide
Yes

CERTIFICATION

ENERGY STAR Certification
Yes

CCC
Yes

TCO
9.0

TCO Edge
2.0

EPEAT
Gold

Volatile Organic Compound Certification
Yes

RoHS (2011/65/EU)
Yes

Windows Certification
Windows 10, Windows 11

China Energy Efficiency Standard
Grade 2

TÜV Rheinland Eye Comfort
Yes

TÜV Low Blue Light (Hardware Solution)
Yes

Eyesafe Display Certification
Yes



¹ Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: 5 Gbit/s for USB 3.2 Gen 1; 10 Gbit/s for USB 3.2 Gen 2 & 20 Gbit/s for USB 3.2 Gen2x2.

² Modular VoIP solution (ThinkVision MC30 Monitor Soundbar and ThinkVision MC60 Monitor Webcam) is sold separately. | ³ This software can only be used with Windows 10 & Windows 11. | ⁴ Sold separately.

© 2023 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A., Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, ThinkVision, and ThinkColour are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.