

OMNIVS1500 is not for sale in Colorado, Vermont and Washington state. Customers in these states should purchase the recommended ENERGY STAR® 2.0 model instead: ECO1500LCD. Learn more about [ENERGY STAR 2.0](#) and [sales restrictions](#) in these states.

## OmniVS 120V 1500VA 940W Line-Interactive UPS, Tower, USB port

MODEL NUMBER: OMNIVS1500



### Highlights

- 1500VA / 1.5kVA tower 120V line-interactive UPS
- Corrects brownouts and overvoltages from 75 to 147V
- 5 UPS battery supported outlets, 3 surge-only outlets
- USB port, TEL/DSL/Ethernet protection, 97% line mode efficiency
- NEMA 5-15P input plug and 8 NEMA 5-15R outlets

### Package Includes

- OMNIVS1500 Line-Interactive UPS
- USB and telephone cable
- Owner's manual with warranty information

### Description

Tripp Lite's OMNIVS1500 line interactive UPS system offers voltage regulation, surge suppression and battery support for personal computers, internetworking equipment and other sensitive electronics. Internal UPS batteries support entry level PC systems for up to 75 minutes during power failures so that connected equipment can be shut down without data loss. Automatic Voltage Regulation (AVR) circuits regulate brownouts as low as 75 and overvoltages up to 147 volts back to usable 120V levels without using battery power. Offers complete desktop power protection in an attractive black tower configuration. Includes 5 battery supported outlets for computer, monitor and vital system peripherals, plus 3 additional surge suppression only outlets for printers and other system accessories not requiring battery support. USB port enables optional unattended system shutdown without data loss in the case of extended power failure (USB cable included). PowerAlert software available via free download. HID-compliant USB port also enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Built-in data line suppression offers protection for equipment with single line TEL/DSL or network Ethernet connection. Built-in audible alarm and 5 front panel LEDs indicate status of line power, battery power, battery low/replace, voltage regulation and overload. 1500VA power handling ability supports entry-level PCs, network workstations, point-of-sale equipment, small business phone systems, audio/video equipment and home theater systems. Offers 4.5 minutes battery runtime with a full load of 1500VA and 11.5 minutes with a half load of 750VA. Supports hot-swappable battery replacement via built-in access panel.

### Features

- OMNIVS1500 Uninterruptible Power Supply offers voltage regulation, surge suppression and long lasting battery support
- Supports entry level PCs up to 75 minutes during blackouts to enable shutdown without data loss
- Regulates brownouts as low as 75V and overvoltages to 147V back to usable 120V nominal levels without using battery power
- 5 UPS battery supported outlets, plus 3 additional surge suppression only outlets
- USB port enables data-saving unattended shutdown when used with Tripp Lite's PowerAlert software, available via FREE download from [www.tripplite.com/poweralert](http://www.tripplite.com/poweralert)
- HID-compliant USB port also enables integration with built-in power management and auto shutdown



features of Windows and Mac OS X

- Data line surge suppression protects standard dialup/DSL or ethernet line connection
- Built-in audible alarm and 5 front panel LEDs indicate status of line power, battery power, battery low/replace, voltage regulation and overload
- 1500VA power handling ability supports a variety of sensitive electronic equipment
- 4.5 minutes full load runtime (1500VA), 11.5 minutes half load runtime (750VA)
- Supports hot swappable battery replacement via built-in access panel
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment

## Specifications

OVERVIEW	
UPC Code	037332126382
UPS Type	Line-Interactive
INPUT	
Rated input current (Maximum Load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Input Phase	Single-Phase
Input Frequency	60Hz +/-5%
OUTPUT	
Output Volt Amp Capacity (VA)	1500
Output Capacity (kVA)	1.5
Output Watt Capacity (Watts)	940
Nominal Voltage Details	120v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-18%, +8%
Output Voltage Regulation (Battery Mode)	+/- 5%
UPS Output Receptacles (Surge Suppression Only)	5 UPS outlets, 3 surge-only outlets
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave



Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(8) 5-15R
Individually Controllable Load Banks	No
<b>BATTERY</b>	
Battery Type	Valve Regulated Lead Acid (VRLA)
Full Load Runtime (min.)	4.5 min. (940w)
Half Load Runtime (min.)	11.5 min. (470w)
Expandable Runtime	No
DC System Voltage (VDC)	24
Battery Recharge Rate (Included Batteries)	Less than 4 hours from 10% to 90%
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	&nbsp;<a class="productLink" href="//www.tripplite.com/UPS-Replacement-24VDC-Battery-Cartridge-for-select-Tripp-Lite-SLT-UPS~RBC24-SLT">RBC24-SLT</a>&nbsp;
Battery Replacement Description	Hot-swappable, user replaceable batteries
<b>VOLTAGE REGULATION</b>	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 75 to 147
Overvoltage Correction	Input voltages between 128 and 147 are reduced by 12%
Undervoltage Correction	Input voltages between 93 and 107 are boosted by 14%
Severe Undervoltage Correction	Input voltages between 75 and 92 are boosted by 30%
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
LED Indicators	5 LEDs indicate line power, battery power, overload, voltage regulation and battery low/replace status
<b>SURGE / NOISE SUPPRESSION</b>	
UPS AC Suppression Joule Rating	510
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC Noise Suppression	Yes



<b>PHYSICAL</b>	
Primary Form Factor	Tower
Installation Form Factors Supported with Included Accessories	Tower
Installation Form Factors Supported with Optional Accessories	Wallmount ( <a href="http://www.tripplite.com/Wall-Mount-Bracket-Installation-Accessories-for-UPS-Systems-UPSWM">UPSWM</a> ) - tower mounting kit
Primary UPS Depth (mm)	191
Primary UPS Height (mm)	300
Primary UPS Width (mm)	183
Shipping Dimensions (hwd / cm)	40.00 x 28.50 x 27.51
Shipping Dimensions (hwd / in.)	15.75 x 11.22 x 10.83
Shipping Weight (kg)	13.68
Shipping Weight (lbs.)	30.16
UPS Housing Material	Polycarbonate
UPS Power Module Dimensions (hwd, cm)	29.97 x 18.29 x 19.05
UPS Power Module Dimensions (hwd, in.)	11.8 x 7.2 x 7.5
UPS Power Module Weight (kg)	10.07
UPS Power Module Weight (lbs.)	22.2
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	109
Battery Mode BTU / Hr. (Full Load)	523
AC Mode Efficiency Rating (100% Load)	97%
<b>COMMUNICATIONS</b>	
PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert Local software at <a href="https://www.tripplite.com/poweralert">https://www.tripplite.com/poweralert</a>
Communications Cable	USB interface cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools Compatibility	NUT compatible. See the full list of Tripp Lite NUT compatible UPS systems at <a href="#">NUT UPS Compatibility Lis</a>
Network Management Card Description	Network management not supported
Communications Interface	USB (HID enabled)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	75
High Voltage Transfer to Battery Power (Setpoint)	147
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic Voltage Regulation (AVR); Hot swappable batteries; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
<b>STANDARDS &amp; COMPLIANCE</b>	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000&nbsp;<a class="insuranceLink" href="//www.tripplite.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp;

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>