enovo-

Lenovo IDEAPAD

IdeaPad 5i 2-in-1 (14" | 16")

The smarter choice for versatility.

Meet your challenges head-on with 360° versatility on the Lenovo IdeaPad 5i 2-in-1. With up to the latest Intel® Core™ 7 processors, you can knock any project out of the park. And the ultra-thin bezel up to OLED display brings out astounding visuals. With machine learning and an optional stylus, you can tackle anything effortlessly.



Because one mode doesn't fit all.

There are endless possibilities with the versatile laptop, which folds back on a 360° hinge for amazing flexibility. Knock out a business plan on laptop mode, stream the latest episode on tent mode, go into stand mode for presentations, or sketch your next idea on tablet. Made for easy carrying, the 14" and 16" models are perfect for being on the move.



Dial up your entertainment

Every moment on the 14" WUXGA and 16" 2K displays are a cinematic one. With narrow bezels all around the 16:10 screen, the up-to-OLED panel offers a fuller viewing experience. The Dolby Audio®-certified speakers offer greater volume in sound with +3 decibels. Long sessions are still incredibly coloraccurate and eye-friendly, thanks to TÜV Low Blue Light.









All systems ahead

Pausing is not an option with up to the latest Intel® Core™ 7 processors, unleashing exhilarating performance to throttle through your deadlines and boss battles. It features up to 16 GB LPDDR5X of memory, so all your apps, content, and documents run like clockwork. With up to 1 TB storage onboard, everything you love can be stored safely with you.



Productivity done your way

Always be on top of your daily life with productivity-centered features: Log in securely via the Fingerprint sensor, stay powered throughout with a fast-charging battery, keep prying eyes shut out on the FHD camera with privacy shutter, take unforgettable notes with the optional Lenovo Digital Pen, and expand your universe with a range of ports.





IdeaPad 5i 2-in-1 (14" | 16")

SPECIFICATIONS

IdeaPad 5 2-in-1 14IRU9 | IdeaPad 5 2-in-1 16IRU9*

PERFORMANCE

Processor

Intel® Core™ 7 150U Intel® Core™ 5 120U Intel® Core™ 3 100U¹

Operating System

Windows 11 Home

Graphics

UMA: Intel® Graphics

Memory

LPDDR5X: 8 GB / 16 GB

PCle M.2 : 256 GB¹ / 512 GB / 1 TB

Camera & Microphone

HD Camera | FHD Camera | Privacy Shutter | Dual Microphone Array

Audio

2 x 2W User-facing Speakers, Dolby Audio®

Batterv²

57WHr Polymer

Rapid Charge Boost : 15 min. @ 2 Hours

WUXGA OLED

MobileMark® 2025 : Up to 10.5 Hours (Target) 1080p Video Playback: Up to 19 Hours (Target)

WUXGA LCD

MobileMark® 2025 : Up to 10 Hours (Target) 1080p Video Playback: Up to 19 Hours (Target)

16" 2K OLED

MobileMark® 2025 : Up to 9 Hours (Target) 1080p Video Playback: Up to 16.5 Hours (Target)

WUXGA LCD

MobileMark® 2025 : Up to 9.5 Hours (Target) 1080p Video Playback: Up to 17.5 Hours (Target)

DESIGN

Display

14"

14" WUXGA (1920 x 1200) OLED, 60 Hz, 16:10, 400 nits, 100% DCI-P3, TÜV Low Blue Light Certification, Touch

14" WUXGA (1920 x 1200) IPS, 60 Hz, 16:10, 300 nits, 45% NTSC, TÜV Low Blue Light Certification, Touch

16" 2K (2048 x 1280) OLED, 60 Hz, 16:10, 400 nits, 100% DCI-P3, TÜV Low Blue Light Certification, Touch

16" WUXGA (1920 x 1200) IPS, 60 Hz, 16:10, 300 nits, 45% NTSC, TÜV Low Blue Light Certification, Touch

Dimension (W x D x H)

14"

Metal Version

(mm) : 313 x 227 x as thin as 17.5 (inches): 12.32" x 8.94" x as thin as 0.69"

16"

Metal Version

(mm) : 356 x 255 x as thin as 18.4 (inches): 14.02" x 10.03" x as thin as 0.72"

Weight

: Starting at 1.5 kg (3.31 lbs) 16" : Starting at 1.9 kg (4.19 lbs)

Colors Luna Grey

Cosmic Blue

CONNECTIVITY

WLAN

WiFi 6 | WiFi 6E

Bluetooth*

Up to Bluetooth® 5.3

Input/Output (I/O) Ports

2 x USB 3.2 Gen 23 Type-C (Full-function) 1 x HDMI™ 1.4b 1 x Audio Jack

2 x USB 3.2 Gen 13 Type-A (one support USB charging) 1 x Micro SD Card Reader

PRELOADED SOFTWARE

- Windows 11 Home/Pro
- · Lenovo Vantage
- Microsoft 365 Trial
- McAfee® LiveSafe™

GREEN CERTIFICATIONS

- ENERGY STAR® 8.0
- EPEAT™ Gold Registered in the US
- · MIL-STD-810H Military Test Passed
- ¹ 14" only.
- All battery life claims are approximate and based on two methods of testing: MobileMark* 2025 battery life benchmark and continuous 1080p video playback on the latest update of Windows 10 (with 150 nits brightness and default volume level). Actual battery life will vary and depends on many factors such as product configuration and usage, software use, wireless functionality, power management settings, and screen brightness. The maximum capacity of the battery will decrease with time and use.
- The actual transfer speed of the USB 3.2 will vary and, depending on many factors, such as the processing capability of host and peripheral devices, file attributes and other factors related to system configuration and your operating environments, will be slower than a speed of 20 Gbit/s.

With Lenovo **Al Engine**

LENOVO SERVICES

Lenovo Premium Care Plus is the ultimate PC support experience with you as our priority 24/7. Enjoy personalized hardware and software support from a global network of elite technicians, along with accidental damage protection, fast repairs with onsite support, extended battery warranty, data migration assistance, and smart performance solutions that optimize PC performance and security.

Lenovo Smart Performance

Smart Performance Services within Lenovo Vantage will keep your system running at optimum performance and proactively fix issues that affect PC performance, internet performance, remove malware, and improve device security.

Lenovo Accidental Damage Protection

Avoid the hassles of unexpected damage & repair costs. With coverage for drops, spills, electric surges, and broken LCD screens, accidental damage protection makes it easy to repair to your PCs and ensures your device is up and running fast.

Lenovo CO₂ Offset Services*

Offset the carbon emissions of your PC with Lenovo CO₂ Offset Services – an easy and transparent solution to offset emissions across the average lifecycle of your device. These offsets are invested in UN-approved initiatives like renewable energy or ecological projects, thus contributing towards a more sustainable future.

Lenovo Sealed Battery Warranty

Long-lasting battery life is not just a feature but a necessity to help you stay productive and connected all day long. Protect your PC's sealed battery from degradation, enjoy hassle-free battery replacement service, and safeguard your PC from future battery failure with our Sealed Battery Warranty Service.

Lenovo Warranty Extensions (Up to 3 Years

Gain complete peace of mind by extending your base warranty to up to 3 years and minimize unexpected repair costs.

Optional.





Lenovo 540 **USB-C Wireless** Compact Mouse

Lenovo USB-C 3-in-1 Hub

OPTIONS & ACCESSORIES

Lenovo 100 Stereo Analog Headset

McAfee® LiveSafe™

Register McAfee* to enjoy these benefits in your FREE 30-day trial.

- Award-winning Antivirus Password Manager
- Multi-device Compatibility • Identity Theft Protection
- Safe Web Browsing
- Free Customer Support

*Example of Lenovo marketing naming convention











WWW.LENOVO.COM

Lengyo reserves the right to alter product offerings and specifications at any time, without notice. Lengyo makes every effort to ensure accuracy of all information but is not liable or responsible for any editorial. photographic or typographic errors. All images are for illustration purposes only. For full Lenovo product, service and warranty specifications visit www.lenovo.com. Lenovo makes no representations or warranties regarding third party products or services. **Trademarks**: The following are trademarks or registered trademarks of Lenovo: Lenov, the Lenovo logo, ideaped, ideaCentre, yoga and yoga home. Microsoft, Windows and Vista are registered trademarks of intel Corporation in the U.S. and/or other company, product and service names may be trademarks or service marks of others. Visit www.lenovo.com/lenovo/us/en/safecomp/ periodically for the latest information on safe and effective computing. **@2024 Lenovo.** All rights reserved.



