

Product data sheet

Specifications



APC NetShelter SX Server Rack Gen 2, 42U, 1991H x 600W x 1070D mm, with Sides, Black [TAA]

AR3100B2

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Product or Component Type	Rack enclosure
Number of rack unit	42U
Provided equipment	Baying hardware Key(s) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters Side Panels

Physical

Height	78.39 in (199.1 cm)
Width	23.62 in (60 cm)
Depth	42.13 in (107 cm)
Net Weight	269.27 lb(US) (122.14 kg)
Color	Black
Mounting preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	36.02 in (91.49 cm)
minimum mounting depth	7.50 in (19.05 cm)
Rack Width	19"
Marking	14 gauge EIA mounting rail
Permanent permissible load	2250 lb(US) (1020.6 kg) dynamic 4000 lb(US) (1814.4 kg) static

Conformance

Standards	UL 2416 EIA-310E
-----------	---------------------

Ordering and shipping details

GTIN	731304642176
Country of origin	CN

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	83.78 in (212.8 cm)
Package 1 Width	29.45 in (74.8 cm)
Package 1 Length	45.59 in (115.8 cm)
Package 1 Weight	318.68 lb(US) (144.55 kg)

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	1205

Use Better	
Materials and Substances	
[EU RoHS Directive](#)	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	[REACH Declaration](#)
Use Again	
Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No