

Bang & Olufsen Cisco 950



Contents

03	Product overview
04	Features and benefits
05	Compatibility
05	Product specifications
10	Ordering information
11	Warranty information
11	For more information



Above: Bang & Olufsen Cisco 950 earbuds

Product overview

In partnership with Bang & Olufsen, we have created true wireless earbuds that are designed for professionals. Offering a trendy minimalistic design in Black Anthracite showcasing luxury materials, the best sound quality, and features that make your work day a little more engaging.

The Bang & Olufsen Cisco 950 earbuds deliver pure sound, a tailored fit, and the best meeting experience. With Bluetooth® 5.2, Adaptive Active Noise

Cancellation, on-ear controls, enterprise grade security, and management – these earbuds are perfect for professional and IT teams.

Securely manage the Bang & Olufsen Cisco 950, along with all your other Cisco devices, from a single platform with Webex Control Hub at no additional cost. Simplify deployments, track inventory, troubleshoot issues, and push new firmware to ensure users have the latest features and enjoy optimal performance.

Features and benefits

Table 1. Features and benefits for the Bang & Olufsen Cisco 950 earbuds

FEATURE	DESCRIPTION
Enhanced features for professionals	Fitted with the technology needed for an high-end audio experience on calls, video meetings, and listening to music. Plus, benefits for IT teams that enable organizations to maximize their ROI with inventory tracking, usage stats, and firmware upgrades.
Bluetooth® (5.2)	Connect on the go to any devices that supports Bluetooth. Simultaneously connect 2 Bluetooth devices (<i>Cisco USB HD adapter supported</i>)
Crystal clear communications	Get 6 geometrically placed microphones that isolate your voice and cancel out background noise using advanced algorithms
The Bang & Olufsen audio experience	Immerse yourself in a legendary audio experience with advanced codecs. A minimalistic wearing style that is optimized for Webex makes listening to music or calls comfortable and effortless.
Adaptive Active Noise Cancellation	Tune out the background noise with adaptive active noise cancellation (ANC), which automatically adjusts the level of ANC based on your surroundings or manually turn on Transparency Mode to better listen to your surroundings.
Customizable controls	On-ear controls provide users with unparalleled control with device sync to quickly mute, pause/play or change songs, adjust volume, and more.
Enterprise-grade security	Hardware and software protection to help communications stay secure
Premium materials	A tailored fit provides ultra-high, all-day comfort with luxury materials including an aluminum case, tempered glass, silicon, and polymer.

Table 1. Features and benefits for the Bang & Olufsen Cisco 950 earbuds

FEATURE	DESCRIPTION
Bang & Olufsen mobile app	Enjoy a customized sound experience with Beosonic tuning that allows you to adjust sound modes for defined audio highs, mids, and lows.
Easy Device Management	Manage your earbuds and headsets, along with all your other Cisco devices, from a single platform in Control Hub. No additional software or service fees are required. Enjoy simple IT headset management to deploy, monitor, push new firmware, and troubleshoot issues

Compatibility

For compatibility information with Cisco IP Phone, Cisco Desk Series, Webex, and Webex Meetings, please refer to [Cisco Headset Compatibility Guide](#) for details.

Product specifications

Table 2. Product specifications

CONNECTIVITY	SPECIFICATIONS
Connectivity options	Bluetooth
Simultaneous connections	2 Bluetooth
Bluetooth codecs	<ul style="list-style-type: none"> • SBC • AAC • Qualcomm® aptX™ Adaptive

Table 2. Product specifications

CONNECTIVITY	SPECIFICATIONS
Bandwidth	<ul style="list-style-type: none">• Narrowband (8 kHz)• Wideband (16 kHz)• Full band (48 kHz)
Range	10 meters (32 feet)
Bluetooth profiles	Headset Profile (HSP), Hands-Free Profile (HFP), Audio/Video Remote Control Profile (AVRCP), Advanced Audio Distribution Profile (A2DP), Human Interface Device (HID)
Bluetooth version	5.2
Frequency band	2402 ~ 2480 MHz
Modulation technique	GFSK, $\pi/4$ -DQPSK, 8-DPSK
Max EIRP power (dBm)	9.7 dBm
Certifications	<ul style="list-style-type: none">• Apple Mfi (Made for iPhone)• Google Fast Pair• Microsoft Swift Pair

Table 2. Product specifications

AUDIO	SPECIFICATIONS
Adaptive Active Noise Cancellation & Transparency Mode	Equipped with adaptive ANC and transparency mode that can be manually selected on the earbuds or within the mobile app.
Voice assistant	Supports the connected device's native assistant
Hearing protection	Acoustic shock protection from sounds louder than 118 dB (A)
Microphone type	6 MEMS Mic integrated into the earbuds
Microphone directionality	Omni-directional (beam directional for speech)
Microphone frequency response	20 to 20 kHz
Speaker and microphone configuration	Stereo and mono use on either left or right earbud
Speaker size	9.2 mm
Speaker impedance	32 Ohm
Speaker bandwidth	20 Hz to 22 kHz

Table 2. Product specifications

BATTERY	SPECIFICATIONS
Talk time earbuds	Up to 5 hours in earbuds with adaptive ANC
Listen time earbuds	Up to 6 hours in earbuds with adaptive ANC. Up to 8 hours without adaptive ANC.
Additional listen time provided by case	Provides 2.5 additional charges for the pair of earbuds
Quick charge earbuds	105 minutes of listen time after 20 minutes of charge time
Charging time earbuds	90 minutes in charging case
Charging time case (USB-C)	105 minutes
Charging time case (wireless – Qi)	135 minutes
Battery type	Rechargeable lithium-ion battery: <ul style="list-style-type: none"> • Capacity right earbud: 70 mAh • Capacity left earbud: 70 mAh • Capacity charging case: 380 mAh
Power Supply Wired	. 5V charging by USB-C input
Power supply wireless	Wireless Qi charger

Table 2. Product specifications

SECURITY	SPECIFICATIONS
Image authentication	Ensures only images encrypted by Cisco AES-128 bit key are allowed
Secure Boot	Ensures only authentic Cisco image can run on the device; image is encrypted with Cisco AES-128 bit key and digests are calculated using AES-CCM
GENERAL	SPECIFICATIONS
Weight	<ul style="list-style-type: none"> • Left earbud: 6g • Right earbud: 6g • Charging case: 53g
Dimensions	<ul style="list-style-type: none"> • Earbuds: 22.5 W x 34.8 H x 22.7 D mm • Charging case: 66.2 W x 48.2 H x 28.1 D mm
Colour	Black Anthracite
Materials	Aluminium, tempered glass, polymer, silicone
Integrated LED lights in case	Status LED and Battery LED
Waterproof (earbuds)	Yes (IP57)
Operating temperature	+5 °C to 40 °C
Non-operating temperature shock	-10°C to +55°C

Table 2. Product specifications

GENERAL	SPECIFICATIONS
Humidity	<ul style="list-style-type: none"> Operating 10% to 90% RH, non-condensing Non-operating 30% to 70% RH, non-condensing
Contents included in the box	<ul style="list-style-type: none"> Earbuds left and right Charging case with wireless Qi receiver USB-A cable (0.5 m) Silicone ear tips: XS, S, M – default mounted, L) COMPLY™ foam ear tips: M Pointer Card
Cisco USB HD Adapter	Compatible and available to purchase as a spare accessory
Mobile app	Bang & Olufsen app (Apple App Store, Google Market, Baidu, Huawei)
Exchangeable ear tips	Yes

Ordering information

The Bang & Olufsen Cisco 950 is available now. To order, visit the [Cisco Ordering Home Page](#).

Table 3. Ordering information

PART NUMBER	PRODUCT DESCRIPTION
HS-WL-950-BUN-C	950 True Wireless, In-Ear Earbuds with charging case in Black Anthracite finish, USB-A cable, 4 sets of silicon ear tips and 1 set of COMPLY™ foam ear tips

Warranty information

The Bang & Olufsen Cisco 950 has a one-year limited liability warranty.

Cisco environmental sustainability

Information about Cisco’s environmental sustainability policies and initiatives for our products, solutions, operations, and extended operations or supply chain is provided in the “Environment Sustainability” section of Cisco’s Corporate Social Responsibility (CSR) Report.

Reference links to information about key environmental sustainability topics (mentioned in the “Environment Sustainability” section of the CSR Report) are provided in the following table:

Table 4. Environmental sustainability reference links

SUSTAINABILITY TOPIC	REFERENCE
Information on product material content laws and regulations	Materials
Information on electronic waste laws and regulations, including products, batteries and packaging	WEEE compliance

Cisco makes the packaging data available for informational purposes only. It may not reflect the most current legal developments, and Cisco does not represent, warrant, or guarantee that it is complete, accurate, or up to date. This information is subject to change without notice.

October 2023



For more information
Please visit cisco.com/go/headsets