


### Overview



- |                       |                                                                                                                                                                                                                                           |                     |                                                                                                                                                                               |
|-----------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>1. Menu</b>        | Opens, selects or exits the OSD menu.                                                                                                                                                                                                     | <b>4. OK/auto</b>   | If the OSD menu is on, press to select the highlighted menu item.<br>If the OSD menu is inactive, press to activate the auto adjustment feature to optimize the screen image. |
| <b>2. Minus</b>       | If the OSD menu is on, press to navigate backward through the OSD menu and decrease adjustment levels.                                                                                                                                    | <b>5. Power</b>     | Turns the monitor on or off.                                                                                                                                                  |
| <b>3. Plus/source</b> | If the OSD menu is on, press to navigate forward through the OSD menu and increase adjustment levels.<br>If the OSD menu is inactive, press to activate the source button that chooses the video signal input (VGA, DVI, or DisplayPort). | <b>6. Power LED</b> | Blue = Fully powered.<br>Amber = Sleep mode.<br>Flashing Amber = Sleep Timer mode.                                                                                            |

### Model

XN375A\*

COH31AA/A8#ABA (Head only)

### Technical Specifications

<b>Panel</b>	<b>Type</b>	TN (Twisted Nematic) LED Backlit LCD
	<b>Viewable Image Area</b> (diagonal)	<b>58,42 cm.</b> (23 in.) widescreen; diagonally measured
	<b>Screen Opening</b> (W x H)	<b>50,92 x 28,64 cm.</b> (20.05 x 11.28 in.)
	<b>Aspect Ratio</b>	16:9
	<b>Viewing Angle</b> (typical)	Up to 170° horizontal/160° vertical (10:1 minimum contrast ratio)
	<b>Brightness</b> (typical)*	250 nits (cd/m <sup>2</sup> )
	<b>Contrast Ratio</b> (typical)*	1000:1
	<b>Dynamic Contrast Ratio</b> (typical)*	1,000,000:1
	<b>Response Time</b> (typical)*	5 ms (on/off)
	<b>Pixel Pitch</b>	0.265 mm
	<b>Backlight Lamp Life</b> (to half brightness)	30,000 hours minimum
	<b>Colour Support</b>	Over 16 million colours (through FRM)
	<b>Colour Gamut</b> (typical)	68%
<i>*All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.</i>		
<b>On Screen Display (OSD) Controls</b>	<b>Buttons or Switches</b>	"Menu" "-" "+" "OK" "Power"
	<b>Languages</b>	English, French, German, Italian, Dutch, Spanish, Japanese, Portuguese, Traditional Chinese, and Simplified Chinese
	<b>User Controls</b>	Brightness, contrast, positioning, colour temperature (warm, standard, cool, custom), image control (clock, clock phase, scaling, sharpness, DCR), monitor management, source control, information and factory reset
<b>Signal Interface/ Performance</b>	<b>Horizontal Frequency</b>	24 to 94 kHz
	<b>Vertical Frequency</b>	50 to 76 Hz
	<b>Native Resolution</b>	1920 x 1080 @ 60 Hz
	<b>Preset VESA Graphic Modes</b> (non-interlaced)	1920 x 1080 @ 60 Hz 1680 x 1050 @ 60 Hz 1440 x 900 @ 60 Hz 1280 x 1024 @ 60 Hz 1280 x 720 @ 60 Hz 1024 x 768 @ 60 Hz 800 x 600 @ 60 Hz 720 x 400 @ 70 Hz 640 x 480 @ 60 Hz
	<b>Text Mode</b>	720 x 400 @ 70 Hz
	<b>Maximum Pixel Clock Speed</b>	200 MHz (VGA); 165MHz (DVI and DisplayPort)

### Technical Specifications

	<b>User Programmable Modes</b>	Yes (10)
	<b>Anti-Glare</b>	Yes
	<b>Default Colour Temperature</b>	Warm (6500K)
<b>Video/Other Inputs</b>	<b>Plug and Play</b>	Yes
	<b>Input Connectors</b>	VGA (analog), DVI-D and DisplayPort w/ HDCP, USB 2-port hub
	<b>Input Impedance</b>	75 Ohms (VGA)
	<b>Sync Input</b>	TTL separate synch
	<b>Video/Other Cables</b>	(1) (1) DVI-D cable, (1) VGA cable, (1) USB cable
	<b>Cable Lengths</b>	<b>1,8 m.</b> (5.9 ft.)
<b>Power</b>	<b>Input Power</b>	100 - 240 VAC, 50/60 Hz
	<b>Typical Power Consumption</b>	33 W
	<b>Maximum</b>	41.5 W
	<b>Power Saving</b>	< 0.5 W standby; < 0.5 W off
	<b>Power Cable Length</b>	<b>1,9 m.</b> (6.2 ft.)
<b>Mechanical</b>	<b>Dimensions (W x D x H)</b>	<b>Unpacked w/stand</b> <b>55,15 x 24,94 x 35,1 to 46,7 cm.</b> (21.71 x 9.82 x 13.82 to 18.39 in.)
		<b>Unpacked w/o stand</b> <b>55,51 x 4,95 x 33,42 cm.</b> (head only) (21.69 x 1.95 x 13.16 in.)
		<b>Packaged</b> <b>62,4 x 50,2 x 16,9 cm.</b> (24.57 x 19.76 x 6.65 in.)
	<b>Weight</b>	<b>Head Only</b> <b>4,4kg.</b> (9.68 lb.)
		<b>Head Only (Packaged)</b> <b>7,0 kg.</b> (15.4 lb.)
		<b>Unpacked</b> <b>6,8 kg.</b> (15.0 lb.)
		<b>Packaged</b> <b>9,2 kg.</b> (20.3 lb.)
	<b>Tilt Range</b>	-5° to +30°
	<b>Swivel Range</b>	Yes 360°
	<b>Height Adjustable</b>	Yes - from <b>0 to 13,0 cm.</b> (0 to 5.1 in.)
	<b>Pivot Rotation</b>	Yes
	<b>Base</b>	Detachable, ships attached
<b>Environmental</b>	<b>Temperature - Operating</b>	<b>5° to 35° C</b> (41° to 95° F)
	<b>Temperature - Non-operating</b>	<b>-20° to 60° C</b> (-4° to 140° F)
	<b>Humidity - Operating</b>	20% to 80% non-condensing
	<b>Humidity - Non-operating</b>	5% to 95%, 38.7° C max wet-bulb
	<b>Altitude - Operating</b>	<b>0 to 5000 m.</b> (16,400 ft.)
	<b>Altitude - Non-operating</b>	<b>0 to 12192 m.</b> (40,000 ft.)
	<b>White LED Backlights</b>	Yes

### Technical Specifications

<b>Environmental Data</b>	<p><b>CCFL Panel</b> No</p> <p><b>Arsenic-Free Glass<sup>4</sup></b> Yes</p> <p><b>BFR/PVC Free</b> Plastics and Finishes or Paint</p> <p><b>Mercury Free</b> Yes</p> <p><b>Eco-Label Certifications &amp; Declarations</b> This product has received or is in the process of being certified to the following approvals and may be labeled with one or more of these marks:</p> <ul style="list-style-type: none"> <li>● US Energy Star®</li> <li>● IT ECO declaration</li> <li>● EPEAT® Gold where HP registers commercial display products. See <a href="http://www.epeat.net">http://www.epeat.net</a> for registration status in your country.</li> </ul>																
	<p><b>Energy Consumption (in accordance with US Energy Star® test method)</b></p> <table border="0"> <thead> <tr> <th></th> <th><b>115VAC, 60Hz</b></th> <th><b>230VAC, 50Hz</b></th> <th><b>100VAC, 60Hz</b></th> </tr> </thead> <tbody> <tr> <td>Normal Operation</td> <td>22.61 W</td> <td>22.55 W</td> <td>22.67 W</td> </tr> <tr> <td>Sleep</td> <td>0.25 W</td> <td>0.25 W</td> <td>0.31 W</td> </tr> <tr> <td>Off</td> <td>0.22 W</td> <td>0.21 W</td> <td>0.28 W</td> </tr> </tbody> </table>		<b>115VAC, 60Hz</b>	<b>230VAC, 50Hz</b>	<b>100VAC, 60Hz</b>	Normal Operation	22.61 W	22.55 W	22.67 W	Sleep	0.25 W	0.25 W	0.31 W	Off	0.22 W	0.21 W	0.28 W
	<b>115VAC, 60Hz</b>	<b>230VAC, 50Hz</b>	<b>100VAC, 60Hz</b>														
Normal Operation	22.61 W	22.55 W	22.67 W														
Sleep	0.25 W	0.25 W	0.31 W														
Off	0.22 W	0.21 W	0.28 W														
	<p><b>Heat Dissipation*</b></p> <table border="0"> <thead> <tr> <th></th> <th><b>115VAC, 60 Hz</b></th> <th><b>230VAC, 50 Hz</b></th> <th><b>100VAC, 60 Hz</b></th> </tr> </thead> <tbody> <tr> <td>Normal Operation</td> <td>77 BTU/hr</td> <td>77 BTU/hr</td> <td>77 BTU/hr</td> </tr> <tr> <td>Sleep</td> <td>0.8 BTU/hr</td> <td>0.8 BTU/hr</td> <td>1 BTU/hr</td> </tr> <tr> <td>Off</td> <td>0.7 BTU/hr</td> <td>0.7 BTU/hr</td> <td>0.9 BTU/hr</td> </tr> </tbody> </table> <p>* Heat dissipation is calculated based on the measured watts, assuming the service level is attained for one hour.</p>		<b>115VAC, 60 Hz</b>	<b>230VAC, 50 Hz</b>	<b>100VAC, 60 Hz</b>	Normal Operation	77 BTU/hr	77 BTU/hr	77 BTU/hr	Sleep	0.8 BTU/hr	0.8 BTU/hr	1 BTU/hr	Off	0.7 BTU/hr	0.7 BTU/hr	0.9 BTU/hr
	<b>115VAC, 60 Hz</b>	<b>230VAC, 50 Hz</b>	<b>100VAC, 60 Hz</b>														
Normal Operation	77 BTU/hr	77 BTU/hr	77 BTU/hr														
Sleep	0.8 BTU/hr	0.8 BTU/hr	1 BTU/hr														
Off	0.7 BTU/hr	0.7 BTU/hr	0.9 BTU/hr														
	<p><b>Additional Information</b></p> <ul style="list-style-type: none"> <li>● This product is in compliance with the Restrictions of Hazardous Substances (RoHS) directive - 2002/95/EC.</li> <li>● This HP product is designed to comply with the Waste Electrical and Electronic Equipment (WEEE) Directive - 2002/96/EC.</li> <li>● This product is in compliance with California Proposition 65 (State of California; Safe Drinking Water and Toxic Enforcement Act of 1986).</li> <li>● This product is in compliance with the IEEE 1680 (EPEAT®) standard at the Gold level, see <a href="http://www.epeat.net">www.epeat.net</a></li> <li>● Plastics parts weighing over 25 grams used in the product are marked per ISO 11469 and ISO1043.</li> <li>● This product contains 0.14% post-consumer recycled plastic (by wt.)</li> <li>● This product is 98.0% recycle-able when properly disposed of at end of life.</li> </ul>																
	<p><b>Packaging Materials</b></p> <table border="0"> <tr> <td><b>External:</b></td> <td>Corrugated carton</td> <td>1500g</td> </tr> <tr> <td><b>Internal:</b></td> <td>Polyethylene low density</td> <td>36g</td> </tr> </table>	<b>External:</b>	Corrugated carton	1500g	<b>Internal:</b>	Polyethylene low density	36g										
<b>External:</b>	Corrugated carton	1500g															
<b>Internal:</b>	Polyethylene low density	36g															
	<p><b>RoHS Compliance</b> Hewlett-Packard is committed to compliance with all applicable environmental laws and regulations, including the European Union Restriction of Hazardous Substances (RoHS) Directive. HP's goal is to exceed compliance obligations by meeting the requirements of the RoHS Directive on a worldwide basis. By July 1, 2006, RoHS substances will be virtually eliminated (virtually = to levels below legal limits) for all HP electronic products subject to the RoHS Directive,</p>																

### Technical Specifications

#### Material Usage

except where it is widely recognized that there is no technically feasible alternative (as indicated by an exemption under the EU RoHS Directive).

This product does not contain any of the following substances in excess of regulatory limits (refer to the HP General Specification for the Environment at [http://www.hp.com/hpinfo/globalcitizenship/environment/supplychain/gen\\_specifications.html](http://www.hp.com/hpinfo/globalcitizenship/environment/supplychain/gen_specifications.html)):

- Asbestos
- Certain Azo Colorants
- Certain Brominated Flame Retardants - may not be used as flame retardants in plastics
- Cadmium
- Chlorinated Hydrocarbons
- Chlorinated Paraffins
- Formaldehyde
- Halogenated Diphenyl Methanes
- Lead carbonates and sulfates
- Lead and Lead compounds
- Mercuric Oxide Batteries
- Nickel - finishes must not be used on the external surface designed to be frequently handled or carried by the user.
- Ozone Depleting Substances
- Polybrominated Biphenyls (PBBs)
- Polybrominated Biphenyl Ethers (PBBEs)
- Polybrominated Biphenyl Oxides (PBBOs)
- Polychlorinated Biphenyl (PCB)
- Polychlorinated Terphenyls (PCT)
- Polyvinyl Chloride (PVC) - except for wires and cables, and certain retail packaging has been voluntarily removed from most applications.
- Radioactive Substances
- Tributyl Tin (TBT), Triphenyl Tin (TPT), Tributyl Tin Oxide (TBTO)

#### Packaging

HP follows these guidelines to decrease the environmental impact of product packaging:

- Eliminate the use of heavy metals such as lead, chromium, mercury and cadmium in packaging materials.
- Eliminate the use of ozone-depleting substances (ODS) in packaging materials.
- Design packaging materials for ease of disassembly.
- Maximize the use of post-consumer recycled content materials in packaging materials.
- Use readily recyclable packaging materials such as paper and corrugated materials.
- Reduce size and weight of packages to improve transportation fuel efficiency.
- Plastic packaging materials are marked according to ISO 11469 and DIN 6120 standards.

#### End-of-life Management and Recycling

Hewlett-Packard offers end-of-life HP product return and recycling programs in many geographic areas. To recycle your product, please go to: <http://www.hp.com/go/reuse-recycle> or contact your nearest HP sales office. Products returned to HP will be recycled, recovered or disposed of in a

### Technical Specifications

responsible manner.

The EU WEEE directive (2002/95/EC) requires manufacturers to provide treatment information for each product type for use by treatment facilities. This information (product disassembly instructions) is posted on the Hewlett Packard web site at: <http://www.hp.com/go/recyclers>. These instructions may be used by recyclers and other WEEE treatment facilities as well as HP OEM customers who integrate and re-sell HP equipment.

For more information about HP's commitment to the environment:

#### **Hewlett-Packard Corporate Environmental Information**

Global Citizenship Report

<http://www.hp.com/hpinfo/globalcitizenship/gcreport/index.html>

Eco-label certifications

<http://www.hp.com/hpinfo/globalcitizenship/environment/productdesign/ecolabels.html>

ISO 14001 certificates:

<http://www.hp.com/hpinfo/globalcitizenship/environment/operations/envmanagement.html>

#### **Options**

##### **HP Single Monitor Arm Part number BT861AA**

The flexible design of the HP Single Monitor Arm provides a seemingly endless range of display adjustments with an amazing 13 inches of lift, 50 degrees of tilt, and 360 degrees of pan and rotation - all at your fingertips -- helping you stay comfortable and productive throughout the day.

##### **HP Adjustable Dual Display Stand Part Number AW664AA**

Premium space-saving dual screen solution provides access to more monitor real estate and makes it possible to manage multiple applications simultaneously. Weight adjustable for dual monitors from 17-24". Rotate displays into portrait/landscape positions.

##### **HP LCD Speaker Bar Part number NQ576AA**

Powered directly by the connected PC, the Speaker Bar seamlessly attaches to the monitor's lower bezel to bring full audio support to select HP flat panel monitors. Features include dual speakers with full sound range and dual external headphone jacks.

##### **HP LCD Monitor Quick Release Part number EM870AA<sup>1</sup>**

An easy-to-use, VESA-compliant, LCD monitor mounting solution that allows you to quickly and securely attach an LCD monitor to a variety of stands, brackets, arms or wall mounts.

##### **HP Integrated Work Centre Stand—Part number LH526AA**

Allows mounting of a 17 - 24 inch (43.18- to 60.96 cm) diagonal HP LCD monitor and an HP Compaq 8000 series Ultra-slim Desktop PC as well as select HP Thin Clients on a single stand for the convenience of an "all-in-one" form factor. For more information, refer to this product's QuickSpecs document.

##### **HP Integrated Work Centre 2 - Small Form Factor (SFF) - Part number QP897AA**

Designed specifically for use with the HP Compaq Small Form Factor (SFF) Desktop PC and a 17 to 24-inch (43.18 to 60.96 cm) diagonal monitor, the HP Integrated Work Centre 2 (IWC) - Small Form Factor (SFF) provides a portable, compact workspace to help maximize space-constrained work environments. (17 to 24-inch diagonal monitors need to meet supported weight limits of 7.5 to 12.1 lbs. (3.38 to 5.5 kg). For more information, refer to the product's QuickSpecs.

##### **HP USB Graphics Adapter Part number NL571AA**

Enables connection of up to six simultaneous displays to help you boost productivity and multi-task across several open applications. Use one Adapter to bridge between a notebook or desktop PC and second monitor or use multiple Adapters to connect several displays to each other.

### Technical Specifications

<b>HP Business PC Security Lock Kit</b> <b>Part number PV606AA</b>	Attaches to the rear of the PC with a six-foot steel cable that can be used to secure a PC or peripherals such as mice, keyboards, monitors or USB security devices to protect them against unauthorized removal by physically connecting the system to an anchor point.
<b>HP DisplayPort Cable Kit</b> <b>Part number VN567AA</b>	Connects a DisplayPort connector on an HP Business Desktop computer to a DisplayPort connector on a monitor.
<b>HP USB HD 720P Business Webcam</b> <b>Part Number QP896AA</b>	Enjoy live video conferencing in 720p high-definition <sup>1</sup> with this small and stylish webcam that captures images and video. Attach it to your monitor with a clip or sit it on your desk, and then connect to your desktop through a USB port. Meet face to face over the Internet (Internet service required and sold separately) with co-workers and clients.
<b>Other</b>	
<b>Accessories Included</b>	AC Power cable, VGA cable, DVI-D cable, USB cable
<b>Software</b>	Yes - HP Display Asst, Auto Adjustment Pattern Utility, Monitor Driver, PDF Complete (v35109 rc4)
<b>User Guide Languages</b>	English, Danish, Dutch, Finnish, French, German, Italian, Norwegian, Spanish (International), Swedish, Czech, Greek, Hungarian, Polish, Russian, Slovenian, Turkish, Arabic, Portuguese (Brazilian), Bahasa Indonesia, T. Chinese, S. Chinese, Japanese
<b>Warranty Languages</b>	English, German, French, Italian, Turkish, Greek, Arabic, Hungarian, Czech, Russian, Polish, Japanese, Dutch, Danish, Finnish, Portuguese, Norwegian, Swedish, T. Chinese, Korean, Slovenian, Bahasa, Spanish
<b>Colour</b>	Black
<b>VESA External Mounting</b>	Yes (one set of standard 4-hole pattern, 100 mm).
<b>Security Lock-Ready</b>	Yes
<b>Certification and Compliance</b>	TCO 5.0, VCCI, KC, CECP, FCC, CE, BSMI, ISC, C-Tick, Gost, E-Standy, RoHS, WEEE, ETL, CCC, Energy Star <sup>®</sup> 5.0, NOM, KCC, BSMI, TUV, Microsoft WHQL, China Energy Label Grade 1, EPEAT <sup>®</sup> Gold <sup>3</sup>
<b>Compatibility</b>	Recommended for use with HP products.
<b>Service and Warranty</b>	Protected by HP, including a 3 years parts, 3 years labour, and 3 years onsite service (3/3/3) standard limited warranty. Certain restrictions and exclusions apply. <sup>2</sup>

### Technical Specifications

© Copyright 2012 Hewlett-Packard Development Company, L.P.

ENERGY STAR® is a US registered mark of the United States Environmental Protection Agency.

<sup>1</sup> The HP Quick Release has been designed to support a maximum of up to 24 lbs (10.9 kg) for all devices mounted. Because mounting surfaces vary widely and the final mounting method and configuration may vary, mounting fasteners are not supplied (other than the VESA-compliant screws). HP recommends that you consult with a qualified engineering, architectural or construction professional to determine the appropriate type and quantity of mounting fasteners required for your application and to ensure that your mounting solution is properly installed to support applied loads.

<sup>2</sup> HP Care Pack Services extend service contracts beyond the standard warranties. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts from date of hardware purchase. To choose the right level of service for your HP product, use the HP Care Pack Services Lookup Tool at: <http://www.hp.com/go/lookuptool>. Additional HP Care Pack Services information by product is available at: <http://www.hp.com/hps/carepack>.

<sup>3</sup> EPEAT Gold where HP registers commercial display products. See [www.epeat.net](http://www.epeat.net) for registration status in your country.

<sup>4</sup> Arsenic and its compounds were not detected using US EPA Test Methods 3052 & 3052/6010b by ICP or ICP-AES.

All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.