

PERFORMANCE

Processor

Intel® Core™ i5-14500T, 14C (6P + 8E) / 20T, P-core 1.7 / 4.8GHz, E-core 1.2 / 3.4GHz, 24MB

AI PC Category^[1]

AI PC

NPU

Discrete NPU card, up to 30 TOPS

Graphics^[2]

NVIDIA® GeForce RTX™ 4060 8GB GDDR6

Chipset

Intel® Q670 Chipset

Memory

1x 16GB SO-DIMM DDR5-4800

Memory Slots

Two DDR5 SO-DIMM slots, dual-channel capable

Max Memory^[3]

Up to 64GB DDR5-5200

Storage

256GB SSD M.2 2280 PCIe® 4.0x4 NVMe® Opal 2.0

Storage Support^[4]

Dual SSD mode: up to two drives, 2x M.2 SSD
• M.2 2280 SSD up to 2TB

RAID Preset

None

Card Reader

No card reader

Optical

None

Audio Chip

High Definition (HD) Audio

Speakers

2Wx1

Power Supply

350W 92%

DESIGN

Keyboard

USB Calliope Keyboard, Black, English

Mouse

USB Calliope Mouse, Black

Expansion Slots

Four M.2 slots (one for WLAN, one for AI Card, two for SSD)

Case Color

Luna Grey

Pen

Pen Not Supported

Form Factor

Tiny (3.6L)

Dimensions (WxDxH)^[5]

195 x 191 x 108 mm (7.68 x 7.52 x 4.25 inches)

Weight^[6]

Around 3.5 kg (7.72 lbs)

CONNECTIVITY

WLAN + Bluetooth®

Intel® Wi-Fi® 6E AX211, 802.11ax 2x2 + BT5.3, vPro®

WWAN

Non-WWAN

Ethernet

Integrated 100/1000M

Front Ports

- 1x USB-C® (USB 20Gbps / USB 3.2 Gen 2x2), data transfer only
- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2), one supports 5V@2.1A charging
- 1x headphone / microphone combo jack (3.5mm)

Rear Ports

- 2x USB-A (USB 10Gbps / USB 3.2 Gen 2)
- 2x USB-A (USB 5Gbps / USB 3.2 Gen 1)
- 1x HDMI® 2.1 TMDS
- 1x HDMI® 2.1a FRL
- 4x DisplayPort™ 1.4a
- 1x Ethernet (GbE RJ-45)

Optional Rear Ports (configured)

- 2x DP 1.4
- 1x HDMI® 2.1a FRL, 3x DP 1.4a (HBR3, DSC) on NVIDIA® GeForce RTX™ 4060

SECURITY & PRIVACY

Security Chip

Firmware TPM 2.0 integrated in chipset

Fingerprint Reader

No fingerprint reader

Physical Locks

Kensington® Security Slot™

MANAGEABILITY

System Management^[7]

Intel® vPro® Enterprise

SERVICE

Base Warranty

1-year, Onsite

Included Upgrade

None

CERTIFICATIONS

Green Certifications

- ENERGY STAR® 8.0
- ErP Lot 3
- GREENGUARD®
- RoHS compliant
- TCO Certified

SOFTWARE

Operating System

Windows® 11 Pro, English

Bundled Software

None

ACCESSORIES

Bundled Accessories

None

MODEL

TopSeller	: Yes	Announce Date	: 2025-04-29
EAN / UPC / JAN	: 198158920773	End of Support	: 2031-01-29



Product image is a sample, it may not match the real color of this model

Note:

[1] AI PCs have a NPU capable of 10+ TOPs to run the Copilot assistant by pressing the optional Microsoft Copilot key or using Win + C.

[2] The information of integrated graphics are not applicable for the models with processor which has no integrated graphics inside (for the details, please refer to processor section).

[3] The max memory is based on the test results with current Lenovo memory offerings.

[4] The max capacity of each disk type is based on the test results with current Lenovo storage offerings.

[5] The system dimensions may vary depending on configurations.

[6] The system weight is approximate and based on results in.....

• Lenovo reserves the right to change specifications without notice.

To see more note information, please link to

<https://psref.lenovo.com/Detail/2489?M=12W1003EUS>

Premier Support - A direct 24x7x365 line to our most elite technicians.



Advanced technical support, 24x7x365, in more than 100 markets



Technical Account Managers for proactive relationship and escalation management



Comprehensive hardware & OEM software support



Priority on service delivery and repair parts



Single point of contact for simplified end-to-end case management



Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - Protection of your PC from the unexpected.

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - Included with the systems you purchase, default 1- or 3-year coverage window.

Warranty Extensions & Upgrades - Service and protection that's right for your circumstances.

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



ThinkCentre Tiny VESA Mount II

4XFON03161

The ThinkCentre Tiny VESA Mount II is a unique design specific to house the Tiny PC while featuring the universal VESA mount configuration. The VESA standard enables this mount to attach to anything that is VESA comp...



ThinkPad USB3.0 to Ethernet Adapter

4X90S91830

The ThinkPad USB3.0 to Ethernet Adapter is quick and easy way to connect your notebook and desktop to Ethernet connections. It's ideal for imaging of systems or transferring large files quickly.

For a full list of accessories and services, please visit:
<https://smartfind.Lenovo.com>

Lenovo

PSREF
Product Specifications
Reference