

Single Desk-Mount Monitor Arm | Full Motion Articulating with 2x USB 3.0 Ports



Actual product may vary from photos

User Manual SKU#: ARMPIVOT2USB3

For the latest information and specifications visit www.startech.com/ARMPIVOT2USB3



Compliance Statements

Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of third-party companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. Regardless of any direct acknowledgement elsewhere in the body of this document, StarTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.



Warning Statements

• Make sure that you assemble this product according to the instructions.

Do not exceed the weight capacity of this product. Overloading this
product might result in injury or property damage. This product can
support the following weight: 17.6 lb. (8 kg).

This product is intended for indoor use only and should not be used

outdoors.

Varningsmeddelanden

Se till att du monterar produkten i enlighet med instruktionerna.

 Överskrid inte produktens viktkapacitet. Överbelastning av produkten kan orsaka skada på person eller egendom. Denna produkt har stöd för föliande vikter: 8 kg.

Produkten är endast avsedd för användning inomhus och ska inte

användas utomhus.

Avertissements

Assemblez ce produit conformément aux instructions.

 Ne dépassez pas la capacité pondérale du produit. Une surcharge du produit peut entraîner des blessures ou des dommages matériels. Ce produit peut supporter 8 kg.

• Ce produit est uniquement destiné à une utilisation en intérieur et ne

doit pas être utilisé à l'extérieur.

Warnhinweise

Beachten Sie bei der Montage dieses Produkts die

Montageanweisungen.

 Überschreiten Sie nicht die Tragkraft dieses Produkts. Ein Überladen dieses Produkts kann zu Verletzungen oder zur Beschädigung des Produkts führen. Dieses Produkt ist für folgendes Gewicht geeignet: 8 ka.

 Dieses Produkt ist nur zum Gebrauch in Innenräumen vorgesehen und sollte nicht im Freien verwendet werden.

Dichiarazioni di avvertenza

Assicurarsi di Assemblare il prodotto secondo le istruzioni.

 Non superare la capacità di carico del prodotto. Il sovraccarico del prodotto potrebbe causare danni o lesioni. Il prodotto è in grado di supportare i seguenti pesi: 8 kg.



 Il prodotto è destinato all'uso in ambienti interni. Se ne sconsiglia l'impiego in ambienti esterni.

Mensagens de aviso

- Certifique-se de que monta este produto de acordo com as instruções.
- Não exceda a capacidade de peso deste produto. Sobrecarregar este produto pode resultar em ferimentos ou danos de propriedade. Este produto pode suportar o seguinte peso: 8 kg.
- Este produto destina-se apenas a uma utilização no interior e não deve ser utilizado no exterior.
- Este produto requer uma ligação à terra. Não utilize este produto sem uma ligação à terra.

Advertencias de uso

- Asegúrese de ensamblar este producto según las instrucciones.
- Asegúrese de no exceder la capacidad de peso de este producto. La sobrecarga de este producto puede causar lesiones personales o daños en la propiedad. Este producto tiene capicidad para el siguiente peso: 8 kg.
- El uso de este producto es solo para interiores y no debe utilizarse en exteriores.

Waarschuwingen

- Zorg dat u dit product volgens de instructies in elkaar zet.
- Overschrijd de maximale capaciteit van dit product niet. Overbelasting van dit product kan letsel of materiële schade veroorzaken. Dit product ondersteunt het volgende gewicht: 8 kg.
- Dit product is alleen bedoeld voor binnengebruik en mag niet buiten worden gebruikt.

注意

- 必ず取扱説明書に従って本製品の組み立てを行って下さい。
- 本製品で定められた最大積載重量を超えないようにして下さい。最大積載重量をオーバーした場合、怪我をする恐れや器物破損の恐れがあります。本製品は、モニター1台あたり8kgまで支持できます。
- 本製品は、室内での使用を想定しています。戸外では使用しないで下さい。



Safety Statements

Safety Measures

 Cables (including power and charging cables) should be placed and routed to avoid creating electric, tripping or safety hazards.

Mesures de sécurité

 Les câbles (y compris les câbles d'alimentation et de chargement) doivent être placés et acheminés de façon à éviter tout risque électrique, de chute ou de sécurité

安全対策

ケーブル(電源ケーブルと充電ケーブルを含む)は、適切な配置と引き回しを行い、電気障害やつまづきの危険性など、安全上のリスクを回避するようにしてください。

Misure di sicurezza

 I cavi (inclusi i cavi di alimentazione e di ricarica) devono essere posizionati e stesi in modo da evitare pericoli di inciampo, rischi di scosse elettriche o pericoli per la sicurezza.

Säkerhetsåtgärder

 Kablar (inklusive elkablar och laddningskablar) ska dras och placeras på så sätt att risk för snubblingsolyckor och andra olyckor kan undvikas.




Table of Contents

Compliance Statements	1
Warning Statements	2
Safety Statements	4
Product Diagram	6
Product Dimensions	7
Product Rotation	8
Product Information	9
Pack Contents	9
Product Specifications	13
Requirements	15
Assembling the Monitor Mount Using the C-Clamp	16
Assembling the Monitor Mount Using the Grommet Clamp	24
Mounting the Monitor	33
Adjusting the Monitor Mount	36
Adjusting the Spring Arm Tension	36
Adjusting the Tilt	37
Routing the Cables	39
Using the 3.0 USB Passthough Ports	41




Product Diagram



 $To \ view \ manuals, videos, drivers, downloads, technical \ drawings, and \ more \ visit \ www.startech.com/support$




Product Dimensions





Product Rotation




To view manuals, videos, drivers, downloads, technical drawings, and more visit www.startech.com/support




Product Information


Pack Contents


















Product Specifications

75 x 75 100 x 100
- 90° to + 90°
- 90° to + 90°
17.6 lb. (8 kg)



	15" to 34"
Screen Size	
	-90º to +90º
Swivel	



Requirements

Tools

· Phillips Head Screwdriver x 1

Displays

• 15" to 34" Display x 1


Optional

- USB Cables x 2
- USB Compatible Devices x 2



Assembling the Monitor Mount Using the C-Clamp

 Using the 6 mm Hex Key loosen the C-Clamp Screw, opening the C-Clamp to the thickness of the Mounting Surface you wish to mount the Monitor Mount to. The C-Clamp Screw is located in the center of the Mounting Peg on the Base Clamp Assembly.




Loosening the C-Clamp Screw

Align the C-Clamp with the edge of the Mounting Surface.




Gently push the USB Cables coming out of the back of the Base Clamp Assembly into the two Cable Grooves on the back of the Base Clamp Assembly.



Routing the USB Cables Through the Cable Grooves

- 4. Slide the **C-Clamp** over the edge of the **Mounting Surface**. The **C-Clamp** accommodates ranges from 10 mm (.3") to 50 mm (1.9").
- While supporting the C-Clamp under the Mounting Surface, use the 6 mm Hex Key to tighten the C-Clamp Screw until the C-Clamp Plate is pressed tightly against the bottom of the Mounting Surface.






Tightening the C-Clamp Screw

- Align the Pole with the Mounting Hole on the Base Clamp Assembly.
- Using your hand, screw the Pole into the Base Clamp Assembly.
- Using the 3 mm Hex Key, tighten the small screw located on the Neck of the Mounting Hole on the Base Clamp Assembly to secure the Pole.






Mounting the Pole to the Base Clamp Assembly

Slide the Cable Clip over-top of the Pole, sliding it down into position.






Sliding the Cable Clip over-top of the Pole

- 10. Slide the **Arm Shoulder** over-top of the **Pole**, sliding it down into position.
- 11. Turn the **Locking Lever** on the **Arm Shoulder** clock-wise, securing the **Arm Shoulder** into place.

Note: The **Locking Lever** may require multiple turns in order to properly secure the **Arm Shoulder** in place.

To view manuals, videos, drivers, downloads, technical drawings, and more visit www.startech.com/support






Installing the Arm Shoulder

- 12. Align the **Mounting Peg** on the bottom of the **Lower Arm** with the **Mounting Hole** on the **Arm Shoulder**.
- 13. Slide the Mounting Peg on the Lower Arm into the Mounting Hole on the Arm Shoulder.
- 14. Using the 3 mm Hex Key, tighten the small screw located on the Arm Shoulder to secure the Lower Arm.






Installing the Lower Arm

- 15. Align the **Mounting Peg** on the bottom of the **Upper Arm** with the **Mounting Hole** on the top of the **Lower Arm**.
- 16. Slide the Mounting Peg on the Upper Arm into the Mounting Hole on the Lower Arm.






Mounting the Upper Arm to the Lower Arm

17. Using the 3 mm Hex Key to tighten the Screw on the Lower Arm securing it to the Upper Arm.






Tightening the Screw on the Lower Arm

Assembling the Monitor Mount Using the Grommet Clamp

- While holding the C-Clamp, use the 6 mm Hex Key to loosen the C-Clamp Screw and remove it from the Base Clamp Assembly. The C-Clamp Screw is located in the center of the Mounting Peg on the Base Clamp Assembly.
- Once the C-Clamp Screw is removed the C-Clamp will also detach from the Base Clamp Assembly.






Removing C-Clamp Screw and C-Clamp


- Align the Grommet Hole on the Base Clamp Assembly with the Grommet Hole on the Mounting Surface.
- Insert the Grommet Screw through the center of the Mounting Peg on the Base Clamp Assembly and out the Grommet Hole on the Mounting Surface.





Inserting the Grommet Screw

Underneath the Mounting Surface, thread the Grommet Hole on the Grommet Plate onto the Grommet Screw.




Aligning the Grommet Plate

To view manuals, videos, drivers, downloads, technical drawings, and more visit www.startech.com/support




While holding the Grommet Plate, use the 6 mm Hex Key, tighten the Grommet Screw, securing the Base Clamp Assembly to the Mounting Surface.



Tightening the Grommet Screw

- Align the Pole with the Mounting Hole on the Base Clamp Assembly.
- Using your hand screw the Pole into the Base Clamp Assembly.
- Using the 3 mm Hex Key, tighten the small screw located on the Neck of the Mounting Hole on the Base Clamp Assembly to secure the Pole.






Mounting the Pole to the Base Clamp Assembly

10. Slide the **Cable Clip** over-top of the **Pole**, sliding it down into position.






Sliding the Cable Clip over-top of the Pole

- 11. Slide the **Arm Shoulder** over-top of the **Pole**, sliding it down into position.
- 12. Turn the **Locking Lever** on the **Arm Shoulder** clock-wise, securing the **Arm Shoulder** into place.

Note: The **Locking Lever** may require multiple turns in order to properly secure the **Arm Shoulder** in place.

To view manuals, videos, drivers, downloads, technical drawings, and more visit www.startech.com/support






Installing the Arm Shoulder

- 13. Align the Mounting Peg on the bottom of the Lower Arm with the Mounting Hole on the Arm Shoulder.
- 14. Slide the Mounting Peg on the Lower Arm into the Mounting Hole on the Arm Shoulder.
- 15. Using the 3 mm Hex Key, tighten the small screw located on the Arm Shoulder to secure the Lower Arm.






Installing the Lower Arm

- 16. Align the Mounting Peg on the bottom of the Upper Arm with the Mounting Hole on the top of the Lower Arm.
- 17. Slide the **Mounting Peg** on the **Upper Arm** into the **Mounting Hole** on the **Lower Arm**.






Mounting the Upper Arm to the Lower Arm

18. Using the 3 mm Hex Key, tighten the Screw on the Lower Arm securing it to the Upper Arm.





Tightening the Screw on the Lower Arm


Mounting the Monitor

- 1. Place the **Monitor** screen side down on a flat, clean surface.
- (Optional) Remove any Screws or Place Holders from the VESA Mounting Holes on the back of the Monitor.
 - **Note:** Be careful not to remove any of the **Screws** holding the **Monitor's Casing** together.
- Align the Washers (included) with the VESA Mounting Holes on the back of the Monitor.



 Align the Screw Holes on the VESA Mount with the VESA Mounting Holes on the back of the Monitor. The VESA Mount can support a 75 x 75 or 100 x 100 mounting pattern.

Note When attached, the **Arrow** on the **VESA Mount** should be pointing toward the top of the **Monitor**.



Aligning the VESA Mount with Monitor


- Select the appropriate hardware for mounting the VESA Mount to the back of the Monitor either M4 x 12 mm, M5 x 12 mm, or customer sourced screws.
- Insert the appropriate Screws through the Screw Holes on the VESA Mount and into the VESA Mounting Holes on the back of the Monitor.
- Using a Phillips Head Screwdriver (or appropriate screwdriver) tighten the screws.

Note: Do not over-tighten the **Screws**. If you encounter resistance while you're tightening the **Screws**, stop tightening. Failure to do so could result in damage to the **Monitor**.



Note: It is recommended that two people mount the **Monitors**.

Pull the VESA Clip on the VESA Holder back towards the Spring Arm.



Pulling back the VESA Clip

Note: The **VESA Clip** on the **VESA Holder** should be at the top of the **VESA Holder** before mounting the **Monitor**.

- While holding the VESA Clip and supporting the weight of the Monitor, align the Mounting Plate of the VESA Mount with the VESA Holder on the Spring Arm.
- 10. Slide the Mounting Plate on the VESA Mount down into the VESA Holder until the Mounting Plate is sitting on the bottom of the VESA Holder.




11. While holding the **Monitor** in place, release the **VESA Clip**, securing the **Monitor** in place.

Adjusting the Monitor Mount

Adjusting the Spring Arm Tension


- Using your hand push downward on the Spring Arm and hold it in place.
- The Spring Arm should only be placed in a horizontal position or tilted downwards.



Correct Spring Arm Position

 Use the 6 mm Hex Key to rotate the Adjustment Screw located at the back of the Spring Arm, just above the joint. Rotate clockwise to increase tension or counter clockwise to decrease tension.






Adjusting the Spring Arm Tension

Note: Be careful not to pinch your hand when making adjustments to the **Monitor**.

Adjusting the Tilt

 Use the 6 mm Hex Key to loosen the Tilt Adjustment Screw located at the side of the VESA Holder.





Loosening the Tilt Adjustment Screw

2. Use your hand to adjust the tilt of the **Monitor**.


Note: Be careful not to pinch your hand when making adjustments to the **Monitor**.

When you have achieved the desired tilt, hold the Monitor in that position and tighten the Tilt Adjustment Screw.



Routing the Cables


 Slide the Cable Cover on the Lower Arm upward to remove the Cable Cover. The Cable Cover is located along the bottom of the Lower Arm.



Removing the Cable Cover

- 2. Run the **Monitor Cables** along the inside of the **Upper Arm**.
- Gently push the Monitor Cables into the Cable Clip located on the inside of the Upper Arm.






Routing the Monitor Cables Along the Upper Arm

- Route the Monitor Cables down the Lower Arm and through the Tool Clip on the back of the Base Clamp Assembly. Make sure that you leave enough slack in the Monitor Cable to compensate for arm movement and adjustments.
- Replace the Cable Cover removed in step 1 by sliding it down the Lower Arm, securing the Cable Cover to the Lower Arm. Be careful not to pinch the Monitor Cable between the Cable Cover and Lower Arm.
- Run the Monitor Cable down the Pole and through the Cable Clip.





Routing the Monitor Cables

Using the 3.0 USB Passthough Ports

- Plug the two USB Cables on the back of the Base into USB Ports on the Host Computer.
- Connect a USB Cable to the USB Ports on the front of the Base and the other end to a compatible USB Device.



Warranty Information

This product is backed by a two-year warranty.

For further information on product warranty terms and conditions, please refer to www.startech.com/warranty.

Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product.

Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.



Hard-to-find made easy. At StarTech.com, that isn't a slogan. It's a promise.

StarTech.com is your one-stop source for every connectivity part you need. From the latest technology to legacy products — and all the parts that bridge the old and new — we can help you find the parts that connect your solutions.

We make it easy to locate the parts, and we quickly deliver them wherever they need to go. Just talk to one of our tech advisors or visit our website. You'll be connected to the products you need in no time.

Visit www.startech.com for complete information on all StarTech.com products and to access exclusive resources and time-saving tools.

StarTech.com is an ISO 9001 Registered manufacturer of connectivity and technology parts. StarTech.com was founded in 1985 and has operations in the United States, Canada, the United Kingdom and Taiwan servicing a worldwide market.

Reviews

Share your experiences using StarTech.com products, including product applications and setup, what you love about the products, and areas for improvement.

StarTech.com Ltd.	StarTech.com LLP	StarTech.com Ltd	
45 Artisans Cres.	2500 Creekside Pkwy.	Unit B, Pinnacle	
London, Ontario	Lockbourne, Ohio	15 Gowerton Rd., Brackmills	
N5V 5E9	43137		
Canada L	U.S.A.	Northampton	
		NN4 7BW	
		United Kingdom	
FR: startech.com/fr	ES: startech.com/es	IT: startech.com/it	
DE: startech.com/de	NL: startech.com/nl	JP: startech.com/jp	