

Position a 100A fuse link less than 18 in. from the battery in the positive line to protect against high-current draw that may occur during inverter failure.

2400W PowerVerter APS 48VDC 120V Inverter/Charger with Auto-Transfer Switching, Hardwired, UL

MODEL NUMBER: **APS2448UL**



Portable UL-rated power source for any type of equipment from power tools to computers as a vehicle inverter, standalone AC power source or extended-run UPS. Ideal for RVs, construction equipment and emergency vehicles.

Description

The APS2448UL 2400W PowerVerter APS 48VDC 120V Inverter/Charger is a reliable power source for a wide variety of equipment ranging from power tools and pumps to portable lighting and computer equipment in heavy-load conditions. With no fumes, fuel or excess noise, it's an excellent alternative to generator power. And it's tested to meet UL (U.S.) and CSA (Canada) safety standards.

The DC-to-AC inverter features an automatic line-to-battery transfer switch and integrated charging system that allow it to work as an extended-run UPS, standalone AC power source or vehicle inverter. It delivers 2400W of continuous power, 3600W up to one hour, or 4800W of peak power up to 10 seconds during equipment startup or cycling. An automatic overload detector, cooling fan and resettable AC circuit breakers protect the unit from damage.

Designed for easy installation in RVs, commercial and fleet vehicles, emergency vehicles and construction equipment, the APS2448UL converts stored power from any 48V battery or automotive DC source to safe, stable, computer-grade AC power for unlimited runtime.

When hardwired to an external 120V AC source, the unit keeps the user-supplied battery charged via a three-stage 15A charging system while simultaneously delivering AC power to connected equipment.

When used as a UPS, the APS2448UL responds to blackouts and brownouts with an automatic, instantaneous transfer to battery-derived AC output.

Highlights

- Delivers clean 120V AC power from AC or DC power source
- 2400W continuous output power; 4800W peak power
- Auto-transfer switching option for UPS operation
- Protects against blackouts, surges and EMI/RFI line noise
- Tested to UL (U.S.) and CSA (Canada) safety standards

Package Includes

- APS2448UL 2400W PowerVerter APS 48V DC 120V AC Inverter/Charger
- Owner's manual

Features

Reliable Power for Mobile, Emergency and Remote Sites

- Generates safe, stable, computer-grade 120V AC power from 48V battery bank
- Ideal for powering tools, saws, motors, pumps, portable lighting, appliances and computer equipment in heavy-load conditions
- Designed for easy installation in RVs, commercial and fleet vehicles, emergency vehicles and construction equipment
- Functions as extended-run UPS, standalone AC power source or vehicle inverter
- Unlimited runtime with variety of user-supplied batteries
- Tested to UL (U.S.) and CSA (Canada) safety standards

Meets Normal and Peak Power Demands

- 2400W of continuous power
- 3600W of reserve power up to 1 hr.
- 4800W of peak power up to 10 sec. to accommodate surge power demands during equipment startup and cycling
- Automatic overload detector, built-in cooling fan and resettable AC circuit breakers protect unit from damage
- High-current DC input terminals for simple hardwired installation

Automatic Transfer Switching

- Transfer relay switches to inverter power during blackout in 8 ms
- 3-position switch enables Auto, Charge Only or System Off mode
- DIP switches configure high and low voltage auto-transfer

3-Stage 15A Battery Charger

- Serves as battery charger when external 120V AC power is supplied and powering connected equipment
- Protects battery from overcharging and overdischarging
- Low-battery protection prevents excessive battery depletion
- DIP switches configure wet/gel charging profiles

Optional Remote Control Capability

- RJ45 communication port allows connection of optional remote control module, such as Tripp Lite's APSRM4

Front-Panel LEDs

- Indicate AC/DC operational modes, overload status, DC voltage level, shutdown status and system fault status

Rugged Polycarbonate Housing



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Battery Charge	15A
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LEDs	Set of 6 LEDs offer continuous status information on load percentage (6 levels reported) and battery charge level (7 levels reported). See manual for sequences.
Switches	3 position on/off/remote switch enables simple on/off power control plus "auto/remote" setting that enables distant on/off control of the inverter system when used in conjunction with optional APSRM4 ; accessory when used in inverter mode. In AC uninterruptible power mode, "auto/remote" setting enables automatic transfer from line power to battery power - to maintain continuous AC power to connected loads.
PHYSICAL	
Cooling Method	Multi-speed fan
Form Factors Supported	Mounting slots enable permanent placement of inverter on any horizontal surface (see manual for additional mounting information)
Material of Construction	Polycarbonate
Shipping Dimensions (hwd / cm)	32.77 x 53.59 x 36.83
Shipping Dimensions (hwd / in.)	12.90 x 21.10 x 14.50
Shipping Weight (kg)	20.23
Shipping Weight (lbs.)	44.60
Unit Dimensions (hwd / cm)	18.415 x 21.59 x 42.545
Unit Dimensions (hwd / in.)	7.25 x 8.5 x 16.75
Unit Weight (kg)	17.51
Unit Weight (lbs.)	38.6
ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
Operating Temperature	32-104 Fahrenheit / 0-40 Celcius
LINE / BATTERY TRANSFER	
Transfer Time (Line Power to Battery Mode)	8 milliseconds (typical - compatible with many computers, servers and networking equipment - verify transfer time compatibility of loads for UPS applications)
Low Voltage Transfer to Battery Power	In AC "auto" mode, inverter/charger switches to battery mode as line voltage drops to 75V (user adjustable to 85, 95, 105V - see manual)
High Voltage Transfer to Battery Power	In AC "auto" mode, inverter/charger switches to battery mode as line voltage increases to 135V (user adjustable to 145 - see manual)
SPECIAL FEATURES	
Load Sensing	Optional load sense function enables automatic inverter shutoff and startup as connected equipment is powered off and on. Front panel load sense potentiometer can be set to shutoff or turn on inverter power in response to loads of any level, up to 150 watts.
STANDARDS & COMPLIANCE	



Certifications	Tested to UL1778 (US), CSA CAN/CSA-C22.2 No.107.1-M91, NOM, RoHS
WARRANTY	
Product Warranty Period (U.S. & Canada)	1-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	2-year limited warranty
Product Warranty Period (Puerto Rico)	1-year limited warranty
Optional Coverage	1-Year, 2-Year, and 3-Year standard warranty extensions available. See Extended Warranties section for ordering part number

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>