

# >VPC2-O Series

Slot in PC module Quick Start Guide




Model No.	P/N	Model No.	P/N
VS18602	VPC27-W53-O1	VS18604	VPC25-W33-O1
VS18602	VPC27-W55-O2	VS18604	VPC25-W53-O1
VS18603	VPC2C-W33-O1	VS18605	VPC25-W53-O2

## Thank you for choosing ViewSonic®

As a world-leading provider of visual solutions, ViewSonic® is dedicated to exceeding the world's expectations for technological evolution, innovation, and simplicity. At ViewSonic®, we believe that our products have the potential to make a positive impact in the world, and we are confident that the ViewSonic® product you have chosen will serve you well.

Once again, thank you for choosing ViewSonic®!


# 1. Interface




Item	Description	
1	TYPE-C (DC5V, 500mA)	
2	RESET	
3	USB 2.0 x 2 (DC5V, 500mA)	
4	USB 3.2 (DC5V, 500mA)	
5	LAN	
6	HDMI	
7	DP	
8	LINE-OUT	
9	HDD/POWER_LED	
10	POWER BUTTON	


# 2. Installation

2-1




2-2





# 3. Internet Connection




# 4. Input Selection



## To select an Input Source:

- **1.** Press INPUT on the remote control, press the setting button (a) on the front panel, or press the (a) setting icon from the toolbar to display the Input Settings menu.
- 2. Press ▼ / ▲ / ◀ / ▶ to select PC.
- **3.** Press  $\binom{OK}{OK}$  on the remote control, or touch the input source.
- **4.** Press on the remote control, or touch a blank area outside of the menu to exit.

# 5. USB Connection



# 6. Specifications

Processor	Intel® Comet Lake-S				
PCH	H510	Q570			
Graphic	Integrated Intel® UHD graphic				
RAM	2 x DDR4 SO-DIMM, 32GB (Max)				
Storage	1 x NVMe M.2 2280 PCle SSD				
IO ports	1 x USB Type-C 1 x USB Type-C				
	(USB 3.2 Gen1, Data Only)	(USB 3.2 Gen2, Data Only)			
	2 x USB 2.0,	2 x USB 2.0,			
	1 x USB 3.2 Gen1	1 x USB 3.2 Gen2			
	1 x DP 1.4 out				
	1 x HDMI 2.0 out				
	1 x RJ45 Ethernet (with Intel® I219-LM)				
	1 x Audio jack				
	2 x External antenna Holes				
	1 x Power On/Off Button				
	1 x Reset Button				
	1 x Power LED				
	1 x HDD LED				
	1 x 80 Pin JAE OPS connector				
WIFI/BT	1 x M.2 2230 (with Intel® AX201 WiFi 6 + BT 5.2 module)				
Watchdog	Support				
vPro/AMT	No	Yes			
BIOS	AMI UEFI BIOS				
Power	DC in +19V @ 4.74A				
	60 W (Typical)				
Operating	-5 °C to +45 °C				
Conditions	20% RH ~ 80% RH non-condensing				
Storage	-20 °C to +80 °C				
Conditions	10% ~ 80% R.H. non-condensing				

# > Regulatory and Service Information

## **Compliance Information**

This section addresses all connected requirements and statements regarding regulations. Confirmed corresponding applications shall refer to nameplate labels and relevant markings on the unit.

## **FCC Compliance Statement**

This device complies with part 15 of FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

This equipment has been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses, and can radiate radio frequency energy, and if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

**Warning:** You are cautioned that changes or modifications not expressly approved by the party responsible for compliance could void your authority to operate the equipment.

## **Industry Canada Statement**

CAN ICES-003 (B)/NMB-003(B)

Contains FCC ID: PD9AX201NG

IC ID: 1000M-AX201NG

### **CE Conformity for European Countries**



The device complies with the EMC Directive 2014/30/EU and Low Voltage Directive 2014/35/EU and Radio Equipment Directive (RED) 2014/53/EU.

#### The following information is only for EU-member states:

The mark shown to the right is in compliance with the Waste Electrical and Electronic Equipment Directive 2012/19/EU (WEEE). The mark indicates the requirement NOT to dispose the equipment as unsorted municipal waste, but use the return and collection systems according to local law. In all EU member states, operation of 5150-5350MHz is restricted to indoor use only. This device should be installed and operated with a minimum distance of 20cm between the radiator and your body.



### **Declaration of RoHS2 Compliance**

This product has been designed and manufactured in compliance with Directive 2011/65/EU of the European Parliament and the Council on restriction of the use of certain hazardous substances in electrical and electronic equipment (RoHS2 Directive) and is deemed to comply with the maximum concentration values issued by the European Technical Adaptation Committee (TAC) as shown below:

Substance	Proposed Maximum Concentration	<b>Actual Concentration</b>
Lead (Pb)	0.1%	< 0.1%
Mercury (Hg)	0.1%	< 0.1%
Cadmium (Cd)	0.01%	< 0.01%
Hexavalent Chromium (Cr6+)	0.1%	< 0.1%
Polybrominated biphenyls (PBB)	0.1%	< 0.1%
Polybrominated diphenyl ethers (PBDE)	0.1%	< 0.1%
Bis (2-ethylhexyl) phthalate (DEHP)	0.1%	< 0.1%
Butyl benzyl phthalate (BBP)	0.1%	< 0.1%
Dibutyl phthalate (DBP)	0.1%	< 0.1%
Diisobutyl phthalate (DIBP)	0.1%	< 0.1%

# Certain components of products as stated above are exempted under the Annex III of the RoHS2 Directives as noted below:

- Copper alloy containing up to 4% lead by weight.
- Lead in high melting temperature type solders (i.e. lead-based alloys containing 85% by weight or more lead).
- Electrical and electronic components containing lead in a glass or ceramic other than dielectric ceramic in capacitors, e.g. piezoelectronic devices, or in a glass or ceramic matrix compound.
- Lead in dielectric ceramic in capacitors for a rated voltage of 125V AC or 250V DC or higher.

#### **Indian Restriction of Hazardous Substances**

Restriction on Hazardous Substances statement (India). This product complies with the "India E-waste Rule 2011" and prohibits use of lead, mercury, hexavalent chromium, polybrominated biphenyls or polybrominated diphenyl ethers in concentrations exceeding 0.1 weight % and 0.01 weight % for cadmium, except for the exemptions set in Schedule 2 of the Rule.

#### **Product Disposal at End of Product Life**

ViewSonic® respects the environment and is committed to working and living green. Thank you for being part of Smarter, Greener Computing. Please visit the ViewSonic® website to learn more.

#### **USA & Canada:**

http://www.viewsonic.com/company/green/recycle-program/

#### **Europe:**

http://www.viewsoniceurope.com/eu/support/call-desk/

#### Taiwan:

https://recycle.epa.gov.tw/

## **Customer Service**

For technical support or product service, see the table below or contact your reseller.

**NOTE:** You will need the product's serial number.

Country/ Region	Website	Country/ Region	Website		
Asia Pacific & Africa					
Australia	www.viewsonic.com/au/	Bangladesh	www.viewsonic.com/bd/		
中国 (China)	www.viewsonic.com.cn	香港 (繁體中文)	www.viewsonic.com/hk/		
Hong Kong (English)	www.viewsonic.com/hk-en/	India	www.viewsonic.com/in/		
Indonesia	www.viewsonic.com/id/	Israel	www.viewsonic.com/il/		
日本 (Japan)	www.viewsonic.com/jp/	Korea	www.viewsonic.com/kr/		
Malaysia	www.viewsonic.com/my/	Middle East	www.viewsonic.com/me/		
Myanmar	www.viewsonic.com/mm/	Nepal	www.viewsonic.com/np/		
New Zealand	www.viewsonic.com/nz/	Pakistan	www.viewsonic.com/pk/		
Philippines	www.viewsonic.com/ph/	Singapore	www.viewsonic.com/sg/		
臺灣 (Taiwan)	www.viewsonic.com/tw/	ประเทศไทย	www.viewsonic.com/th/		
Việt Nam	www.viewsonic.com/vn/	South Africa & Mauritius	www.viewsonic.com/za/		
	Amer	icas			
United States	www.viewsonic.com/us	Canada	www.viewsonic.com/us		
Latin America	www.viewsonic.com/la	,			
Europe					
Europe	www.viewsonic.com/eu/	France	www.viewsonic.com/fr/		
Deutschland	www.viewsonic.com/de/	Қазақстан	www.viewsonic.com/kz/		
Россия	www.viewsonic.com/ru/	España	www.viewsonic.com/es/		
Türkiye	www.viewsonic.com/tr/	Україна	www.viewsonic.com/ua/		
United Kingdom	www.viewsonic.com/uk/				

