



HELIOS™ 60

Comb Binding Machines

Offer Valid:
January 1 – March 31, 2017

This offer applies only to purchases from resellers within Canada.



LED Control Panel

Ensures this advanced binder is user-friendly.



Heat Shield Safety Barrier

Prevents accidental contact with the heating plate.



Auto Document Thickness Detector

Determines and selects binding settings.

\$40 REBATE



Specifications

Model	HELIOS™ 60
Item Number	5219501
Rebate	\$40
Application	Large Office
Binding Capacity	600 Sheets
Binding Type	Thermal
Binding Element Selector	Yes
Dimensions (H x W x D)	22-3/8 x 5-1/2 x 12-13/16"
Warranty	2 Years

ENGINEERED TO PERFORM -
FIRST TIME, EVERY TIME

©2016 Fellowes, Inc.

www.fellowes.com/ca

100
YEARS

Innovation in Motion™
Since 1917

To receive your mail-in Rebate offer: Mail the original invoice or packing slip with the completed form below.

Company*: _____

Phone*: _____ Email: _____

Name & Title*: _____

Place of Purchase*: _____

Address*: _____

City*: _____ Prov: _____ Postal Code: _____

Submit this form along with your original invoice or packing slip dated between 01/01/17 and 03/31/17. Submissions must be received no later than 04/30/2017. Submissions mailed to any address other than the address indicated on this form will not be acknowledged. Keep copies of all submitted material for your records and inquiries. Fellowes will not be responsible for claims that are lost, stolen, delayed or not received. Illegible or incomplete requests will not be honored. This offer is limited to one rebate per name, company and address. This offer is not valid with any other Fellowes promotional/discount/special offers. Fellowes has the right to limit the number of redemptions by company. Allow 6-8 weeks to receive your rebate. Offer void where prohibited by law. Offer limited to residents of Canada.

Mail to:

Binder Rebates
Promo 41770
P.O. Box 250-F182
Pickering, ON
L1V 2R4

*REQUIRED INFORMATION