

17" Rack LCD Console with Integrated 8 Port Analog KVM Switch

The Rack LCD Console with Integrated KVM Switch combines the functionality of Rack LCD Console and Analog KVM switches in one convenient package optimizing U space in the rack environment, eliminating cable clutter, and offering a value of two

AP5808

Overview

Presentation

	products functionality in one package. Keyboard is a US English keyboard layout.
Lead time	Usually in Stock
Main	
Main Input Voltage	120 V 240 V
Input Connection Type	IEC 60320 C14
Number of rack unit	1U
Cable length	6 ft (1.8 m)
Number of cables	1

USB KVM cable
Single user rack mount kit
PS2 KVM cable
NEMA 5-15 power cord
Installation guide
Firmware upgrade cable
Documentation CD
C13-C14 power cord

Physical

Provided equipment

Color	Black
Height	1.69 in (4.3 cm)
Width	19.02 in (48.3 cm)
Depth	27.99 in (71.1 cm)
Net Weight	30.36 lb(US) (13.77 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Rack-mounted
Maximum Mounting Depth	41.33 in (104.98 cm)
minimum mounting depth	26.77 in (68 cm)

Input

Input Frequency 50/60 Hz

Conformance

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	cUL Listed C-tick CE Industry Canada KCC UL Listed VDE TAA compliance
Standards	EN 60950 FCC Part 15 class A IEC 60950

Environmental

Ambient air temperature for operation

32...104 °F (0...40 °C)

Supported Hardware

Display colour	16 colours	
Display size	337.9 (H) x 270.3 (V) 17 inch	
Trackball Type	PS/2 Touchpad USB mouse	
Display Type	LCD display	

Ordering and shipping details

GTIN 731304278801

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.12 in (13 cm)
Package 1 Width	32.68 in (83 cm)
Package 1 Length	26.18 in (66.5 cm)
Package 1 Weight	43.78 lb(US) (19.86 kg)

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint		
Carbon footprint (kg CO2 eq, Total Life cycle)	60	

Use Better

Materials and Substances	
EU RoHS Directive	Compliant with Exemptions
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Yes