

APC Smart-UPS X, Line Interactive, 2200VA, Rack/tower convertible 2U, 208V-230V, 8x C13+1x C19 IEC, SmartSlot, Extended runtime

SMX2200RMHV2U

#### Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.	
Lead time	Usually in Stock	
Main		
Main Input Voltage	208 V 230 V	
Other Input Voltage	220 V 240 V	
Main Output Voltage	208 V 230 V	
Other Output Voltage	220 V 240 V	
Kw Rating	1980 W	
Rated power in VA	2200 VA	
Product or Component Type	Uninterruptible power supply (UPS)	
Input Connection Type	IEC 320 C20 Schuko CEE 7 / EU1-16P BS1363A British	
output connection type	8 IEC 320 C13 2 IEC Jumpers 1 IEC 320 C19	
Number of rack unit	2U	
Cable length	6 ft (1.8 m)	
Number of cables	1	
Battery Type	Lead-Acid battery	
Provided equipment	CD with software Documentation CD Smart UPS signalling RS-232 cable User Manual USB cable Rack Mounting brackets	
Range of Product	Smart-UPS	

### Complementary

Communication port type SmartSlot

#### **Batteries & Runtime**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Run Time	View Runtime Graph ☐
Efficiency	View Efficiency Graph ☐
Extendable Run Time	1
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery life	35 year(s)
Replacement battery	APCRBC117 ☐
Battery Charge Power (Watts)	233 W rated

### General

Number of power module	0
Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	Extended run
Redundant	No

# **Physical**

color	Black
Height	3.35 in (8.5 cm)
Width	17.01 in (43.2 cm)
Depth	26.26 in (66.7 cm)
Net Weight	82.28 lb(US) (37.32 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes

## Input

Efficiency at full load	140280 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

## Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	2200 VA
Max Configurable Power (Watts)	1980 W
Transfer Time	2-4 ms 6ms typical : 10ms maximum
Topology	Line Interactive

Wave type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

### Conformance

Dunadurat Cantifications	0.5
Product Certifications	CE
	EAC
	IRAM
	RCM
	TISI
	VDE
	UK PSTI
Standards	EN/IEC 62040-1:2019/A11:2021
	EN/IEC 62040-2:2006/AC:2006
	EN/IEC 62040-2:2018

### **Environmental**

Acoustic level	55 dBA	
Online Thermal Dissipation	150 Btu/h	
Operating altitude	010000 ft	
Ambient air temperature for operation	32104 °F (040 °C)	
Ambient Air Temperature for Storage	5113 °F (-1545 °C)	
Storage altitude	050000 ft (0.000000000015240.0000000000 m)	
Relative Humidity	095 %	
Storage Relative Humidity	095 %	

# Communications & Management

control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : and Overload Indicators Multi-function LCD status and control console	
Emergency Power Off (EPO)	Yes	
Free slots	1	
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays	

## **Surge Protection and Filtering**

Surge energy rating	645 J	
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m	

## Ordering and shipping details

GTIN	731304272687	

## **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.84 in (25.000 cm)
Package 1 Width	23.62 in (60.000 cm)
Package 1 Length	34.25 in (87.000 cm)
Package 1 Weight	104.367 lb(US) (47.340 kg)

Unit Type of Package 2	P12
Number of Units in Package 2	2
Package 2 Height	29.53 in (75.000 cm)
Package 2 Width	31.50 in (80.000 cm)
Package 2 Length	47.24 in (120.000 cm)
Package 2 Weight	235.189 lb(US) (106.680 kg)
Pallet unit layers	2
Pallet layers	4

## **Contractual warranty**

Warranty

 $3\ \text{years}$  repair or replace (excluding battery) and  $2\ \text{years}$  for battery, optional on-site warranties available, optional extended warranties available



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

#### Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	2716
Environmental Disclosure	Product Environmental Profile

#### **Use Better**

EU RoHS Directive	Compliant with Exemptions
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
<sup>™</sup> Energy efficiency	
Optimized Energy Efficiency	Energy efficient product

#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	User replaceable
Take-back	Yes