

APC Netshelter Rack Automatic Transfer Switch, 1U, 20 A, 208V, 2 C20 IN, 8 C13, 1 C19 OUT, 50/60Hz

AP4434A

Overview

Lead time Usually in Stock

Main

Main Input Voltage	208 V AC 1 phase	
Product or Component Type	Automatic transfer switch	
Main Output Voltage	208 V AC 1 phase 208 V	
Input Connection Type	IEC 60320 C20 16 A 2P+E	
Number of rack unit	1U	
Cable length	8 ft (2.4 m)	
Provided Equipment	Mounting Hardware Rack Mounting brackets	

Physical

Color	Black	
Height	1.73 in (4.4 cm)	
Width	17.01 in (43.2 cm)	
Depth	9.29 in (23.6 cm)	
Net Weight	8.25 lb(US) (3.74 kg)	
Mounting Location	Front Rear	
Mounting preference	No preference	
Mounting Mode	Rack-mounted	
Mounting position	Horizontal	

Input

Input Frequency	50/60 Hz
Line Rated Current	20 A
Permissible voltage	187228 V
Max line current	20 A
Input current limits	20 A
Load Capacity	3300 VA

Output

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Max current draw	20 A	
Number of power socket outlets	8 IEC 60320 C13 12 A 2P+E 1 IEC 60320 C19 16 A 2P+E	
Protection Type	Without circuit breaker	
Cord Length	8.005 ft (2.44 m)	

Conformance

Product Certifications	cUL Listed CE UL Listed
Standards	EN 55022 Class A FCC Part 15 class A

Environmental

Ambient air temperature for operation	23113 °F (-545 °C)	
Relative Humidity	595 %	
Operating altitude	010000 ft	
Ambient Air Temperature for Storage	-13149 °F (-2565 °C)	
Storage Relative Humidity	595 %	
Storage altitude	0.000000000050000.000000000 ft (015240 m)	

Ordering and shipping details

GTIN 731304432500

Packing Units

Unit Type of Package 1	PCE	
Number of Units in Package 1	1	
Package 1 Height	4.49 in (11.4 cm)	
Package 1 Width	23.62 in (60 cm)	
Package 1 Length	14.02 in (35.6 cm)	
Package 1 Weight	12.15 lb(US) (5.51 kg)	

Contractual warranty

Warranty 2 years repair or replace



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

⊘ Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	433
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
EU RoHS Directive	Compliant
REACh Regulation	REACh Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Use Again

○ Repack and remanufacture	
Circularity Profile	End of Life Information
Removable battery	Yes
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Yes