

AM1333D3DRLPR/4G
4GB DDR3-1333MHz 1.35V 240-PIN CL9 RDIMM


Product Description

This Industry Standard 4GB DDR3-1333MHz dual rank registered ECC 1.35V 240-pin CL9 factory original RDIMM is 100% guaranteed to be compatible with your system and to work right the first time. All of our server memory is built to strict JEDEC standards at one of the tier 1 facilities (Samsung, Micron, or Hynix). Our products are also guaranteed by federal law to not affect or void OEM warranties.

Specifications

Parameter	
Form Factor	RDIMM
Memory Size	4Gb
Rank	Dual
Row Cycle Time (tRCmin)	48.125ns (Min)
Refresh to Active/ (tRFmin)	260ns (min.)
CL (IDD)	9 cycles
Row Active Time (tRASmin)	35ns (min.)
UL Rating	94 V - 0
DIMM Type	Registered
Memory Voltage	1.35V
Operating Temperature	0° C to 85° C
Storage Temperature	-55° C to +100° C

Mechanical Description



Contact Information

Founded in 1999, AddOn Networks is North America's leading provider of transceivers and high-speed cabling. With a reputation for high quality products as well as an extensive custom design portfolio, AddOn has the connectivity solution regardless of the requirement.

At AddOn, 100% of the products we ship every day are tested in the specific application for which they are intended—never batch or spec tested only. We run bandwidth, distance and IOS network tests. We have documented an impressive 0.03% failure rate over the last 10 years. To continue this rate of success we invest millions annually in our own on-site testing lab.

Corporate office:
AddOn Networks
15775 Gateway Circle
Tustin, CA 92780

Tel: 877-292-1701
Fax: 949-266-9273
Email: sales@addonnetworks.com
Email: support@addonnetworks.com
Web: <http://www.addonnetworks.com>