






REVISIONS		
Rev	DESCRIPTION	DATE
A	INITIAL RELEASE	2017.06.30



MATERIAL

Overall Shield: Copper C2680, $t=0.009$ in (0.25 mm), plated with 30 μ in (0.67 μ m) nickel

Housing: High-impact Polycarbonate (PC resin), UL 94 V-2 rated, clear transparent

Blades: Phosphor bronze, plated with 50 μ in (1.27 μ m) thick hard gold over 100 μ in (2.54 μ m) thick nickel underplate on contact area

RoHS 2 compliant

WIRE RANGE

Conductor Diameters: 0.016 in (0.41 mm) 26 AWG - 0.020 in (0.51 mm) 24 AWG

Insulation Diameters: 0.038 in (0.96mm) - 0.040 in (1.02mm)

Cable Diameters: 0.197 in (5 mm) - 0.276 in (7 mm)

SPECIFICATION

Meet IEC 60603-7 Standard

Meet TIA-1096-A Standard

DIMENSIONS ARE IN[MM]				
TOLERANCES:				
-0.787[20]	-1.969[50]	-5.906[150]	5.906[150]	ANGLE
$\pm 0.008[0.2]$	$\pm 0.016[0.4]$	$\pm 0.020[0.5]$	$\pm 0.059[1.5]$	$\pm 2^\circ$
3rd Angle Projection				

The information contained in this document is the sole property of Black Box Corporation of Pennsylvania. Any reproduction in part or whole without the written permission of Black Box Corp. is prohibited.

©Copyright 2012 Black Box Corporation of Pennsylvania d/b/a Black Box Network Services. All Rights Reserved.

UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES
TOLERANCES:
FRACTIONAL $\pm$
ANGULAR: MACH $\pm$ BEND $\pm$
TWO PLACE DECIMAL $\pm$
THREE PLACE DECIMAL $\pm$

INTERPRET GEOMETRIC TOLERANCING PER:
MATERIAL PC
FINISH
DO NOT SCALE DRAWING



NAME			DATE			TITLE		
DRAWN	Kihai Lee		2017.06.30			Category 5e Modular Plugs Shielded - xxx Pack		
ENG APPR.	Kevin Wu		2017.06.30					
CHECKED	Jerry Su		2017.06.30			SIZE	DWG. NO.	REV
COMMENTS:						B	FMT5ES-XXPAK	A
CASE 17						SCALE: 1:1		SHEET 1 OF 1