

6in High Speed HDMI Port Saver Cable M/F - Ultra HD 4k x 2k HDMI Cable

Product ID: HDMIEXTAA6IN



The HDMIEXTAA6IN HDMI Port Saver Cable is a 6-inch HDMI cable designed to prevent wear and tear on the HDMI port on your computer or A/V device (Blu-Ray player, A/V receiver etc.). The port saver cable features 1 HDMI (male) connector and 1 HDMI (female) connector, which extends the HDMI (female) port from a video card or A/V device away from the device itself, relieving the stress of repeated HDMI plug insertions and removals and transferring the weight of typical HDMI cable connection away from the device port.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

The HDMIEXTAA6IN 6in HDMI cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility

Applications

- Protect the video card or monitor's HDMI port against wear from frequent connect/disconnects
- Allows supported HDMI-capable devices to draw power from the host device

Features

- Supports Ultra HD Resolutions up to 4k x 2k
- Gold-plated HDMI connectors
- High quality construction

Hardware

Warranty	Lifetime
Number of Conductors	19

Performance

Maximum Digital Resolutions	4K x 2K @ 30 Hz
-----------------------------	-----------------

Connector(s)

Connector A	HDMI (19 pin)
Connector B	HDMI (19 pin)

Physical Characteristics

Color	Black
Cable Length	6.0 in [15.2 cm]
Product Length	6.0 in [15.2 cm]
Weight of Product	1.3 oz [37 g]

Packaging Information

Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.6 in [15 mm]
Shipping (Package) Weight	1.5 oz [42 g]

What's in the Box

Included in Package	6in High Speed HDMI Port Saver Cable - M/F
---------------------	--

****Product appearance and specifications are subject to change without notice.***

