

3.7kW Single-Phase 208/230V Monitored PDU - LX Platform, 8 C13 Outlets, C20 Input with L6-20P Adapter, 2.4m Cord, 1U Rack-Mount

MODEL NUMBER: PDUMNH20HV



Features

- 16/20A 230/208V Monitored Power Distribution Unit / PDU (agency derated to 16A continuous)
- C20 inlet; 8ft / 2.4m C20 cable and NEMA L6-20P plug adapter included
- 1U horizontal rackmount installation
- 8 C13 outlets
- Lighted display reports output power consumption in amps
- Built-in network interface reports voltage, frequency and PDU loading via network or secure web browser interface with options for user specified alarm and notification thresholds
- Pre-installed WEBCARDLX with the latest version of PowerAlert Device Manager firmware (PADM20) provides enhanced remote management capabilities
- PADM20 and PowerAlert Element Manager (PAEM) form a powerful tool for expanding maintenance functions in large installations, including firmware update checks and backup and restoration of device configurations
- Optional EnviroSense2 modules (sold separately) provide a variety of environmental monitoring capabilities
- 10/100 Mbps auto-sensing allows optimal communication with 10/100 Base-T networks
- Real-time clock backup maintains the time of day and date even if the PDU is unpowered
- Tiered access privileges allow an administrator and a guest to login via web browser for monitoring
- Alert notifications via email or SNMP traps offer immediate event notification
- Firmware upgrade ability supports future product enhancements.
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Mounting ears are reversible for front or rear facing rackmount installation
- Included cord retention brackets keep vital network equipment plugged in and continuously powered
- TAA Compliant for GSA Schedule purchases

Highlights

- Monitored 16A 208/230V PDU, 1U horizontal rackmount
- Reports voltage, frequency & load level via ethernet interface
- Visual current meter, Reversible housing
- C20 inlet; 8ft / 2.4m C20 cable with L6-20P plug adapter
- 8 C13 outlets with included plug-lock retention sleeves
- Pre-installed WEBCARDLX with latest version of PADM20 for enhanced remote management
- TAA Compliant for GSA Schedule purchases

Package Includes

- Rackmount PDU
- Rack mounting brackets
- Plug retention inserts
- 2.6m C19-to-C20 power cord
- C19-to-L6-20P plug adapter
- Mounting hardware
- Owner's manual



Specifications

OVERVIEW	
UPC Code	037332160928
PDU Type	Monitored
INPUT	
PDU Input Voltage	208/230V
Recommended Electrical Service	Single-phase 16/20A 230/208V service
Maximum Input Amps	16
PDU Plug Type	NEMA L6-20P; IEC-320 C20
Input Phase	Single-Phase
Input Cord Length (ft.)	8.5
Input Cord Length (m)	2.59
OUTPUT	
Output Capacity Details	3.68kW (230V), 3.33kW (208V) / 16A total capacity; 12A (10A CE) max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) C13
Output Nominal Voltage	208/230V
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital meter reports PDU output current in amps
PHYSICAL	
Material of Construction	Metal
Form Factors Supported	1U horizontal rackmount in 2 or 4 post racks
Minimum Required Rack Depth (cm)	43.43
Minimum Required Rack Depth (inches)	17.1
PDU Form Factor	Horizontal (1U)
Shipping Dimensions (hwd / cm)	15.24 x 52.70 x 58.42
Shipping Dimensions (hwd / in.)	6.00 x 20.75 x 23.00
Shipping Weight (kg)	6.12
Shipping Weight (lbs.)	13.50
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 14.8
Unit Dimensions (hwd / cm)	4,4 x 44,4 x 37,6



Unit Weight (lbs.)	9.00
Unit Weight (kg)	4.08
ENVIRONMENTAL	
Operating Temperature Range	0C ~ 40C (32F ~ 104F)
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5 to 95% non-condensing
COMMUNICATIONS	
SNMP Compatibility	Pre-installed LX platform interface provides remote monitoring via Java-free HTML5 web interface, telnet, SSH and SNMP management systems
STANDARDS & COMPLIANCE	
Certifications	Tested to UL 60950-1 (USA, Canada), CE (EEA), Class A (Emissions), NOM (Mexico), RoHS compliant, TAA Compliant
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>