

Product data sheet

Specifications



Power Cord Splitter, L21-20P to (3)L5-20R



AP9883

Product availability: Stock - Normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

Product or Component Type	Power cord
Input Connection Type	NEMA L21-20P
number of rack unit	0U
Number of cables	1

Physical

Color	Black
Net Weight	2.25 lb(US) (1.02 kg)
mounting location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	50/60 Hz
Max line current	20 A
Input current limits	20 A

Output

Maximum Total Current Draw per Phase	16 A
Number of power socket outlets	3 NEMA L5-20R
Cord Length	2 ft (0.6 m) 4 ft (1.2 m) 6 ft (1.8 m)

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	32...113 °F (0...45 °C)
Storage Relative Humidity	0...95 %

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
-------------------------	--

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
-----------------	---------------------------

Discount Schedule	APC1
--------------------------	------

GTIN	731304198796
-------------	--------------

Returnability	No
----------------------	----

Country of origin	US
--------------------------	----

Packing Units

Unit Type of Package 1	PCE
-------------------------------	-----

Number of Units in Package 1	1
-------------------------------------	---

Package 1 Height	3.0 in (7.6 cm)
-------------------------	-----------------

Package 1 Width	12.5 in (31.8 cm)
------------------------	-------------------

Package 1 Length	12.5 in (31.8 cm)
-------------------------	-------------------

Package 1 Weight	3.00 lb(US) (1.36 kg)
-------------------------	-----------------------

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Take-back Transparency RoHS/REACH

Resource performance

 Take-Back Program Available

Well-being performance

 Lead Free

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov