

## 1m External Serial Attached SCSI SAS Cable - SFF-8470 to SFF-8088

**Product ID:** ISAS88701



The ISAS88701 1-meter Serial Attached SCSI Cable is designed for high-performance networks, servers, workstations and desktops, featuring one SFF-8470 (Infiniband) connector and one SFF-8088 (external mini-SAS) connector with support for data transfer rates up to 6 Gbps.

This SFF-8470 to SFF-8088 SAS cable is constructed of high quality materials and is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility

### Applications

- Connect SAS Controllers to SAS Backplanes
- For use in Storage Area Networks, to connect SAS Expander enabled controllers and enclosures

### Features

- Durable metal connectors
- Infiniband plug with thumbscrews for secure connections
- Supports data transfer rates up to 6 Gbps
- Compatible with many servers, including:
  - IBM MegaRAID 8480
  - IBM System Storage EXP3000
  - IBM x3850 (8864)
  - IBM x3800 (8866)
  - IBM x3655 (7985)
  - IBM x3455 (7984,7986)
  - IBM x3250 (4364,4365)

---

## Hardware

Warranty	Lifetime
Number of Conductors	8 Twisted Pair
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-polyester foil with tinned copper braid

---

## Connector(s)

Connector A	SFF-8470 (32 pin, Infiniband, External SAS)
Connector B	SFF-8088 (26-pin, External Mini-SAS)

---

## Physical Characteristics

Color	Black
Wire Gauge	26 AWG (0.404 mm)
Cable Length	39.4 in [100 cm]
Diameter	8.763mm
Product Length	39.4 in [100.0 cm]
Product Width	0.0 in [0.0 mm]
Product Height	0.0 in [0.0 mm]
Weight of Product	6.7 oz [190.0 g]

---

## Packaging Information

Package Quantity	1
Package Length	13.0 in [33.0 cm]
Package Width	10.0 in [25.5 cm]
Package Height	0.6 in [14.0 mm]
Shipping (Package) Weight	6.8 oz [193.0 g]

---

## What's in the Box

Included in Package	1m External Serial Attached SCSI SAS Cable - SFF-8470 to SFF-8088
---------------------	---

---

***\*Product appearance and specifications are subject to change without notice.***

