

Product data sheet

Specifications



Power Cord, C13 to C14, 2.5m

AP9870



Overview

Lead time Usually in Stock

Main

Product or Component Type Power cord
Input Connection Type IEC 60320 C14
Cable length 8.2 ft (2.5 m)
Number of cables 1

Physical

Color Black
Height 1.5 in (3.8 cm)
Width 3.0 in (7.6 cm)
Depth 8.0 in (20.3 cm)
Net Weight 0.51 lb(US) (0.23 kg)
Mounting preference No preference
Mounting Mode Not rack-mountable

Input

Input Frequency 50/60 Hz
Acceptable Input Voltage 90...250 V
Max line current 10 A
Input current limits 10 A

Output

Maximum Total Current Draw per Phase 10 A
Number of power socket outlets 1 IEC 60320 C13
Protection Type Without circuit breaker

Conformance

Product Certifications CSA
UL Listed
VDE

Environmental

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	731304107897
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.008 in (5.1 cm)
Package 1 Width	4.02 in (10.2 cm)
Package 1 Length	8.0 in (20.3 cm)
Package 1 Weight	0.7 lb(US) (0.3 kg)
Unit Type of Package 2	CAR
Number of Units in Package 2	25
Package 2 Height	9.8 in (25 cm)
Package 2 Width	13.8 in (35 cm)
Package 2 Length	22.05 in (56 cm)
Package 2 Weight	20.06 lb(US) (9.1 kg)
Unit Type of Package 3	PAL
Number of Units in Package 3	25
Package 3 Height	56.69 in (143.99 cm)
Package 3 Width	39.4 in (100 cm)
Package 3 Length	47.2 in (120 cm)
Package 3 Weight	20.06 lb(US) (9.1 kg)

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Lead Free

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov