

Product data sheet

Specifications



Power Cord, C19 to 5-20P, 2.5m

AP9873



Product availability: Stock - Normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

Product or Component Type	Power cord
Input Connection Type	NEMA 5-20P
Cable length	8.2 ft (2.5 m)
Number of cables	1

Physical

Color	Black
Height	2.008 in (5.1 cm)
Width	9.02 in (22.9 cm)
Depth	4.02 in (10.2 cm)
Net Weight	0.49 lb(US) (0.22 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input Frequency	50/60 Hz
Acceptable Input Voltage	100...120 V
Max line current	20 A
Input current limits	20 A
Load Capacity	2400 VA

Output

Maximum Total Current Draw per Phase	20 A
Number of power socket outlets	1 IEC 60320 C19
Protection Type	Without circuit breaker

Conformance

Product Certifications	CSA UL Listed
------------------------	------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Environmental

Ambient Air Temperature for Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304189367
Returnability	No
Country of origin	US

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.02 in (10.2 cm)
Package 1 Width	4.3 in (10.8 cm)
Package 1 Length	12.5 in (31.8 cm)
Package 1 Weight	0.7 lb(US) (0.3 kg)

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Take-back Transparency RoHS/REACH

Resource performance

 Take-Back Program Available

Well-being performance

 Lead Free

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov