

450D & NC450D

Handheld Communications Dynamic Microphone

Key Features:

- Omnidirectional or Noise-Cancelling
- Rugged Construction
- Low Impedance
- PTT Switch

General Description:

The Telex Models 450D and NC450D Dynamic Microphones are designed for voice-paging applications requiring a rugged hand-held microphone.

The 450D is a low-impedance, balanced-line dynamic microphone that provides smooth, peak-free response and trouble-free performance. The rugged design makes it particularly effective for use in busy environments (e.g. manufacturing and restaurants) where excellent voice response characteristics in a microphone are required.

The NC450D is a noise-cancelling design that makes it particularly effective for use in noisy locations, and the excellent voice response characteristics make it a good choice in quiet areas as well.

Design Features:

The NC450D microphone contains a shock-mounted dynamic, differential type cartridge which discriminates and cancels distant sounds and noise in favor of voice inputs spoken close to the microphone. The 450D features a standard omnidirectional shock-mounted dynamic cartridge. Output impedance on both models is 200 ohms for matching low impedance input circuits. A push-to-talk switch is located on the microphone housing. The black microphone housings are constructed of molded ABS plastic, which will withstand the day-to-day abuse of hand-held mobile microphone applications. The NC450D includes a soft rubber lip guard which assures the user of correct microphone-to-mouth positioning.

Note:

Always talk close to the microphone, with the edge of the lip guard just touching the upper lip. This is important because the noise-canceling feature accepts close sounds best and discriminates against sounds greater than 1/2-inch (12mm) away.




Technical Specifications:

	NC450D	450D
Type:	Noise-Canceling Dynamic	Dynamic Omnidirectional
Frequency Response:	100 to 8,000 Hz	
Output Level at 1 kHz, Open Circuit:	-85 dB (ref: 0 dB = 1V/ μ bar)	-79 dB (ref: 0 dB = 1V/ μ bar)
Output Level at 1 kHz, Power Level:	-64 dB (ref: 0 dB = 1mW/10 μ bar)	-58 dB (ref: 0 dB = 1mW/10 μ bar)
EIA Sensitivity:	-151 dB	
Impedance:	200 Ohms	
Switch:	Two-Position Momentary Slide Normally Open Microphone Contacts	
Cable:	Unterminated, 4-Conductor, 2 Shielded, Black Neoprene, Coiled Cord, 12" (304mm) Retracted/6' (1.8m) Extended	
Finish:	Black, Pebble-Grain	
Hanger Bracket:	Nickel-Plated Spring Steel	
Weight:	225 g (9 oz.)	


The coil units are equipped with an unterminated black neoprene coil cord which is relieved at the housing by a spring-type strain relief. In addition, the microphones are equipped with a hanger button, and supplied with standard dashboard mounting bracket and hardware.

TELEX

Dimensions:




Model 450D Outline




Model NC450D Outline

Wiring Diagrams:



Model 450D Wiring Diagram



Model NC450D Wiring Diagram

Ordering Information:

Model 450D	Catalog No. 47000
Model NC450D	Catalog No. 47005
Replacement Hanger with Hardware	Catalog No. 02506
Replacement Element	Catalog No. 02189

TELEX

12000 Portland Avenue South, Burnsville, MN 55337
Phone: 952/884-4051, Fax: 952/884-0043

www.telex.com

© Telex Communications, Inc. 12/2006
Part Number 38109-638 Rev. C

U.S.A. and Canada only. For customer orders, contact Customer Service at:
800/392-3497 Fax: 800/955-6831

Europe, Africa, and Middle East only. For customer orders, contact Customer Service at:
+ 49 9421-706 0 Fax: + 49 9421-706 265

Other International locations. For customer orders, contact Customer Service at:
+ 1 952 884-4051 Fax: + 1 952 736-4212

For warranty repair or service information, contact the Service Repair department at:
800/553-5992 or 402/467-5321

For technical assistance, contact Technical Support at: **800/392-3497 or 952/736-4656**

Specifications subject to change without notice.