



C2G

25ft (7.6m) RapidRun® Multi-Format Runner Cable - In-Wall CMG-Rated

Part No. CG-60003

RapidRun® is designed to be the standard for in-wall audio/video installations. Using pre-terminated Break-away flying leads and wall plates with an in-wall runner ensures flexible, efficient, high quality connections for all types of equipment, with no field terminations.



Ideal for educational and institutional installations, this wall plate receives PC video, 3.5mm stereo audio, USB and RCA composite audio/video from one Runner cable. Constructed from aluminum for durability, this wall plate has a locking connector that enables the integrator to save valuable space inside the surface mount or electrical box that typically is already packed with cables. The included keystone bezels will work with most brands of keystone inserts including Leviton®, L-com®, NetKey®, ADC Krone, HellermannTyton, and Allen Tel.

Please note: Each complete RapidRun Multi-Format solution requires a break-away flying lead or wall plate to terminate each end of the runner cable. Each runner requires (2) break-away flying leads, (2) wall plates, OR (1) break-away flying lead and (1) wall plate.

Features & Benefits

In-wall, CMG-rated jacket

Supports VGA video and other audio/video signals

Designed for use with RapidRun Multi-Format flying leads and wall plates

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120600039	Country Of Origin	China
Application Sector	Residential, Commercial	Warranty Type	Lifetime
Type	Cable		

Dimensions

Cable Length	25 ft
--------------	-------

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm
--------------------------	-----	--------------------------	------------------------------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	24 AWG
Video Resolution	UXGA (1600x1200)	Bend Radius	90 mm
Cable Type	Runner, Audio, Video	Jacket Rating	CMG (FT4) Rated
Adapter Rear	RapidRun 15-pin Female	Adapter Front	RapidRun 15-pin Female
