

SPECIFICATION SHEET

PART NUMBER : EVNSL0504A-1000

STYLE : 75°C 300v

COMMUNICATION CABLE

DESCRIPTION : Category 5e Bulk Cable, 350 MHz, Shielded, PVC – Yellow, 24 AWG,
Solid, F/UTP, CMR

RECOGNIZED : UL 、 ETL

BLACK BOX CORPORATION

BLACK BOX NETWORK SERVICES

SPECIFICATION

STYLE	60°C 300V COMMUNICATION CABLE	
SIZE	UTP 24AWG×4P	ESTABLISHED DATE: June/16/2022
STANDARD : E196163-C c(UL)us CM & ETL VERIFIED TO ANSI/TIA-568.2-D APPLICATION : LAN CABLE ARE SUITABLE FOR PERFECT AUDIO DATA AND VIDEO OF TRANSFER FOR HORIZONTAL NETWORK CONSTRUCTION:		
CONDUCTOR	SIZE	24AWG
	CONSTRUCTION	STRANDED BARE COPPER
	COND. DIAM.	1/24AWG
INSULATION	AVG. THICK.	0.284 mm 0.01118 inch
	MIN. THICK.	0.251 mm 0.00988 inch
	DIAMETER	1.10 ± 0.05 mm 0.04331±0.00197 inch
	MATERIAL	Polyethylene
	COLOR CODES	1.BLUE × WHITE/BLUE STRIPE 2.ORANGE × WHITE/ORANGE STRIPE 3.GREEN × WHITE/GREEN STRIPE 4.BROWN × WHITE/BROWN STRIPE
CABLING	PAIR	2 single conductors paired
	FILLER(SPINE)	N/A
	ASSEMBLY STRANDED	4 twisted pairs
SHIELD	OVERALL SHIELD & MATERIAL	AL/Polyester , 25% overlap
	DRAIN WIRE	26AWG solid tinned copper
JACKETED	AVG. THICK.	0.5 mm 0.02087inch
	MIN. THICK.	0.45 mm 0.01772inch
	DIAMETER	6.30± 0.30 mm 0.2480±0.01181 inch
	MATERIAL	PVC
	COLOR	YELLOW - RAL 1021
	RIP CORD	NO
PACKAGING	Reelex or Spool	Spool

BLACK BOX NETWORK SERVICES

SPECIFICATION

ELECTRICAL & PHYSICAL PROPERTIES:			
ITEM			24AWG × 4P
RATING TEMP VOLTAGE			75°C 300V
CONDUCTOR RESISTANCE			9.38 OHM/100m/20°C MAX.
MUTUAL CAPACITANCE			5.6 nF/100M MAX.
DIELECTRIC STRENGTH			DC 2.5KV/2SECONDS.
SPARK TEST			2500V
INSULATION	UNAGED	TENSILE	2400 PSI MIN
		ELONGATION	300% MIN.
	AGED	TENSILE	UNAGED MIN. 75%(100°C×48HRS)
		ELONGATION	UNAGED MIN. 75%(100°C×48HRS)
JACKETED	UNAGED	TENSILE	2000 PSI MIN
		ELONGATION	100% MIN.
	AGED	TENSILE	UNAGED MIN. 75%(100°C×168HRS)
		ELONGATION	UNAGED MIN. 50%(100°C×168HRS)
INSULATION SHRINKBACK			150mm, 100°C±2°C×1HR ≤7.5mm
COLD BENDTEST			-20°C×4HRS NO CRACK
FLAME RETARDANT TEST			CMR
AC LEAKAGE CURRENT THROUGH OVERALL JACKET			AC 1500V ≤ 10mA
DC RESISTANCE UNBALANCE			2 %/ 20°C MAX
PAIR-TO-GROUND CAPACITANCE			330 pF/100m MAX.
PROPAGATION DELAY			100 MHz 537nS/100m MAX.
DELAY SKEW			1~100MHz 45nS/100m MAX.
PRINTING:			
BLACK BOX CORPORATION --- CATEGORY 5E SHIELDED --- E196163-C (UL) C(UL) CMR F/UTP 75°C 4PR 24AWG ANSI/TIA 568.2-D CAT 5E TESTED TO 350MHZ YY-MM XXXXFT(countdown circulated length in feet and printing per two feet)			

BLACK BOX NETWORK SERVICES

SPECIFICATION

Electrical performance (100 METER LOOP)

ITEM(dB)	IL	NEXT	ACR	PS. NEXT	PS. ACR	ACRF	PS. ACRF	R.L.
Frequency (MHz)	MAX. dB/100m	MIN. (dB)	MIN. (dB)	MIN. (dB)	MIN. (dB)	MIN. (dB)	MIN. (dB)	MIN. (dB)
1	2.0	65.3	63.3	62.3	60.3	63.8	63.8	20.0
4	4.1	56.3	52.2	53.3	49.2	51.8	51.8	23.0
8	5.8	51.8	46.0	48.8	43.0	45.7	45.7	24.5
10	6.5	50.3	43.8	47.3	40.8	43.8	43.8	25.0
16	8.2	47.2	39.0	44.2	36.0	39.7	39.7	25.0
20	9.3	45.8	36.5	42.8	33.5	37.8	37.8	25.0
25	10.4	44.3	33.9	41.3	30.9	35.8	35.8	24.3
31.25	11.7	42.9	31.2	39.9	28.2	33.9	33.9	23.6
62.5	17.0	38.4	21.4	35.4	18.4	27.9	27.9	21.5
100	22.0	35.3	13.3	32.3	10.3	23.8	23.8	20.1
200	32.4	30.8	-	27.8	-	17.7	17.8	18.0
250	36.9	29.3	-	26.3	-	15.8	15.8	17.3
300	41.0	28.1	-	25.1	-	14.3	14.3	16.8
350	44.9	27.1	-	24.1	-	12.9	12.9	16.3

Between 100 and 350MHZ is only for reference