

## 30 ft DisplayPort Cable with Latches - M/M

**Product ID:** DISPLPORT30L



The DISPLPORT30L 30-foot DisplayPort Cable supports a maximum bandwidth of 10.8 Gbps, and is capable of providing higher performance than either HDMI or dual link DVI, while supporting next generation multimedia applications with a maximum resolution capability of up to WQXGA (25601600).

The cable features latching connectors, with support for two-way display connectivity and optional audio support.

Featuring 26 gauge (AWG) pure copper wire, the cable includes Aluminum and Mylar shielding to help eliminate EMI and RFI interference and maintain signal integrity without any degradation of quality.

This 30-foot DisplayPort cable is both HDCP and DPCP capable, ensuring that digitally protected content is displayed properly on the connected display.

## Certifications, Reports and Compatibility

### Applications

- Connecting a DisplayPort display to a PC or other DisplayPort source

### Features

- Molded latching connectors with strain relief
- Designed and manufactured to DisplayPort standards
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP

---

**Hardware**

Warranty	Lifetime
Number of Conductors	19
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)

---

**Connector(s)**

Connector A	DisplayPort (20 pin)
Connector B	DisplayPort (20 pin)

---

**Physical Characteristics**

Color	Black
Connector Style	Latching
Wire Gauge	26 AWG (0.404 mm)
Cable Length	30.0 ft [9.1 m]
Cable OD	0.3 in [8.5 mm]
Product Length	30.0 ft [9.2 m]
Product Width	0.8 in [20.5 mm]
Product Height	0.4 in [10.8 mm]
Weight of Product	23.6 oz [669.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	13.0 in [33.0 cm]
Package Width	9.9 in [25.2 cm]
Package Height	1.9 in [48.0 mm]
Shipping (Package)	24.0 oz [679.0 g]



Weight

---

**What's in the  
Box**

Included in Package	30 ft DisplayPort Cable with Latches - M/M
---------------------	--

---

***\*Product appearance and specifications are subject to change without notice.***

