

USB 3.0 Multi Media Flash Memory Card Reader

Product ID: FCREADHCU3



The FCREADHCU3 USB 3.0 Card Reader enables easy read/write access to a variety of popular flash memory card formats/types (CompactFlash, Secure Digital, Memory Stick) in a single unit, over a high speed USB 3.0 connection.

Using a connection over USB 3.0, which is up to 10 times faster than the USB 2.0 standard, makes transferring large data files much quicker; it (USB 3.0) is still backward compatible with USB 2.0 however, ensuring compatibility with older systems.

This compact and lightweight external card reader offers a portable, convenient solution for accessing many different types of Flash Memory/Media cards and is easy to use, with no driver or software installation required.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Laptop users looking to be able to access one or more types of flash memory cards
- Professionals looking to access their high speed flash memory cards over USB 3.0, instead of USB 2.0

Features

- Compatible with various types of CompactFlash, SecureDigital and MemoryStick flash cards
- SuperSpeed USB 3.0 host interface standard, which supports transfer rates up to 5 Gbps
- Powered directly from the USB port

- Backward compatible with USB 2.0 computer systems
- Power indicator LED
- Compact design and lightweight plastic construction
- No driver or software installation required

Hardware

| | |
|------------|------------------------|
| Warranty | 2 Years |
| Interface | USB 3.0 |
| Chipset ID | Genesys Logic - GL3220 |

Performance

| | |
|-------------------|---|
| Memory Media Type | MS Duo, MS Pro Duo, MS Pro-HG Duo CF (Compact Flash I Card) SDXC (Secure Digital eXtended Capacity) SDHC (Secure Digital High Capacity) microSDHC (Micro Secure Digital High Capacity) SD/MMC (Secure Digital/Multimedia Card) M2 (Memory Stick Micro) MS MG (Memory Stick w/ MagicGate) MS/MS Pro (Memory Stick/Memory Stick Pro) RS-MMC (Reduced Size Multimedia Card) MSXC (Memory Stick eXtended Capacity) Mini-SD, Micro-SD (Mini/Micro Secure Digital) |
|-------------------|---|

Connector(s)

| | |
|-------------------|--|
| Connector Type(s) | USB Type-B (9 pin) USB 3.0 |
| External Ports | SD / MMC Slot CompactFlash (50 pin) Slot MiniSD / MicroSD / MMC Slot |



Memory Stick / Memory Stick Pro Slot

Software

| | |
|------------------|---|
| OS Compatibility | OS independent; No software or drivers required |
|------------------|---|

Special Notes / Requirements

| | |
|-------------------------------|--------------------|
| System and Cable Requirements | Available USB port |
|-------------------------------|--------------------|

Indicators

| | |
|----------------|-------|
| LED Indicators | Power |
|----------------|-------|

Power

| | |
|------------------------------|--------------|
| Power Source | USB-Powered |
| Input Voltage | 100 - 240 AC |
| Input Current | 0.8 A |
| Output Voltage | 5 DC |
| Output Current | 4 A |
| Power Consumption (In Watts) | 20 |

Environmental

| | |
|-----------------------|-----------------------------|
| Operating Temperature | -40C to 80C (-40F to 176F) |
| Storage Temperature | -65C to 150C (-85F to 302F) |
| Humidity | 5% ~ 90% RH |

Physical Characteristics

| | |
|-------------------|------------------|
| Color | Black |
| Material | Plastic |
| Product Length | 3.3 in [85.0 mm] |
| Product Width | 2.2 in [55.0 mm] |
| Product Height | 0.8 in [20.0 mm] |
| Weight of Product | 1.9 oz [54.0 g] |



Packaging Information

| | |
|---------------------------|------------------|
| Package Quantity | 1 |
| Package Length | 6.8 in [17.3 cm] |
| Package Width | 5.6 in [14.3 cm] |
| Package Height | 1.3 in [32.0 mm] |
| Shipping (Package) Weight | 6.0 oz [169.0 g] |

What's in the Box

| | |
|---------------------|---------------------|
| Included in Package | USB 3.0 Card Reader |
| | USB 3.0 Cable |
| | Instruction Manual |

****Product appearance and specifications are subject to change without notice.***

