

ADD-MGMC-LX-2SC

100M/1G/2.5G/5G/10GBase-N(RJ-45) to Open SFP+ Port Media Converter

Features

- Built-in IP-based Web Interface.
- Supporting remote and local management.
- Supporting IEEE802.3X Frame Flow Control for Full-Duplex mode.
- Store and Forward mechanism.
- Manual IP address setting/DHCP client for IP address assignment.
- SNMP v1/ v2c monitor/ private Enterprise MIB.
- Event trap and SNMP trap support.
- Speed duplex mode configuration/ Flow Control setting/ bandwidth Control on TP/ Fiber port.
- Supports Port Status/ Ethernet Statistics on both TP and Fiber interface.
- Supports Maximum frame size to 16K bytes.
- Loop detection/ Broadcast/ Multicast/ Unicast storm control.
- Management VLAN/ 16 IEEE 802.1Q VLAN groups/ Q-in-Q VLAN.
- 802.1p Tag Priority/ IP address priority/ IP DSCP option in.
- Quality of Service Mode and Strict Priority/ Weighted Round Robin (WRR) QoS policies.
- TS-1000 OAM/ IEEE 802.3ah OAM/ Loop Back Test.
- 16 TCP/ UDP Filter groups.
- Firmware upgrade via remote Web interface.
- LED indicators for easy network diagnosing.
- Rest Button at the front panel for the factory default reset.



Product Description

This is a one to one managed media converter that converts a 10/100/1000Base-TX(RJ-45) to 1000Base-LX(SC) via a 1310nm single-mode fiber (SMF) SC connector, which allows distance reach up to 20km. This provides a cost effective conversion from 10/100/1000Base-TX(RJ-45) to 1000Base-LX fiber, while extending the network reach beyond the 100m reach limitation of copper. Our one to one type manageable media converters are independent standalone systems that do not require a centralized, or unified platform management system. One to One manageable media converters can supervise the real time situation of remote manageable fiber media converters, and allow end users to set the functions remotely. With this system, the response speed of the operator is quickened, the daily maintenance and network expenditure is reduced, and the service quality is enhanced. Our media converters are 100% compliant for all of our networking needs. Now you have a cost effective solution to your network upgrade needs.

Specifications

Parameter	
Ethernet Interface	
Standards	IEEE802.3, IEEE802.3u, IEEE802.3z, IEEE802.3ab, IEEE802.3x
Data Rate	10Mbps, 1000M Half/Full Duplex Auto-Sensing
Connector	RJ-45
UTP Cat5 or Cat5e	Connecting with RJ-45, Transmission Distance at 100m
Fiber Port	
Connector	SC
Operating Wavelength	1310nm
Optical Fibers	Single-Mode: 8.3/125, 8.7/125, 9/125, 10/125µm
Transmission Distance	20km
Basic Working Environment	
Operating Temperature	0 to 50°C
Storage Temperature	-10 to 70°C
Humidity	5-90% (Non-Condensing)
Dimension (Standalone)	156mm (W) x 128mm (D) x 32mm (H)
Power Supply	120V AC Power Cable
Power Consumption	≤5W

About AddOn Networks

In 1999, AddOn Networks entered the market with a single product. Our founders fulfilled a severe shortage for compatible, cost-effective optical transceivers that compete at the same performance levels as leading OEM manufacturers. Adhering to the idea of redefining service and product quality not previously had in the fiber optic networking industry, AddOn invested resources in solution design, production, fulfillment, and global support.

Combining one of the most extensive and stringent testing processes in the industry, an exceptional free tech support center, and a consistent roll-out of innovative technologies, AddOn has continually set industry standards of quality and reliability throughout its history.

Reliability is the cornerstone of any optical fiber network and is engrained in AddOn's DNA. It has played a key role in nurturing the long-term relationships developed over the years with customers. AddOn remains committed to exceeding industry standards with certifications from NEBS Level 3 to ISO 9001:2005 with every new development while maintaining the signature reliability of its products.



U.S. Headquarters

Email: sales@addonnetworks.com

Telephone: +1 877.292.1701

Fax: 949.266.9273

Europe Headquarters

Email: salesupportemea@addonnetworks.com

Telephone: +44 1285 842070