

USB 3.0 to DVI / VGA Adapter – 2048x1152

Product ID: USB32DVIPRO



The USB32DVIPRO USB 3.0 to DVI Adapter turns an available USB 3.0 port into a DVI output, with high resolution 2048x1152 video support - a convenient external video solution that makes it easy to add multi-monitor capability to a USB 3.0-enabled desktop or laptop computer (optimal performance from USB 3.0, backward compatible with USB 2.0).

Leveraging the high-bandwidth (5 Gbps) SuperSpeed USB 3.0 interface, the adapter functions as an external graphics card to deliver smooth, high-resolution content to your DVI or VGA-capable display (DVI to VGA Adapter included). The adapter can be used to mirror your primary desktop, showing the same image on each display, or to extend your desktop to double your workspace and increase your productivity.

Backed by a StarTech.com 2-year warranty and free lifetime technical support. **Recommended System Requirements:**

CPU: Quad Core 2.4GHz or Higher (i5 recommended)

RAM: 4GB or higher

Certifications, Reports and Compatibility

Applications

- Add a secondary DVI or VGA display and extend your desktop without taking apart your computer to install a new video card
- Add multi-monitor capability to a single computer, to create engaging multimedia presentations
- Use the adapter to connect your PC to your DVI or VGA-equipped TV, for showing family pictures and movies

- Great for researchers and writers, offering the ability to have reference material on one display and a working document copy on the other
- Increase productivity by running multiple applications on different screens, check your e-mail on one display and search the web on the other
- View large or multiple spreadsheets across multiple displays
- A compact, lightweight solution for traveling business associates using laptop PCs, enabling connection to a secondary display/projector

Features


- SuperSpeed USB 3.0 (5 Gbps) Interface and backwards compatible with USB 2.0
- Quick, easy installation
- DVI to VGA adapter included
- Supports resolutions up to 2048x1152
- USB-powered - No external power adapter required
- Choose between Mirrored, Extended or Primary display configurations
- Driver software supports display rotation
- Supports the Windows Aero interface
- Supports the use of multiple USB32DVIPRO adapters on a single system (up to 5)

Hardware

Warranty	2 Years
AV Input	USB 3.0
AV Output	DVI
Audio	Yes
USB Pass-Through	No
Memory	512MB
Chipset ID	DisplayLink - DL-3100

Performance

Maximum Analog Resolutions	2048x1152
----------------------------	-----------



Maximum Digital Resolutions	2048x1152
Supported Resolutions	<p>Widescreen(16/32 bit):</p> <p>2048x1152, 1920x1200, 1920x1080, 1680x1050, 1366x768, 1280x800, 1280x768, 1280x720</p> <p>Standard(16/32 bit):</p> <p>1600x1200, 1400x1050, 1280x1024, 1024x768, 800x600, 640x480</p>
Wide Screen Supported	Yes
General Specifications	<p>Note: If using OS X 10.8, Apple update 10.8.3 must be installed before installing DisplayLink software. 10.8.3 fixes several serious OS X bugs exposed when DisplayLink software is installed.</p> <p>This USB video adapter uses a DisplayLink family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, please avoid using devices with a Trigger or Fresco family chipset.</p>
MTBF	90,577 hours

Connector(s)

Connector A	USB Type-A (9 pin) USB 3.0 (5 Gbps)
Connector B	DVI-I (29 pin)

Software

OS Compatibility	<p>Windows XP (32-bit), Vista, 7, 8, 8.1, 10</p> <p>macOS 10.6 - 10.12, 10.14 - 10.15, 11.0</p> <p>Ubuntu 14.04, 16.04, 18.04</p> <p>Chrome OS v55+</p>
------------------	---

Special Notes / Requirements

System and Cable Requirements	<p>System Processor: Quad Core 2.4GHz (i5 recommended)</p> <p>System Memory: 4GB</p>
Note	<p>This USB video adapter uses a DisplayLink family chipset. If you're connecting this device to a computer along with additional USB video adapters or docking stations, avoid using devices with different family chipsets, such as Trigger or Fresco Logic</p> <p>Connect a maximum of five USB video adapters on a single computer. Support for multiple adapters will vary depending upon your system</p>

resources

This USB video adapter is not intended for graphical intensive applications, such as gaming

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	10C to 40C (50F to 194F)
Storage Temperature	-10C to 80C (14F to 167F)
Humidity	<85% RH Non-Condensing

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	6.0 in [15.2 cm]
Product Length	3.1 in [78 mm]
Product Width	1.7 in [43.5 mm]
Product Height	0.6 in [15.5 mm]
Weight of Product	3.2 oz [91 g]

Packaging Information

Package Length	6.7 in [17.1 cm]
Package Width	5.7 in [14.4 cm]
Package Height	1.2 in [30 mm]
Shipping (Package) Weight	7.4 oz [211 g]

What's in the Box

Included in Package	USB 3.0 to DVI Adapter
	DVI to VGA Adapter
	Driver CD



Installation guide

****Product appearance and specifications are subject to change without notice.***

