

## Gigabit Ethernet Single Mode Fiber Media Converter SC 40 km - 1000 Mbps

**Product ID:** ET91000SM402



The ET91000SM402 1000 Mbps Gigabit Single Mode Fiber Media Converter SC (40 km) lets you extend a Gigabit Ethernet network over single mode fiber by up to 40km (25 miles).

A cost-effective solution for connecting a Gigabit Ethernet (1000Base-T) network to remote network segments over a (1000Base-LX/SX) fiber backbone, the GbE to SM fiber converter supports full Gigabit speeds for ideal network performance and scalability. Designed to offer a durable and convenient Ethernet to fiber solution, the Ethernet to SC Fiber converter features an all-steel chassis, and a simple plug-and-play installation with minimal configuration required.

For added versatility, this fiber media converter supports standalone operation, or installation into the 20 Slot, 2U Rackmount Chassis (ETCHS2U).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Provides network connectivity to users or network segments located in isolated areas of a large complex or separate building
- Suitable for environments such as government agencies, where security threats (network tapping, etc.) need to be prevented
- Connect traffic control/monitoring systems at extreme distances to the main office
- Extend network connectivity to remote areas of stadiums, auditoriums or other venues

- Converts 1000Base-LX fiber optic signals to 1000Base-T Ethernet over single mode fiber cable

## Features

- Supports standalone operation, or installation into the ETCHS2U Rackmount Chassis
- Cost-effective way to extend/bridge networks using fiber cabling
- Advanced features include Link-loss forwarding, remote monitor status, two frame lengths
- Maximum Fiber Cable length of 40 km
- Supports full or half-duplex operation
- Quick and simple installation, easy to use

---

### Hardware

Warranty	2 Years
PoE	No
WDM	No

---

### Performance

Maximum Data Transfer Rate	2000 Mbps (full duplex mode)
Max Transfer Distance	40 km (24.8 mi)
Type	Single Mode
Wavelength	1310nm
Fiber Operating Mode	Half/Full-Duplex
Auto MDIX	Yes
MTBF	65,000 Hours

---


### Connector(s)

Local Unit Connectors	RJ-45 Fiber Optic SC Duplex
-----------------------	--------------------------------

---

### Power

Power Source	AC Adapter Included
--------------	---------------------



Input Voltage	100 - 240 AC
Input Current	0.36A
Output Voltage	12V DC
Output Current	1.6 A
Center Tip Polarity	Positive
Plug Type	M
Power Consumption (In Watts)	4

---

#### Environmental

Operating Temperature	0C to 60C (32F to 140F)
Storage Temperature	-10C to 70C (14F to 158F)
Humidity	10~90% RH

---

#### Physical Characteristics

Color	Black
Material	Steel
Product Length	6.3 in [16 cm]
Product Width	3.7 in [95 mm]
Product Height	0.8 in [20 mm]
Weight of Product	21.2 oz [600 g]

---

#### Packaging Information

Package Length	8.1 in [20.5 cm]
Package Width	5.5 in [14 cm]
Package Height	3.6 in [91 mm]
Shipping (Package) Weight	24.7 oz [700 g]

---

#### What's in the Box



Included in Package	Fiber Media Converter
	Universal Power Adapter (NA/EU/UK/AU)
	Grounding Screw
	Instruction Manual

---

***\*Product appearance and specifications are subject to change without notice.***

